



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 130 $\pm$ 50gf
6. TRAVEL: 0.25mm $\pm$ 0.15
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE: 130g > 50,000 CYCLES
- ▲ 9. SILVER CONTACTS
10. PACKAGING: TAPE & REEL; 2300 PIECES PER REEL.
11. ▲ DENOTES CRITICAL PARAMETER



B	22924	drawing update	7/10/17	MW
A	16309	NEW RELEASE	8/14/06	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL3330AF130QG

SCALE 8:1	DATE 6/14/2006	DR RC	DWG P010950	REV B
--------------	-------------------	----------	----------------	----------