


XDSL Splitter Filter Module

BX8214V / BX8214VNL

Smart Series



- ☐ POTS Central Office Splitter for standard ADSL and VDSL applications
- ☐ For use with ANSI T1.413 standard
- ☐ Part of a standard series with footprint compatibility
- ☐ Patent Approved
- ☐ ADSL2+ compatible
- ☐ Compatible with VDSL2 30MHz
- ☐ NL version: RoHS-6 compliant

Electrical Specifications @ 25°C - Operating Temperature -40°C to +85°C

Parameter	Frequency	
POTS Impedance	100Hz to 4kHz	800 Ω 100 Ω + 50nF
POTS Insertion Loss	1kHz	0.6dB MAX
POTS Attenuation Distortion relative to 1kHz NOTE: Attenuation is positive value, gain is negative	200Hz to 3.4kHz	-1.5 to +0.5dB
	3.4kHz to 4kHz	-1.5 to +1.0dB
POTS Delay Distortion	600Hz to 4kHz	200 μ SEC MAX
POTS Return Loss	200Hz (SRL-L)	5dB MIN
	1kHz (ERL)	8dB MIN
	2.2kHz (SRL-H)	5dB MIN
Intermodulation Distortion (2nd and 3rd harmonics)	4-Tone IEEE 743 signal	-60dB MIN
Longitudinal Balance	200Hz to 3.2kHz	-58dB MIN
Tip to Ring Capacitance	20Hz to 30Hz	115nF MAX
VDSL Insertion Loss	30kHz to 300kHz	-65dB MIN
	300kHz to 2.2MHz	-55dB MIN
DC Current		100mA MAX
Total DC Resistance		25 Ω MAX
Tip to Ring Isolation		600Vdc MIN

Notes: For VDSL2 (30MHz) compatible version, refer to BX8214V.

USA 858 674 8100

Germany 49 7032 7806 0

Singapore 65 6287 8998

Shanghai 86 21 62787060

China 86 755 33966678

Taiwan 886 3 4356768

Smart Series

BX8214V / BX8214VNL

