





PRODUCT NUMBER

77315-YXX-XXLF

- RoHS COMPATIBLE
SEE NOTE 7
- TOTAL NB OF POSITIONS 01 TO 36
- PACKAGING, NOTE 3
- PIN STYLE SEE SHEET 2
- PLATING SEE SHEET 2

NOTES:

- HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
- PIN MATERIAL : PHOSPHOR BRONZE
- PACKAGING:
 - PACKAGING POLYBAG
 - "V" BLIBOX PACK FOR CUSTOMER DEDICATED PART
- 9N MIN RETENTION IN EITHER DIRECTION
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- UNDERPLATING : 1.27µm Ni MIN
- RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code				surface	tolerance	projection	product family	
SEE NOTES				ISO 1302	ISO 406 ISO 1101		BERGSTIK	
ltr	ecr no	dr	date	tolerances unless otherwise specified			title	
AK	B-15093	JCO	13.06.28	angles	.X ±0.3	mm	UNSHR.HEADER RA SR TMT	
AL	B-15388	LMU	13.07.31		.XX ±0.15			
AM	B16178	JCO	13.10.31		.XXX ±0.05			
AN	B-17109	JCO	14.03.06	dr	D.LE	01.01.24	dwg no	sheet 1 of 2 size
AP	B-17839	JCO	14.06.03	enrg	JM.C	01.01.24	77315 A3	
AR	B-18916	LMU	14.09.26	chr	JM.C	01.01.24		
AS	B-19715	BVE	14.12.11	appd	JF.N	01.01.24		
sheet	revision	AS	AM				type	Drawing
index	sheet	1	2					



FCIconnect.com

Copyright FCI

PLATING

- 1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
4 = 2µm TIN MIN FULL PLATED
5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
G = 0.76µm FULL GXT
S = 0.38µm FULL GXT
- 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

PRODUCT SPECIFICATIONS

PIN	STYLE	MATING	SOLDER	DIM "C"
01		5.72	2.57	1.5
02		5.72	5.11	1.5
07		5.72	5.11	3.9
13		5.72	3.45	1.5
18		5.84	3.05	1.5
22		11.71	3.2	1.5
24		6.75	2.85	1.5
25		8.07	3.05	1.5
26		8.2	12.6	1.5
27		5	3.9	1.5
28		3.1	3.1	1.5
29		9.7	2.90	1.5
30		8.30	4.40	1.5
31		11.70	2.80	1.5
32		8.90	3.05	1.5
33		10.20	3.05	1.5
34		10.00	3.25	1.5
35		5.72	12.73	1.5
36		N/A		
37		N/A		
38		8.51	5.51	1.5
39		9.80	9.30	1.5
40		8.13	2.54	3.90
41		14.20	3.05	1.5
42		9.00	7.20	1.5
43		8.08	2.79	1.5
44		15.70	2.79	1.5

mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK		
ltr	ecn no	dr	date	tolerances unless otherwise specified						title		
AG	F12-0095	LMU	12.10.25	angles	linear	.X ±0.3				UNSHR.HEADER RA SR TMT		
AH	B-15093	JCO	13.06.28			.XX ±0.15						
AJ	B-15388	LMU	13.07.31			.XXX ±0.05		scale 5:1				
AK	B-16178	JCO	13.10.31	dr	D.LE	01.01.24				dwg no		
AL	B-17109	JCO	14.03.06	enr	JM.C	01.01.24				sheet 2 of 2		
AM	B-18916	LMU	14.09.26	chr	JM.C	01.01.24				77315		
				appd	JF.N	01.01.24				A3		
sheet index		revision sheet								type CUSTOMER Drawing		