

POWER SPLITTERS/COMBINERS

50&75Ω

12 Way-0° 1 to 1700 MHz


SURFACE MOUNT



JEPS-12



PSC-12



ZN12PD



ZFSC-12

MODEL NO.	FREQ. RANGE MHz f_L - f_U	ISOLATION dB			INSERTION LOSS, dB Above 10.8dB			PHASE UNBALANCE Degrees			AMPLITUDE UNBALANCE dB			CASE STYLE Note B	COAXIAL NO. bu	PRICE \$ Qty. (1-9)
		L Typ. Min.	M Typ. Min.	U Typ. Min.	L Typ. Max.	M Typ. Max.	U Typ. Max.	L Max.	M Max.	U Max.	L Max.	M Max.	U Max.			
◆ JEPS-12-10	50-1000	25	16	—	—	23	14	1.6	2.5	—	—	2.2	4.0	BL372	ix	109.95
PSC-12-1	1-200	35	30	27	20	21	18	0.5	0.8	0.8	1.2	1.0	1.4	E10	bu	88.95
ZN12PD-17	800-1700	—	30	18	—	—	—	0.45	1.2	—	—	—	—	UU589	—	249.00
ZFSC-12-1	1-200	30	25	35	20	28	20	0.8	1.2	1.1	1.4	1.3	1.6	R67	—	174.95
■ ZFSC-12-1W-75	5-860	33	22	30	20	26	18	0.5	1.2	0.8	2.5	1.6	4.2	R67	—	199.95
ZFSC-12-11	10-300	28	20	33	25	28	20	1.1	1.3	1.1	1.5	1.5	1.8	R67	—	174.95
■ ZFSC-12-1-75	10-200	35	27	—	—	27	20	0.5	0.8	—	—	0.8	1.3	R67	—	179.95
■ ZFSC-12-175	10-500	23	20	24	20	22	18	0.9	1.2	1.0	1.3	1.2	2.0	R67	—	197.95

L = low range [f_L to 10 f_L]

M = mid range [10 f_L to $f_U/2$]

U = upper range [$f_U/2$ to f_U]

NOTES:

- ◆ Aqueous washable
- Non-hermetic
- Denotes 75 Ohm model, for coax connector models 75 Ohm BNC connectors are standard.
- ⊗ When only specification for M range given, specification applies to entire frequency range.
- ⊕ At low range frequency band (f_L to 10 f_L), linearly derate maximum input power by 13 dB.
- A. General Quality Control Procedures, Environmental Specifications, Hi-Rel and MIL description are given in section 0, see "Mini-Circuits Guarantees Quality" article.
- B. Connector types and case mounted options, case finishes are given in section 0, see "Case styles & Outline Drawings".
- C. Prices and specifications subject to change without notice.
- 1. Absolute maximum power, voltage and current ratings:
 - 1a. Matched power rating,
 - Model ZC16PD 10 Watt
 - Model ZN12PD 5 Watt
 - Model ZC16PD-23 2 Watt
 - Model JEPS 0.5 Watt
 - All other models 1 Watt
 - 1b. Internal load dissipation,
 - Model ZC16PD, ZC16PD-24 2.4 Watt
 - Model ZN12PD, ZC16PD-23 2 Watt
 - Model ZC16PD-2185 1.75 Watt
 - Model ZFSC-12-1W-75 1.5 Watt
 - Model JEPS-16-1W-75 0.275 Watt
 - Model JEPS-16-1W 1.875 Watt
 - All other models 0.87 Watt

NSN GUIDE

MCL NO.
ZFSC-16-1(BNC)

NSN
5820-01-9321



Distribution Centers NORTH AMERICA 800-654-7949 • 417 335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

ISO 9001 CERTIFIED


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

020314

Surface Mount □, Plug-In & Coaxial

16 Way-0° 10 kHz to 2.6 GHz



	MODEL NO.	FREQ. RANGE MHz f _L -f _U	ISOLATION dB					INSERTION LOSS, dB Above 12dB						PHASE UNBAL. Degrees			AMPLITUDE UNBAL. dB			VSWR (:1)				CASE STYLE Note B	CONNECTION	PRICE \$ Qty. (1-9)	
			L		M°		U	L		M°		U	L	M°	U	L	M°	U	S		OUT						
			Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Typ.	Max.	Typ.	Max.					
NEW◆ ◆■	JEPS-16-1W	5-1000	36	23	23	17	20	15	0.8	2.0	1.5	2.5	3.0	4.2	8	13	20	1.5	1.2	1.8	1.2	—	1.2	—	BL372	kf	79.95
	JEPS-16-1W-75	10-800	32	20	23	15	20	15	1.6	3.5	1.9	3.5	2.2	4.0	10	15	30	0.8	1.2	2.1	1.40	—	1.16	—	BL372	kf	139.95
	ZFSC-16-1	0.5-125	30	24	25	18	20	15	1.0	1.2	1.1	1.3	1.2	1.4	1	3	5	0.3	0.2	0.5	see Yoni for		R30	—	172.95		
	■ ZFSC-16-1-75	1-150	30	25	30	25	25	20	0.8	1.1	0.7	1.1	1.0	1.3	3	6	10	0.4	0.2	0.4	Performance		R30	—	182.95		
	ZFSC-16-3	1-30	—	—	45	28	—	—	0.5	0.9	0.5	0.9	0.5	0.9	1	2	3	0.1	0.1	0.1			R30	—	172.95		
	◆■ ZFSC-16-675	0.01-25	25	20	40	25	25	20	0.8	1.1	0.4	0.8	1.0	1.6	1	3	5	0.1	0.2	0.4	Data and		R30	—	189.95		
	ZFSC-16-12	0.1-200	33	20	27	20	26	20	0.6	1.5	0.7	1.0	0.9	1.5	2	6	9	0.4	0.2	0.4	curves		R30	—	189.95		
	ZC16PD-24	650-2400			25	14				0.8	2.25				14			0.9			1.20	1.90	1.10	1.50	UU640	—	349.00
	ZC16PD-900	800-900			30	20				0.5	1.0							0.5			1.06	1.20	1.06	1.20	UU179	—	295.00
	ZC16PD-960	890-960			28	20				0.5	1.0							0.5			1.06	1.30	1.06	1.20	UU179	—	295.00
	ZC16PD-960W	700-1000			26	15				0.5	1.3							0.6			1.10	1.60	1.06	1.30	UU179	—	265.00
	ZC16PD-1900	1700-1900			30	20				0.5	1.0							0.8			1.15	1.35	1.06	1.30	UU179	—	309.00
	ZC16PD-1900W	1500-2100			30	15				0.7	1.4							0.8			1.25	1.60	1.15	1.35	UU179	—	319.00
	ZC16PD-23	1500-2300			32	20				0.8	1.4				11			0.6			1.15	1.60	1.10	1.40	UU640	—	319.00
ZC16PD-2185	1800-2600			30	16				0.5	1.4				6			0.7			1.15	1.60	1.05	1.30	UU179	—	319.00	

L = low range [f_L to $10 f_L$]

M = mid range [$10 f_L$ to $f_U/2$]

U = upper range [$f_U/2$ to f_U]

pin and coaxial connections see case style outline drawings

PORT	SUM	#1	#2	#3	#4	#5	#6	#7	#8	#9	#10	#11	#12	#13	#14	#15	#16	NOT USED	GND EXT.	CASE GND
bu	5	7	8	1	2	31	32	25	26	22	30	19	27	—	—	—	—	11,14,21	4	all other pins
kf	18	2	3	4	5	9	10	11	12	13	14	15	16	20	21	22	23	—	all other pins	—
lx	18	2	3	4	5	8	9	10	11	14	15	22	23	—	—	—	—	—	all other pins	—