


Commercial Grade Axial Lead Power Wirewound & Film Resistor

CAW/CAF Series

- Power ratings from 2W to 10W
- Non-inductive winding available
- Standard tolerance $\pm 5\%$ and $\pm 10\%$
- Resistance range from 0.1Ω to $200K\Omega$
- Flameproof ceramic case with inorganic potting material



Electrical Data

IRC Type	Power Rating at 25°C (W)	Resistance Range* (Ohms)	Tolerance (±%)	Temperature Coefficient of Resistance (±ppm/°C)
Wirewound Type (CAW)				
CAW-2	2	0.1 - 27	5, 10	400 (<20Ω) 350 (≥20Ω)
CAW-3	3	0.1 - 39	5, 10	
CAW-5	5	0.1 - 47	5, 10	
CAW-7	7	0.1 - 680	5, 10	
CAW-10	10	0.1 - 910	5, 10	
CAW-15	15	1.0 - 1K	5, 10	
CAW-20	20	2.0 - 1.2K	5, 10	
CAW-25	25	2.0 - 1.2K	5, 10	
CAW-2A	2	0.1 - 27	5, 10	
CAW-5A	5	0.1 - 47	5, 10	
CAW-7A	7	0.1 - 680	5, 10	
CAW-10A	10	0.1 - 910	5, 10	
Film Type (CAF)				
CAF-2	2	28 - 33K	5, 10	400 (<20Ω) 350 (≥20Ω)
CAF-3	3	40 - 56K	5, 10	
CAF-5	5	48 - 100K	5, 10	
CAF-7	7	681 - 200K	5, 10	
CAF-10	10	911 - 200K	5, 10	
CAF-15	15	1.1K - 200K	5, 10	
CAF-20	20	1.3K - 200K	5, 10	
CAF-2A	2	28 - 33K	5, 10	
CAF-5A	5	48 - 100K	5, 10	
CAF-7A	7	681 - 200K	5, 10	
CAF-10A	10	911 - 200K	5, 10	

General Note

IRC reserves the right to make changes in product specification without notice or liability.
All information is subject to IRC's own data and is considered accurate at time of going to print.

Wire and Film Technologies Division • 4222 South Staples Street • Corpus Christi Texas 78411 USA
Telephone: 361 992 7900 • Facsimile: 361 992 3377 • Website: www.irc-tt.com



A subsidiary of
TT electronics plc

Commercial Grade Axial Lead Power Wirewound & Film Resistor



Environmental Data

Short-time overload	$\pm 5\% + 0.05\Omega$; 2.5 x nominal power for 5 seconds
Dielectric withstanding voltage	1000Vac
Resistance to Soldering heat	$\pm 5\% + 0.05\Omega$
Operating temperature range	-55°C to 275°C

Physical Data

CAW-X / CAF-X Type


CAW-XA / CAF-XA Type

Dimensions (mm)						
Wirewound Type	Film Type	W (±1)	D (±1)	L (±1)	H (±5)	d (±0.02)
CAW-2	CAF-2	7.0	7.0	18.0	28.0	0.7
CAW-3	CAF-3	8.0	8.0	22.0	22.0	0.7
CAW-5	CAF-5	10.0	9.0	22.0	22.0	0.8
CAW-7	CAF-7	10.0	9.0	35.0	35.0	0.8
CAW-10	CAF-10	10.0	9.0	49.0	35.0	0.8
CAW-15	CAF-15	12.5	11.5	49.0	35.0	0.8
CAW-20	CAF-20	14.5	13.5	60.0	35.0	0.8
CAW-25	-	14.5	13.5	64.0	35.0	0.8
CAW-2A	CAF-2A	7.0	7.0	18.0	28.0	0.7
CAW-5A	CAF-5A	10.0	9.0	22.0	35.0	0.8
CAW-7A	CAF-7A	10.0	9.0	35.0	35.0	0.8
CAW-10A	CAF-10A	10.0	9.0	49.0	35.0	0.8


Commercial Grade Axial Lead Power Wirewound & Film Resistor



Power Derating Curve



Heat Rise Chart



Ordering Data

Specify type, resistance, tolerance, RoHS-Compliance and packaging. This example is for a Ceramic Axial Film, 2-watt, 1000Ω resistor.

Sample Part No. **CAF** **2** **1001** **J** **LF** **BLK**

IRC Type
 CAF - Ceramic Axial Film
 CAW - Ceramic Axial Wirewound

Power rating
 (see specs table)

Resistance Value (EIA 4-digit code)
 (≥100Ω - First 3 significant digits plus 4th digit multiplier)
 Example: 100Ω = 1000; 1000Ω = 1001
 (>1000Ω - "R" is used to designate decimal)
 Example: 10Ω = 10R0; 0.25Ω = R250

Tolerance (EIA format)
 J = ±5%
 K = ±10%

RoHS - Compliance
 LF = RoHS compliant construction

Packaging
 BLK = bulk packaging