







© COPYRIGHT 1973 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
			O	RELEASE		
			A	REVISED PER ECN 2161	5-24-78	DAI
			A1	REV ECN 203	6-4-78	DAI
			A2	REV ECN 1963	6-10-78	SB
			B	RE-RELEASE - 7	8-15-88	SDJ
			C	ADDED - 6 & 8 PER 2745 & AR2373	4-18-89	mpe
			D	REV LOC & DIST AD-4171	11-29-89	BF
			E	OBS - 8 PER 0010-0724-93	8-12-93	SAS
			F	REV PER 0010-1545-93	11-0-94	SAS
			G	REV PER 0010-1125-94	12-14-94	JH
			H	REV PER 0010-0847-96	6-3-96	CB/JH
			J	REV PER 063C-0062-00	11-16-00	MZ



1. .010 MAX CUT-OFF TAB FOR LOOSE PIECE.
2. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000015 GOLD ON CONTACT AREA
3. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT .000030 GOLD ON CONTACT AREA.
4. .000016 MIN TIN.
5. LUBRICATED
6. .000015 GOLD ON CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
7. .000030 GOLD ON CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
8. POINT OF MEASUREMENT FOR PLATING THICKNESS.
9. OBSOLETE PART NUMBER
10. .000030 GOLD OVER NICKEL ON ENTIRE CONTACT.
11. SUPERSEDED BY 102099-2



10	102103-6A	102099-8A
7	102103-5	102099-7A
6	102103-4	102099-6A
4	102103-3	102099-5
3	102103-2	102099-2
2	102103-1	102099-1A
FINISH	LOOSE PIECE P/N	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.005 ANGLES ±	CONTRACT NO	AMP INCORPORATED Harrisburg, Pa.
MATERIAL PHOS. BRONZE	DR CHK APPD APPD	NAME CONTACT, MOD I, RECEPTACLE, CRIMP SNAP-IN, STD. PRESSURE, # 18 - # 22 AWG, SIDE FEED
FINISH SEE TABLE	DSGN APPD OTHER APPD	SIZE C
		CODE IDENT NO 00779
		DRAWING NO 102099
		SHEET