



INDUSTRIAL & FACILITIES



RETAIL & GROCERY



LONG TERM HEALTHCARE



SCHOOLS



LODGING



CONTRACTORS

CONNECT EVERY WORKER INSTANTLY WITH MOTOROLA WIRELESS VOICE COMMUNICATIONS

- Reduce Labor Costs
- Quickly Share Information
- Eliminate Wasted Time
- Accelerate Training
- ROI in 60 Days
- No Monthly Bills



Instant Communication = Instant Results

CONNECT EVERY WORKER

Instant Communication = Instant Results

- Save Time
- Increase Productivity
- Train New Hires
- Reduce Labor Cost

BETTER THAN...

Paging

Communicates only one-way; is loud, annoying, often ignored, response is delayed.

Phone Systems

Permit talking to only one worker at a time; workers must locate a phone; calls are often missed, ignored or sent to voice mail; response time is unknown.

Cordless Phones

Communicate with just one worker at a time, calls often missed or sent to voice mail, coverage can be inconsistent; not durable for everyday business use.

Nextel™ & Cell Phones

Significant monthly airtime cost, hundreds of dollars per worker annually; poor in-building coverage; communication with more than one person at a time costs extra.



MOTOROLA



- Eliminate wasted time of workers leaving their area to find and talk to others
- Ask for help, supplies, information
- Anyone can instantly respond and assist others
- New hires can ask questions, hear others exchange information
- Supervisors can coach, train, direct workers
- Managers always accessible, anywhere in building
- Immediately react to emergencies or injuries
- Answer and make phone calls while moving
- No contracts, monthly fees or per-call charges
- Compact and simple to use

RAPID RETURN ON INVESTMENT

Watch your savings multiply when each worker saves just 5 minutes per hour

<i>Hourly rate</i>	<i>Each radio pays for itself in...</i>	<i>Annual savings for 25 workers</i>
<i>\$8 per hour</i>	<i>59 days</i>	<i>\$35,000</i>
<i>\$12 per hour</i>	<i>40 days</i>	<i>\$52,500</i>
<i>\$24 per hour</i>	<i>20 days</i>	<i>\$105,000</i>

EVERY BUSINESS WILL IMPROVE RESULTS

RETAIL

Apparel, Hardware, Pharmacy, Nursery, Liquor, Gas Stations, Car Dealers

Improve customer service
Increase sales
Reduce shrink
Answer customer questions quickly
Quickly get stock & price checks
Instantly deploy workers where needed
Eliminate paging
Accelerate training of new hires

For Managers, Cashiers, Sales, Stock, Loss Prevention



GROCERY

Super Markets, Convenience, Gas Stations, Specialty Foods

Improve customer service
Increase sales
Reduce shrink
Answer customer questions quickly
Quickly get stock & price checks
Instantly deploy workers where needed
Eliminate paging
Accelerate training of new hires

For Managers, Cashiers, Sales, Stock, Loss Prevention, Clean Team




INDUSTRIAL

Manufacturing, Warehouse, Distribution Centers

Improve assembly line operations
Quickly request help, supplies, maintenance, quality control
Maximize output, sales & profit
Expedite requests & rush orders
Instantly react to injuries or emergencies
Critical for disaster preparedness
Increase safety and security

For Shipping, Receiving, Line Workers, Supervisors, Maintenance, Quality Control, Engineering, Customer Service



PROPERTY MANAGEMENT

Hotels, Resorts, Golf Courses, Apartments, Condos, Office Buildings, Sports Complexes

Improve response time to guest needs
Maximize productivity of staff
Increase safety & security for guests, staff
Coordinate events, banquets, meetings
Make new hires more productive
Respond quickly to emergencies

For Managers, Front Desk, Housekeeping, Meetings, Restaurants, Food Service, Security, Maintenance, Engineering

SCHOOLS

K-8, High, College, Athletics, Dormitory, Day Care

Instantly talk to teachers & staff
Increase safety & security for students, teachers, staff
Respond quickly to emergencies
Monitor crosswalks, playgrounds, facilities, dorms, parking lots, bus loading
Coordinate events, athletics, field trips

For Administrators, Teachers, Maintenance, Security, Nurses, Trainers, Coaches, Cafeteria, Hall Monitors, Engineering, Grounds Crew



CONTRACTORS

Construction, Electrical, Interconnects, Mechanical, Installers, Comm Data

Supervise subs, crews, operators
Coordinate wire pulling & installations
Manage deliveries & materials
Increase safety & security for workers
Respond quickly to emergencies
Critical for disaster preparedness

For GCs, Subs, Operators, Installers



HEALTH CARE

Nursing, Assisted Living, Retirement, Long Term Care, Hospitals, Clinics

Instantly talk to doctors, nurses, staff
Increase productivity of staff
Respond quickly to emergencies
Increase safety & security for patients, residents, staff
Coordinate social activities, events, trips
Critical for disaster preparedness

For Doctors, Nurses, Management, Staff, Maintenance, Food Service



FOOD SERVICE

Restaurant, Banquet, Cafeteria, Bars, Meeting & Convention Facilities

Improve table turns, increase revenue
Reduce customer wait time
Clean & set tables faster
Notify wait staff when orders are ready
Coordinate runners & replenishment
Make new hires more productive

For Managers, Host, Wait Staff, Bus Staff, Kitchen, Valet Parking, Security



MOTOROLA

CONNECT EVERY WORKER

Instantly Communicate To One or All

Small, Sleek, Stylish

Introducing the smallest two-way radio, only 2.4 ozs, 40% smaller and lighter. No external antenna to get caught on clothing or equipment. Includes an earpiece to hear in noisy areas and to keep conversations confidential. 1010/1040 has a lightweight, comfortable swivel earpiece. 1060 has Bluetooth and has a Motorola Bluetooth headset that eliminates the wires. Covers up to 160,000 sq ft and 10 floors, and also works with repeaters/range extenders to increase coverage up to 40%. 90 changeable UHF analog 12.5 narrowband frequencies, also dealer programmable. Voice driven menu for quick access to settings. Includes earpiece, swivel holster with belt clip, charger, 12 hour Li-Ion battery. 3.5" H, 2.4 oz.



CLP1010 UHF 1 watt, 1 chnl, swivel \$219

CLP1040 UHF 1 watt, 4 chnl, swivel \$249

CLP1060 BT, UHF 1 watt, 6 chnl, BT headset \$369

Small & Lightweight

CLS Two-Way Radios have 56 changeable UHF analog 12.5 narrowband frequencies to prevent interference from inexpensive FRS/GMRS models. Display shows battery life and channel. Covers up to 200,000 sq ft and 10 floors. Use earpiece or headset in noisy areas and to keep conversations confidential. Includes swivel holster with belt clip, charger and Li-Ion battery for 12 hours use. 4.1" H, 5 oz.



CLS1110 UHF 1 watt, 1 chnl, display \$189

CLS1410 UHF 1 watt, 4 chnl, display \$209

Compact, Rugged & Durable

RDX 2 Watt Two-Way Radios are 30% louder audio to hear in noisy workplaces. Speaker has low magnetic field to greatly reduce attraction of metal shavings. 89 UHF or 27 VHF analog 12.5 narrowband frequencies. Display models show battery life, channel, name of user and work groups. UHF covers up to 250,000 sq ft and 20 floors, VHF about 25% less. Use earpiece or headset in noisy areas and to keep conversations confidential. Includes belt clip, charger and Li-Ion battery for 12 hours use. 4.5" H, 8.6 oz.



RDU2020 UHF 2 watt, 2 chnl \$245

RDU2080d UHF 2 watt, 8 chnl, display \$290

RDV2020 VHF 2 watt, 2 chnl \$225

RDV2080d VHF 2 watt, 8 chnl, display \$265

Industrial Cordless Phone with Built-in Two-Way Radio



Two devices in one - answer phone calls and use radio to talk to workers. Excellent range and durability. Phone works with multi line phone systems - pick up lines, transfer calls, etc. Phone coverage up to 100,000 sq ft of base. No monthly air time charges. Radio has 56 changeable UHF analog 12.5 narrowband frequencies. Works with other Motorola UHF radios. Radio coverage up to 200,000 sq ft and 10 floors. Use earpiece for hands free operation. Includes phone base, swivel holster with belt clip, charger and Li-Ion battery for 12 hours use. 5.3", 7 oz

CLS1450cB Phone & Radio UHF 1 watt, 4 chnl \$399

Digital, Super High Performance



Digital Two-Way Radios feature Digital Frequency Hopping Spread Spectrum to enhance privacy. Talk to all workers and talk privately to one worker. Send text messages from DTRs or PC. Rugged and durable. Covers up to 350,000 sq ft and 30 floors. Uses license free frequencies, so no FCC license required. Works only with other DTRs. Use earpiece or headset in noisy areas and to keep conversations confidential. Includes swivel holster with belt clip, charger and Li-Ion battery for 14 hours use. 5.2" H, 7.3 oz.

DTR550 Equal to UHF 4 watt, 20 chnl \$355

High Power, Programmable To Work With Other Models & Repeaters



RDX 4 & 5 Watt Two-Way Radios include features of 2 watt RDX and more. Also programmable to work with other models, brands, base stations and repeaters. UHF 4 watt covers up to 300,000 sq ft and 30 floors, VHF 5 watt about 25% less. RDU4160d display shows battery life, channel, name of user and work groups. Includes belt clip, charger and Li-Ion battery for 18 hours use. 4.5" H, 10.3 oz.

RDU4100 UHF 4 watt, 10 chnl \$360

RDU4160d UHF 4 watt, 16 chnl, display \$380

RDV5100 VHF 5 watt, 10 chnl \$325

