




## Features

- Axial/radial leaded
- Fully compatible with current industry standards
- Weldable nickel terminals
- Very low internal resistance
- RoHS compliant\*
- Agency recognition:   

## Applications

Any application that requires extra protection at elevated ambient temperatures, which the 100 °C trip temperature provides.

- Rechargeable battery pack protection
- Cellular phones
- Laptop computers

## MF-LS Series - PTC Resettable Fuses

### Electrical Characteristics

| Model      | V max.<br>Volts | I max.<br>Amps | I <sub>hold</sub>   | I <sub>trip</sub> | Initial<br>Resistance |       | 1 Hour (R <sub>1</sub> )<br>Post-Trip<br>Resistance | Max. Time<br>to Trip |                     | Tripped<br>Power<br>Dissipation |
|------------|-----------------|----------------|---------------------|-------------------|-----------------------|-------|-----------------------------------------------------|----------------------|---------------------|---------------------------------|
|            |                 |                | Amperes<br>at 23 °C |                   | Ohms<br>at 23 °C      |       | Ohms<br>at 23 °C                                    | Amperes<br>at 23 °C  | Seconds<br>at 23 °C | Watts<br>at 23 °C               |
|            |                 |                | Hold                | Trip              | Min.                  | Max.  | Max.                                                |                      |                     | Typ.                            |
| MF-LS180   | 24              | 100            | 1.8                 | 3.8               | 0.040                 | 0.068 | 0.120                                               | 9                    | 2.9                 | 2.0                             |
| MF-LS180L  | 24              | 100            | 1.8                 | 3.8               | 0.040                 | 0.068 | 0.120                                               | 9                    | 2.9                 | 2.0                             |
| MF-LS190   | 24              | 100            | 1.9                 | 4.2               | 0.030                 | 0.057 | 0.100                                               | 10                   | 3.0                 | 1.9                             |
| MF-LS190RU | 15              | 100            | 1.9                 | 4.2               | 0.030                 | 0.057 | 0.100                                               | 10                   | 3.0                 | 1.9                             |
| MF-LS260   | 24              | 100            | 2.6                 | 5.2               | 0.025                 | 0.042 | 0.076                                               | 13                   | 5.0                 | 2.3                             |
| MF-LS300   | 24              | 100            | 3.0                 | 6.3               | 0.015                 | 0.031 | 0.055                                               | 15                   | 4.0                 | 2.0                             |
| MF-LS340   | 24              | 100            | 3.4                 | 6.8               | 0.016                 | 0.027 | 0.050                                               | 17                   | 5.0                 | 2.7                             |

### Environmental Characteristics

|                                                              |                                                             |
|--------------------------------------------------------------|-------------------------------------------------------------|
| Operating/Storage Temperature .....                          | -40 °C to +85 °C                                            |
| Maximum Device Surface Temperature<br>in Tripped State ..... | 125 °C                                                      |
| Passive Aging .....                                          | +85 °C, 1000 hours..... ±10 % typical resistance change     |
| Humidity Aging .....                                         | +85 °C, 85% R.H. 7 days..... ±5 % typical resistance change |
| Vibration .....                                              | MIL-STD-883C,..... No change                                |
| Condition A                                                  |                                                             |

### Test Procedures And Requirements For Model MF-LS Series

| Test                  | Test Conditions                                        | Accept/Reject Criteria                   |
|-----------------------|--------------------------------------------------------|------------------------------------------|
| Visual/Mech. ....     | Verify dimensions and materials .....                  | Per MF physical description              |
| Resistance .....      | In still air @ 23 °C .....                             | R <sub>min</sub> ≤ R ≤ R <sub>1max</sub> |
| Time to Trip .....    | At specified current, V <sub>max</sub> , 23 °C .....   | T ≤ max. time to trip (seconds)          |
| Hold Current .....    | 30 min. at I <sub>hold</sub> .....                     | No trip                                  |
| Trip Cycle Life ..... | V <sub>max</sub> , I <sub>max</sub> , 100 cycles ..... | No arcing or burning                     |
| Trip Endurance .....  | V <sub>max</sub> , 48 hours .....                      | No arcing or burning                     |

|                       |           |
|-----------------------|-----------|
| UL File Number .....  | E 174545S |
| CSA File Number ..... | CA 110338 |
| TUV File Number ..... | R2057213  |

### Thermal Derating Chart - I<sub>hold</sub>/ I<sub>trip</sub> (Amps)

| Model      | Ambient Operating Temperature |             |             |             |             |             |             |             |             |
|------------|-------------------------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|
|            | -40 °C                        | -20 °C      | 0 °C        | 23 °C       | 40 °C       | 50 °C       | 60 °C       | 70 °C       | 85 °C       |
| MF-LS180   | 3.10 / 6.54                   | 2.60 / 5.49 | 2.20 / 4.64 | 1.80 / 3.80 | 1.30 / 2.74 | 1.10 / 2.32 | 0.90 / 1.90 | 0.60 / 1.27 | 0.20 / 0.42 |
| MF-LS180L  | 3.10 / 6.54                   | 2.60 / 5.49 | 2.20 / 4.64 | 1.80 / 3.80 | 1.30 / 2.74 | 1.10 / 2.32 | 0.90 / 1.90 | 0.60 / 1.27 | 0.20 / 0.42 |
| MF-LS190   | 3.30 / 7.29                   | 2.80 / 6.19 | 2.40 / 5.31 | 1.90 / 4.20 | 1.40 / 3.09 | 1.20 / 2.65 | 1.10 / 2.43 | 0.70 / 1.55 | 0.40 / 0.88 |
| MF-LS190RU | 3.30 / 7.29                   | 2.80 / 6.19 | 2.40 / 5.31 | 1.90 / 4.20 | 1.40 / 3.09 | 1.20 / 2.65 | 1.10 / 2.43 | 0.70 / 1.55 | 0.40 / 0.88 |
| MF-LS260   | 4.30 / 8.60                   | 3.70 / 7.40 | 3.10 / 6.20 | 2.60 / 5.20 | 1.90 / 3.80 | 1.60 / 3.20 | 1.40 / 2.80 | 1.10 / 2.20 | 0.60 / 1.20 |
| MF-LS300   | 5.10 / 10.7                   | 4.40 / 9.24 | 3.70 / 7.77 | 3.00 / 6.30 | 2.30 / 4.83 | 1.90 / 3.99 | 1.60 / 3.36 | 1.20 / 2.52 | 0.60 / 1.26 |
| MF-LS340   | 5.50 / 11.0                   | 4.70 / 9.40 | 4.00 / 8.00 | 3.40 / 6.80 | 2.60 / 5.20 | 2.20 / 4.40 | 1.90 / 3.80 | 1.50 / 3.00 | 0.80 / 1.60 |

\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.  
Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.  
Users should verify actual device performance in their specific applications.

# MF-LS Series - PTC Resettable Fuses

**BOURNS®**

## Product Dimensions


| Model      | A               |                 | B               |                 | C              |                 | D              |                | F              |                | Pkg. Style |
|------------|-----------------|-----------------|-----------------|-----------------|----------------|-----------------|----------------|----------------|----------------|----------------|------------|
|            | Min.            | Max.            | Min.            | Max.            | Min.           | Max.            | Min.           | Max.           | Min.           | Max.           |            |
| MF-LS180   | 24.0<br>(0.945) | 26.0<br>(1.024) | 4.9<br>(0.193)  | 5.2<br>(0.205)  | 0.6<br>(0.024) | 1.0<br>(0.039)  | 4.1<br>(0.161) | 5.5<br>(0.217) | 3.8<br>(0.150) | 4.1<br>(0.161) | Std.       |
| MF-LS180L  | 35.0<br>(1.38)  | 37.5<br>(1.48)  | 4.9<br>(0.193)  | 5.6<br>(0.22)   | 0.6<br>(0.024) | 1.0<br>(0.039)  | 9.6<br>(0.38)  | 10.0<br>(0.40) | 3.8<br>(0.150) | 4.2<br>(0.17)  | Std.       |
| MF-LS190   | 21.3<br>(0.839) | 23.4<br>(0.921) | 10.2<br>(0.402) | 11.0<br>(0.433) | 0.5<br>(0.020) | 1.1<br>(0.043)  | 5.0<br>(0.197) | 7.6<br>(0.299) | 4.8<br>(0.189) | 5.4<br>(0.213) | Std.       |
| MF-LS190RU | 19.8<br>(0.780) | 20.8<br>(0.819) | 13.3<br>(0.524) | 14.3<br>(0.563) | 0.4<br>(0.016) | 0.76<br>(0.030) | 8.1<br>(0.319) | 9.5<br>(0.374) | 3.8<br>(0.150) | 4.1<br>(0.161) | RU         |
| MF-LS260   | 24.0<br>(0.945) | 26.0<br>(1.024) | 10.8<br>(0.425) | 11.9<br>(0.469) | 0.6<br>(0.024) | 1.0<br>(0.039)  | 5.0<br>(0.197) | 7.0<br>(0.276) | 5.9<br>(0.232) | 6.1<br>(0.240) | Std.       |
| MF-LS300   | 28.4<br>(1.118) | 31.8<br>(1.252) | 13.0<br>(0.512) | 13.5<br>(0.531) | 0.5<br>(0.020) | 1.1<br>(0.043)  | 6.3<br>(0.248) | 8.9<br>(0.350) | 6.0<br>(0.236) | 6.6<br>(0.260) | Std.       |
| MF-LS340   | 24.0<br>(0.945) | 26.0<br>(1.024) | 14.8<br>(0.583) | 15.9<br>(0.626) | 0.6<br>(0.024) | 1.0<br>(0.039)  | 4.0<br>(0.158) | 5.0<br>(0.197) | 6.0<br>(0.236) | 6.1<br>(0.240) | Std.       |

Packaging: Bulk - 500 pcs. per bag.  
Tape and Reel - Consult factory.

NOTE: Longer lead option available. Consult factory.


DIMENSIONS:  $\frac{\text{MM}}{(\text{INCHES})}$

**Standard Style**




Terminal material: quarter-hard nickel

**"RU" Style**



## Typical Part Marking

Represents total content. Layout may vary.



Specifications are subject to change without notice.


The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

## MF-LS Series - PTC Resettable Fuses

**BOURNS®**

### Typical Time to Trip at 23 °C

MF-LS models offer trip temperatures lower than MF-S models for extra protection at elevated temperatures.



### How to Order

**MF - LS 180**  
 Multifuse® Product Designator \_\_\_\_\_  
 Series \_\_\_\_\_  
 LS = Axial Leaded "Strap" Component  
 Hold Current,  $I_{hold}$  \_\_\_\_\_  
 180-340 (1.8 Amps - 3.40 Amps)  
 Lead Option \_\_\_\_\_  
 RU = Radial Lead Option

MF-LS, REV. M, 05/15

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.