




VECTORBORD® CIRCBORD™.... PART NO. : 45P80-2



Description :

4.5" x 8.08", Hole Dia.: 0.042", Grid: 0.100" x 0.100"

Pad-Per-Hole 2 Sides

Top / Bottom row on 0.200" pitch with no plating.

Isolated 0.085" square pads around each hole

Ground plane are identical on both sides and holes are plated thru


Circuit Pattern : Pad-Per-Hole 2 Sides , Holes plated thru

Contacts : N/A

16 Pin DIP Capacity : 80

Hole Diameter : 0.042" { 1.0668 mm }

Grid : 0.100" x 0.100" { 2.54mm X 2.54mm }



Dimension { H, W, T } :	4.5" x 8.08" x 0.062"
Material :	CEM-1
Wire-Wrap Terminals :	T44, T46, T49, T68
Solder Terminals :	T42-1
Wire-Wrap Socket Pins :	R32
NEMA Grade :	CEM-1
UL Flammability Class :	94V - 0

email us your requirements : inquire@vectorelect.com

11115 Vanowen St., North Hollywood, CA 91605, USA

Tel.: (818) 985 8208, (800) 423 5659; Fax : (818) 985 7708

Circbord®, Vectorbord® and VectorPak® are registered trademarks of Vector Electronics & Technology, Inc.
CompactPCI® is a registered trademark of PCIMG. © 2001 Vector Electronics & Technology, Inc. - All Rights Reserved