






MATERIAL NO.	NUMBER OF CIRCUITS "XX"	DIM. "A"	DIM. "B"
39960-0103	03	24.9 [1.98]	16.00 [1.630]
39960-0104	04	32.9 [1.30]	24.00 [1.945]
39960-0105	05	40.9 [1.61]	32.00 [1.260]
39960-0106	06	48.9 [1.93]	40.00 [1.575]
39960-0107	07	56.9 [2.24]	48.00 [1.890]
39960-0108	08	64.9 [2.56]	56.00 [2.205]
39960-0109	09	72.9 [2.87]	64.00 [2.520]
39960-0110	10	80.9 [3.19]	72.00 [2.835]
39960-0111	11	88.9 [3.50]	80.00 [3.150]
39960-0112	12	96.9 [3.82]	88.00 [3.465]



SECTION Z-Z



PTH PATTERN

NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: NONE
6. ALL CREEP DISTANCES FOR UL 1059, CLASS C, 600V GENERAL INDUSTRIAL.
7. FOR USE WITH #22-#10 AWG SOLID AND STRANDED WIRES.
8. TORQUE RATING IS 7 IN.-LB.
9. "XX" REFERS TO THE NUMBER OF CIRCUITS.

6	XX/2	REAR TERMINAL	BRASS	TIN
5	XX/2	FRONT TERMINAL	BRASS	TIN
4	XX	CAGE	BRASS	NICKEL
3	XX	SCREW, M3.5 X 0.6	BRONZE	TIN
2	I	COVER	THERMOPLASTIC	BLACK
1	I	BODY	THERMOPLASTIC	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

EC NO. ECN 3920
 DRWN: JF 12-20-04
 CHK: K1
 APPR:

QUALITY
 SYMBOLS
 MAJOR
 CRITICAL
 C

GENERAL TOLERANCES: (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES		±.0015
3 PLACES	±.038	±.005
2 PLACES	±.13	±.01
1 PLACE	±.3	
ANGULAR: ±2°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

SCALE 3:2	DESIGN UNITS ☐ mm ☒ INCH
DRAWN BY & DATE GHR 3-19-02	
CHECKED BY & DATE A. PLAZA 6-18-02	
APPROVED BY & DATE L. ROTHBAUS 6-18-02	
CAD FILENAME 9605-XX	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	

THIRD ANGLE PROJECTION		DIMENSIONS: ☒ mm ☐ INCH ☐ mm ONLY		SHT	REV
TITLE: SR BTS, PKT, #10 AWG, ASSY 600V, 30A		MATERIAL NO. SEE CHART		DRAWING NO. SD-39960-002	SHEET NO. 1 OF 1
MOLEX INCORPORATED		SIZE B			