




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECO-14-005178	11APR2014	AP	MH



ISOMETRIC VIEWS
SCALE 3:1



- 1 MATERIAL:
HOUSING: THERMOPLASTIC, FLAMMABILITY RATING UL94 V-0
CONTACT: COPPER ALLOY
2. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION, 108-2375; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
SEE TE PRODUCT SPECIFICATION 108-2375 FOR TEST SEQUENCES.
- 3 ROWS GA THRU GE (SHOWN DARKENED) ARE TYPICALLY USED AS GROUNDS.
- 4 SPECIFIED POSITIONAL TOLERANCE DEFINES HOLE TO HOLE LOCATION WITHIN HOLE PATTERN. POSITIONAL TOLERANCE OF HOLE PATTERN TO FIDUCIAL MARKS OR PCB DATUMS SHALL BE DEFINED BY CUSTOMER.
- 5 AREA RESERVED FOR TE CONNECTIVITY LOGO.
- 6 AREA RESERVED FOR PART NUMBER (X-XXXXXX-X) AND DATE CODE (YYWW).
- 7 USE CENTER LINES INDICATED ON PCB HOLE PATTERN TO ESTABLISH ALIGNMENT BETWEEN HEADER AND RECEPTACLE BOARDS.
- 8 PLATED THROUGH HOLE REQUIREMENTS - SIGNAL:
HOLE SIZE PRIOR TO PLATING = $\varnothing 0.420 \pm 0.013$
COPPER PLATING THICKNESS = 0.038 ± 0.013
CALCULATED FINISHED HOLE SIZE = $\varnothing 0.344 \pm 0.039$
THESE DIMENSIONS APPLY TO THE TOP 1.25mm OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE.
- 9 PLATED THROUGH HOLE REQUIREMENTS - POWER:
HOLE SIZE PRIOR TO PLATING = $\varnothing 0.700 \pm 0.025$
COPPER PLATING THICKNESS = 0.038 ± 0.013
CALCULATED FINISHED HOLE SIZE = $\varnothing 0.624 \pm 0.051$
THESE DIMENSIONS APPLY TO THE TOP 1.50mm OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE.


SIZE 2 HALF WIDE W/GUIDE POSTS *
24 DIFFERENTIAL PAIRS + GROUNDS
83 TOTAL SIGNAL CONTACTS
6 POWER CONTACTS

* SIZE 1 AND SIZE 3 ARE ALSO AVAILABLE

THIS PRODUCT HAS NOT
COMPLETED VALIDATION AND
QUALIFICATION TESTING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN HAMNER 03JUN2011	TE Connectivity	
DIMENSIONS:		CHK D. TROUT 07JUN2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. FEEDER 07JUN2011	NAME	
	0 PLC ±°	PRODUCT SPEC	RECEPTACLE ASSEMBLY, HALF-WIDE, 24/83/6P, STRADA MESA MEZZANINE CONNECTOR	
	1 PLC ±°	108-2375		
	2 PLC ±0.13	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
	3 PLC ±0.013	114-13249	A100779C=2180761	
	4 PLC ±°	WEIGHT	RESTRICTED TO	
	ANGLES ±°	-	-	
	FINISH	-	-	
MATERIAL	△	Customer Drawing	SCALE 6:1	SHEET 1 OF 3 REV A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




PCB LAYOUT AND PIN IDENTIFICATION 
SHOWN FROM CONNECTOR SIDE
SCALE 9:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±"

1 PLC ±"

2 PLC ±0.13

3 PLC ±0.013

4 PLC ±"

ANGLES ±1

FINISH

WEIGHT

-

-

DWN HAMNER 03JUN2011

CHK D. TROUT 07JUN2011

APVD J. FEEDER 07JUN2011

PRODUCT SPEC 108-2375

APPLICATION SPEC 114-13249

Customer Drawing

TE Connectivity

RECEPTACLE ASSEMBLY, HALF-WIDE, 24/83/6P, STRADA MESA MEZZANINE CONNECTOR

SIZE A1 CAGE CODE 00779 DRAWING NO. 2180761


RESTRICTED TO -

SCALE 6:1


SHEET 2 OF 3

REV A

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-



PCB HOLE PATTERN
SHOWN FROM CONNECTOR SIDE
SCALE 7:1



DETAIL A
6X
SCALE 20:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN HAMNER 03JUN2011	TE Connectivity		
DIMENSIONS:		CHK D. TROUT 07JUN2011			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. FEDDER 07JUN2011	NAME	RECEPTACLE ASSEMBLY, HALF-WIDE, 24/83/6P, STRADA MESA MEZZANINE CONNECTOR	
	0 PLC ±	PRODUCT SPEC	SIZE	114-13249	
	1 PLC ±0.13	APPLICATION SPEC	CAGE CODE	2180761	
	2 PLC ±0.013	WEIGHT	DRAWING NO	A100779	
	3 PLC ±	Customer Drawing	RESTRICTED TO	-	
	4 PLC ±		SCALE	6:1	
MATERIAL	FINISH		SHEET	3	OF 3
-	-		REV	A	