




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. TO BE USED WITH PANDUIT STAINLESS STEEL BANDING MBS-MR & MBS-TLR.
2. APPLICATION TOOL: GS4MT, PPTMT, ST2MT, ST3MT AND HTMT.
3. TOOL TENSION SETTING: 1 TO 4 (GS4MT & PPTMT TOOLS ONLY).
4. DIMENSIONS IN [] ARE MILLIMETERS.
5. MINIMUM LOOP TENSILE STRENGTH: 100 lbs. [445 N].
6. TOLERANCES: .XXX = $\pm .010$ [.254]
.XX = $\pm .02$ [.508]
.X = $\pm .03$ [.762]
ANGLES = $\pm 2^\circ$

(A)



							TITLE					
							METAL LOCKING TIE HEAD STANDARD PART # MTHS-C					
							CUSTOMER DRAWING					
							ITEM REVISION NAME			PANDUIT		
							N41145BS/02					
							DATASET FILE NAME			MATERIAL:		
							N41145BS/02					
02A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO. ORIG CAD FILE SPEC WAS S41145_01	SSECN01042	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.127] .XX ± .01 [.25] ANGLES ± 5 ° THIRD ANGLE PROJECTION			304 STAINLESS STEEL		
01	10/03	BRH	DPN	JJB	Ⓐ ADDED ST3MT TO APPLICATION TOOL NOTE	11162						
00	8/03	JAMB	DPN	JJB	DRAWING RELEASED	10938						
										N41145BS_DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE	
							JAMB	8-13-03	DPN	4:1	A	