


REV	DOCUMENT	CHANGED BY	CHECK
10	0038090	VS 28APR08	BLR



NOTE

1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS

2 - TERMINALS ARE PLATED FOR SOLDERING

3 - MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.	PR-3639
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	VK	27 NOV 07		Honeywell TITLE SWITCH - BASIC				
OPERATING FORCE — — — — 3 - 5 OZ		CONTACT ARRANGEMENT S P D T						CHECK	RJ	27 NOV 07						
RELEASE FORCE— — — — — 1 OZ MIN		30 VOLTS DC RATING			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE B	TYPE I	DRAWING NAME		REV 10
DIFFERENTIAL TRAVEL— — — .004 MAX			SEA LEVEL	50,000 FT										11SM23-H4		
OVERTRAVEL — — — — — .005 MIN		INDUCTIVE	1/2 AMP	1/2 AMP												
		RESISTIVE	1 AMP	1 AMP												
		MAXIMUM INRUSH 2 AMP										SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1	
		APPROVALS	KEMA, CE	1A, 250V ~ T85 1E4		CE										
			UL, CSA	1A, 125 VAC		BRAND L 22										