



Side entry hoods with knurled screws

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm
----------------	-----------------	----------	---------	------------------

D-Sub



Hood¹⁾
grey thermoplastic
RAL 7032

9	09 67 009 0571
15	09 67 015 0571
25	09 67 025 0571
37	09 67 037 0571
50	09 67 050 0571

Upper hood part

Lower hood part



9 contacts



grey thermoplastic
with internal
tin-plate screening

9	09 67 009 0573
15	09 67 015 0573
25	09 67 025 0573
37	09 67 037 0573
50	09 67 050 0573

15 – 50 contacts



9-37 way
for packaging density
of 3 TE (15.24 mm)


	a max.	b min.	c	d	e	f
15	39.62	28.40	13.00	14.00	1.00	7.50
25	53.52	42.20	13.00	14.00	1.00	7.50
37	69.80	58.65	13.00	14.00	1.00	7.50
50	67.41	56.18	16.00	17.50	1.50	9.50

Knurled screw

Thread UNC
Thread M3

9-50

09 67 000 9971²⁾
09 67 001 9965*




Grey head / Nickel plated steel

Thread UNC
Thread M3

9-50

09 67 001 9978
09 67 001 9977



Full metal part

Tooling
for assembly
of hoods

Top part
Bottom part

09 99 000 0215*
09 99 000 0216*



3) Screw driver type ISO PH 1 for philips screw No 1 ISO norm 4757
Operating temperature for all hoods on this page: -30 °C ... +100 °C

* Not normally kept in stock
1) Order knurled screw separately
2) 9 way 1 per hood – 15-50 way 2 per hood