


Aufbau	
Hutmutter	Polyamid PA6 V-2
Dichtring	Polychloropren-Nitrilkautschuk CR/NBR
Zwischenstutzen	Polyamid PA6 V-2
Anschlussgewinde	Pg, nach DIN 40430

Eigenschaften	
	mit Biegeschutzspirale, für bewegliche, flexible Leitungen, integrierte Zugentlastung, großer Dicht- und Klemmbereich, montagefreundlich
Temperaturbereich	-20°C / +100°C
Schutzart	IP68 - 5 bar
Prüfnorm	UL 514B
UL / CSA-File	E140310
Hinweis	Angaben zu den einzelnen Prüfungen siehe Anhang

Configuration	
Dome nut	Polyamide PA6 V-2
Sealing ring	Polychloroprene-Nitrile rubber CR/NBR
Gland body	Polyamide PA6 V-2
Connecting thread	Pg as per DIN 40430

Properties	
	with spiral top, for movable flexible cables, integrated anchorage, wide sealing and clamping range, easy-to-install
Temperature range	-20°C / +100°C
Protection grade	IP68 - 5 bar
Test standard	UL 514B
UL / CSA-File	E140310
Comment	details about test standards see annex


Merkmale

Anschlussgewinde Standardlänge						
A	ØC mm	L mm	SW1 mm	SW2 mm	H mm	
Pg 7	3 - 6,5	8	15	15	63	100
Pg 9	4 - 8	8	19	19	74	100
Pg 11	5 - 10	8	22	22	87	100
Pg 13,5	6 - 12	9	24	24	98	50
Pg 16	10 - 14	10	27	27	112	25
Pg 21	13 - 18	11	33	33	130	25

Characteristics

Connecting thread standard length				
		RAL 7001 silbergrau silver grey	RAL 7035 lichtgrau light grey	RAL 9005 tiefschwarz jet black
		Art.-Nr. / Part No.	Art.-Nr. / Part No.	Art.-Nr. / Part No.
Pg 7	50.007 PA/BS	50007PABS7035	50.007 PABSSW	
Pg 9	50.009 PA/BS	50009PABS7035	50.009 PABSSW	
Pg 11	50.011 PA/BS	50011PABS7035	50.011 PABSSW	
Pg 13,5	50.013 PA/BS	50013PABS7035	50.013 PABSSW	
Pg 16	50.016 PA/BS	50016PABS7035	50.016 PABSSW	
Pg 21	50.021 PA/BS	50021PABS7035	50.021 PABSSW	