


PNP/NPN HIGH VOLTAGE SILICON TRANSISTORS



2N5679	2N5681
2N5680	2N5682
PNP	NPN
TO-39	TO-39

These Are High Voltage & High Current, General Purpose Transistors

ABSOLUTE MAXIMUM RATINGS.

DESCRIPTION	SYMBOL	2N5679	2N5680	UNITS
		2N5681	2N5682	
Collector -Emitter Voltage	VCEO	100	120	V
Collector -Base Voltage	VCBO	100	120	V
Emitter -Base Voltage	VEBO		4.0	V
Collector Current Continuous	IC		1.0	A
Base Current	IB		0.5	A
Power Dissipation @ Ta=25 degC	PD		1.0	W
Derate Above 25deg C			5.7	mW/deg C
Power Dissipation @ Tc=25 degC	PD		10	W
Derate Above 25deg C			57	mW/deg C
Operating And Storage Junction	T _j , T _{stg}		-65 to +200	deg C
Temperature Range				
<u>THERMAL RESISTANCE</u>				
Junction to Case	R _{th(j-c)}		17.5	deg C/W
Junction to Ambient	R _{th(j-a)}		175	deg C/W


ELECTRICAL CHARACTERISTICS (Ta=25 deg C Unless Otherwise Specified)

DESCRIPTION	SYMBOL	TEST CONDITION	2N5679	2N5680	UNITS
			2N5681	2N5682	
Collector -Emitter Voltage	VCEO(sus)	IC=10mA, IB=0	>100	>120	V
Collector-Cut off Current	ICBO	VCB=100V, IE=0	<1.0	-	uA
		VCB=120V, IE=0	-	<1.0	uA
	ICEO	VCE=70V, IB=0	<10	-	uA
		VCE=80V, IB=0	-	<10	uA
	ICEX	VCE=100V, VEB=1.5V	<1.0	-	uA
		VCE=120V, VEB=1.5V	-	<1.0	uA
TC=150 deg C					
		VCE=100V, VEB=1.5V	<1.0	-	mA
		VCE=120V, VEB=1.5V	-	<1.0	mA
Emitter-Cut off Current	IEBO	VEB=4V, IC=0	<1.0	<1.0	uA

ELECTRICAL CHARACTERISTICS (Ta=25 deg C Unless Otherwise Specified)				2N5679-82	
DESCRIPTION	SYMBOL	TEST CONDITION	2N5679 2N5681	2N5680 2N5682	UNITS
DC Current Gain	hFE*	IC=1A, VCE=2V IC=250mA, VCE=2V	>5.0 40-150	- 40-150	
Collector Emitter Saturation Voltage	VCE(Sat)*	IC=250mA, IB=25mA IC=500mA, IB=50mA IC=1A, IB=200mA	<0.60 <1.0 <2.0	<0.60 <1.0 <2.0	V V V
Base Emitter on Voltage	VBE(on)*	IC=250mA, VCE=2V	<1.0	<1.0	V
SMALL SIGNAL CHARACTERISTICS					
Small Signal Current Gain	hfe	IC=200mA, VCE=1.5V f=1kHz	>20	>20	
Out-Put Capacitance	Cob	VCB=20V, IE=0 f=1MHz	<50	<50	pF
Transistors Frequency	ft	IC=100mA, VCE=10V f=10MHz	>30	>30	MHz



*Pulse Test: Pulse Width: =300us, Duty Cycle=2%

TO-39 Metal Can Package



DIM	MIN	MAX
A	8.50	9.39
B	7.74	8.50
C	6.09	6.60
D	0.40	0.53
E	—	0.88
F	2.41	2.66
G	4.82	5.33
H	0.71	0.86
J	0.73	1.02
K	12.70	—
L	42 DEG	48 DEG

All dimensions are in mm



PIN CONFIGURATION
1. Emitter
2. Base
3. Collector

Packing Detail

PACKAGE	STANDARD PACK		INNER CARTON BOX		OUTER CARTON BOX		
	Details	Net Weight/Qty	Size	Qty	Size	Qty	Gr Wt
TO-39	500 pcs/polybag	540 gm/500 pcs	3" x 7.5" x 7.5"	20.0K	17" x 15" x 13.5"	32.0K	40 kgs

