

PART NUMBER CODING SFH210-PP C-D -ID-BK

COLOR
BK= BLACK

NUMBER OF POSITIONS
(CONTACTS PER ROW)





PLATING
(SEE PLATING TABLE)

PLATING TABLE




CONTACT SURFACE	TERMINATION
P = GOLD FLASH	GOLD FLASH
V = GOLD FLASH	NICKEL
K = .000015" GOLD	NICKEL
J = .000015" GOLD	GOLD FLASH
E = .000100" PURE TIN, MATTE	.000100" PURE TIN, MATTE

REVISIONS


REV.	ECO. NO	DESCRIPTION	DATE	BY
A	1930	INITIAL RELEASE	3/17/2009	JH




(POSITION 07 THRU 25)




(POSITION 03)



(POSITION 05)



(POSITION 04)



(POSITION 06)

PART NUMBER	POSITIONS/ CONTACTS	A		B		D	
		INCH	MM	INCH	MM	INCH	MM
SFH210-PP C-D03-ID-BK	03/06	0.200	5.08	0.480	12.18	0.075	1.90
SFH210-PP C-D04-ID-BK	04/08	0.300	7.62	0.580	14.72		
SFH210-PP C-D05-ID-BK	05/10	0.400	10.16	0.680	17.26		
SFH210-PP C-D06-ID-BK	06/12	0.500	12.70	0.780	19.80		
SFH210-PP C-D07-ID-BK	07/14	0.600	15.24	0.880	22.34		
SFH210-PP C-D08-ID-BK	08/16	0.700	17.78	0.980	24.88		
SFH210-PP C-D09-ID-BK	09/18	0.800	20.32	1.080	27.42		
SFH210-PP C-D10-ID-BK	10/20	0.900	22.86	1.180	29.96		
SFH210-PP C-D12-ID-BK	12/24	1.100	27.94	1.380	35.04		
SFH210-PP C-D13-ID-BK	13/26	1.200	30.48	1.480	37.58		
SFH210-PP C-D15-ID-BK	15/30	1.400	35.56	1.680	42.66		
SFH210-PP C-D17-ID-BK	17/34	1.600	40.64	1.880	47.74		
SFH210-PP C-D20-ID-BK	20/40	1.900	48.26	2.180	55.36		
SFH210-PP C-D25-ID-BK	25/50	2.400	60.96	2.680	68.06		
POSITION 30 & 32:	30/60	SEE SHEET 2 FOR DIMENSIONS					
SEE SHEET 2 FOR P/N	32/64						

- NOTES:**
1. INSULATOR MATERIAL: PBT 30% GLASS FIBER.
 2. CONTACT MATERIAL: PHOSPHOR BRONZE.
 3. OPERATING TEMPERATURE: -40°C TO +105°C.
 4. UL FLAMMABILITY RATING: 94V-0.
 5. CURRENT RATING: 1 AMP.
 6. INSULATION RESISTANCE: 3,000M OHMS MIN.
 7. CONTACT RESISTANCE: 30m OHMS MAX.
 8. DIELECTRIC WITHSTANDING: 500 VAC.
 9. MATES WITH SBH11 SERIES
 10. FOR 1.27mm PITCH FLAT RIBBON CABLE.







RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES[MM]
TOLERANCES:
ANGULAR: ± 30°
XX = ± .01 [3]
XXX = ± .008 [20]
XXXX = ± .0040 [100]
SURFACE FINISH: 63 Ra
REMOVE ALL BURRS AND SHARP EDGES .010 MAX.
INTERPRET DIMENSIONS AND GEOMETRIC
TOLERANCING
PER: ANSI Y14.5M-1994



DRAWN	DATE	NAME
3/19/09	JH	

THE INFORMATION HEREIN CONTAINS
PROPRIETARY INFORMATION OF
SULLINS ELECTRONICS AND IS NOT
TO BE REPRODUCED, USED OR
DISCLOSED TO OTHERS FOR ANY
PURPOSE EXCEPT AS SPECIFICALLY
AUTHORIZED IN WRITING BY AN
OFFICER OF SULLINS ELECTRONICS.

SULLINS CONNECTOR SOLUTIONS	
DESCRIPTION: IDC SOCKET, .100" CC/RS	
PART NUMBER SFH210-PP C-D -ID-BK	
SIZE C	DWG. NO. 11222
SCALE: NTS	REV A



(POSITION 30 & 32)



PART NUMBER	POSITIONS/ CONTACTS	A		B		D	
		INCH	MM	INCH	MM	INCH	MM
POSITION 03 THRU 25: SEE SHEET 1 FOR PART NUMBERS	03/06	SEE SHEET 1 FOR DIMENSIONS					
	04/08						
	05/10						
	06/12						
	07/14						
	08/16						
	09/18						
	10/20						
	12/24						
	13/26						
	15/30						
	17/34						
	20/40						
	25/50						
SFH210-PP_C-D30-ID-BK	30/60	2.900	73.66	3.179	80.74	0.138	3.50
SFH210-PP_C-D32-ID-BK	32/64	3.100	78.74	3.379	85.82		

- NOTES:
1. INSULATOR MATERIAL: PBT 30% GLASS FIBER.
 2. CONTACT MATERIAL: PHOSPHOR BRONZE.
 3. OPERATING TEMPERATURE: -40°C TO +105°C.
 4. UL FLAMMABILITY RATING: 94V-0.
 5. CURRENT RATING: 1 AMP.
 6. INSULATION RESISTANCE: 3,000M OHMS MIN.
 7. CONTACT RESISTANCE: 30m OHMS MAX.
 8. DIELECTRIC WITHSTANDING: 500 VAC.
 9. MATES WITH SBH11 SERIES
 10. FOR 1.27mm PITCH FLAT RIBBON CABLE.



RoHS COMPLIANT

		DESCRIPTION	
		HEADER FEMALE, .100" CC/RS	
PART NUMBER		SFH210-PP_C-D_--ID-BK	
SIZE	DWG. NO.	REV	
C	11222	A	
SCALE: NTS		SHEET 2 OF 2	