

Philips screwdriver - SF-PH 0-60 - 1212558

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Screwdriver, PH crosshead, size: PH 0 x 60, 2-component grip, with non-slip grip



The figure shows the SF-PH 2-100 version

Product Features

- VDE approval
- Screwdrivers for Phillips screws with Pozidriv and Phillips Recess screw head



Key commercial data

| | |
|--------------------------------------|----------------|
| Packing unit | 1 PCE |
| Weight per Piece (excluding packing) | 42.0 GRM |
| Custom tariff number | 82054000 |
| Country of origin | Czech Republic |

Technical data

Dimensions

| | |
|--------------|--------|
| Length (b) | 161 mm |
| Width (a) | 26 mm |
| Blade height | 80 mm |

General

| | |
|---------------|--------------------|
| Design | Phillips |
| Type | Straight |
| Material | Alloyed tool steel |
| Test standard | DIN ISO 8764-1 |

Philips screwdriver - SF-PH 0-60 - 1212558

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 21040401 |
| eCl@ss 4.1 | 21040401 |
| eCl@ss 5.0 | 21040401 |
| eCl@ss 5.1 | 21040401 |
| eCl@ss 6.0 | 21040401 |
| eCl@ss 7.0 | 21040409 |
| eCl@ss 8.0 | 21040409 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000144 |
| ETIM 5.0 | EC000144 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 27111701 |
| UNSPSC 7.0901 | 27111701 |
| UNSPSC 11 | 27111701 |
| UNSPSC 12.01 | 27111701 |
| UNSPSC 13.2 | 27111701 |

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

| |
|--|
| GOST  |
|--|

Philips screwdriver - SF-PH 0-60 - 1212558

Drawings

Pictogram



© Phoenix Contact 2013 - all rights reserved

<http://www.phoenixcontact.com>