

Si photodiode

S9032-02

RGB color sensor



S9032-02 is a color sensor molded into a plastic package having a 3-channel (RGB) photodiode sensitive to the blue ($\lambda_p=460$ nm), green ($\lambda_p=540$ nm) and red ($\lambda_p=620$ nm) regions of the spectrum. S9032-02 has a 3-segment (RGB) circular active area of $\phi 2$ mm.

Features

- 3-channel (R, G, B) Si photodiode
- Surface-mount small plastic package
- Spectral response range close to the human eye sensitivity
- No sensitivity in the near IR region
- Active area: 3-segment (RGB) circular active area of $\phi 2$ mm

Applications

- Color adjustment for LED back light system for LCD
- Color adjustment for LCD projector
- Color tester
- Color detection


■ Absolute maximum ratings

Parameter	Symbol	Value	Unit
Reverse voltage	V_R Max	10	V
Operating temperature	T_{opr}	-25 to +85	°C
Storage temperature	T_{stg}	-40 to +100	°C

■ Electrical and optical characteristics ($T_a = 25$ °C, per element)


Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Spectral response range	λ	Blue	-	400 to 540	-	nm
		Green	-	480 to 600	-	
		Red	-	590 to 720	-	
Peak sensitivity wavelength	λ_p	Blue	-	460	-	nm
		Green	-	540	-	
		Red	-	620	-	
Photo sensitivity	S	$\lambda = \lambda_p$ Blue	0.13	0.18	-	A/W
		Green	0.18	0.23	-	
		Red	0.11	0.16	-	
Dark current	I_D	$V_R = 1$ V All elements	-	5	100	pA
Temperature coefficient of I_D	T_{CID}		-	1.12	-	times/°C
Rise time	t_r	$V_R = 0$ V, $R_L = 1$ k Ω 10 to 90 %	-	0.2	-	μ s
Terminal capacitance	C_t	$V_R = 0$ V $f = 10$ kHz	-	40	80	pF

■ Spectral response




KSPDB0246EA

■ Dark current vs. reverse voltage




KSPDB0218EA

■ Terminal capacitance vs. reverse voltage



KSPDB0219EA

■ Dimensional outline (unit: mm)



Tolerance unless otherwise noted: ±0.1, ±2°
Shaded area indicates burr.

Chip position accuracy with respect to the package dimensions marked *
X, Y ≤ ±0.2, θ ≤ ±2°

KSPDA0162EA

HAMAMATSU

HAMAMATSU PHOTONICS K.K., Solid State Division

1126-1 Ichino-cho, Hamamatsu City, 435-8558 Japan, Telephone: (81) 053-434-3311, Fax: (81) 053-434-5184, <http://www.hamamatsu.com>

U.S.A.: Hamamatsu Corporation: 360 Foothill Road, P.O.Box 6910, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1) 908-231-0960, Fax: (1) 908-231-1218

Germany: Hamamatsu Photonics Deutschland GmbH: Arzbergerstr. 10, D-82211 Herrsching am Ammersee, Germany, Telephone: (49) 08152-3750, Fax: (49) 08152-2658

France: Hamamatsu Photonics France S.A.R.L.: 8, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: 33-(1) 69 53 71 00, Fax: 33-(1) 69 53 71 10

United Kingdom: Hamamatsu Photonics UK Limited: 2 Howard Court, 10 Tewin Road, Welwyn Garden City, Hertfordshire AL7 1BW, United Kingdom, Telephone: (44) 1707-294888, Fax: (44) 1707-325777

North Europe: Hamamatsu Photonics Norden AB: Smidesvägen 12, SE-171 41 Solna, Sweden, Telephone: (46) 8-509-031-00, Fax: (46) 8-509-031-01

Italy: Hamamatsu Photonics Italia S.R.L.: Strada della Moia, 1/E, 20020 Arese, (Milano), Italy, Telephone: (39) 02-935-81-733, Fax: (39) 02-935-81-741

Cat. No. KSPD1067E01
Sep. 2003 DN