






PRODUCT NUMBER	DESCRIPTION
88917-101 & -101LF	HEAT STAKE VERSION

FRONT VIEW



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE





NOTE:

- HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
- INDICATED HOLES ARE UNPLATED
- PART NUMBER WITH "LF" SUFFIX AT THE END ARE LEAD FREE OPTION
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD OR FOR 10-20
SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW
OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family METRAL ACC.
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
F	C80040	MDF		7/23/98	angles	xx ±.01/.3	RECEPTACLE GUIDE MODULE, 4 ROW
G	H80473	MDF		7/23/98	linear	xxx ±.005/.13	
H	V02701	JWS		10/19/00	0°±2'	xxxx ±.0020/.050	scale 1:1
J	V11668	LSS		6/13/01	dr	S. STONER	9/30/93
K	V12868	CGD		1/02/02	enr	R. DOUTRICH	9/30/93
L	M05-0262	MHT		12/20/05	chr	S. STONER	9/30/93
M	M06-0286	MNR		7/27/06	appd	S. STONER	9/30/93
sheet	revision	M	M	M	M		
index	sheet	1	2	3	4		

PRODUCT NUMBER	DESCRIPTION
88917-201 & -201LF	PRESS-PEG VERSION

FRONT VIEW




REQUIRED PC BOARD LAYOUT
COMPONENT SIDE

NOTE:





- HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
- INDICATED HOLES ARE UNPLATED
- PART NUMBER WITH "LF" SUFFIX AT THE END ARE LEAD FREE OPTION
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD OR FOR 10-20
SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW
OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family METRAL ACC.
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
M					angles	linear	RECEPTACLE GUIDE MODULE, 4 ROW
					0°±2'	xxx ±.01/.3 xxx ±.005/.13 xxxx ±.0020/.050	scale 1:1
			dr	S. STONER	9/30/93		dwg no
			enr	R. DOUTRICH	9/30/93		sheet2 of 4
			chr	S. STONER	9/30/93		size
			appd	S. STONER	9/30/93		A3
sheet	revision						type
index	sheet						Product Customer Drawing



PRODUCT #	DESCRIPTION
88917-401 & -401LF	CLAW RETENTION VERSION

FRONT VIEW



REQUIRED P.C. BOARD LAYOUT
COMPONENT SIDE

NOTES:

- HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
- INDICATED HOLES ARE UNPLATED.

③ PART NUMBER WITH "LF" SUFFIX AT THE END ARE LEAD FREE OPTION

- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD OR FOR 10-20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family METRAL ACC.
ltr	ec	no	dr	date	tolerances unless otherwise specified		title
M					angles	linear	RECEPTACLE GUIDE MODULE, 4 ROW
					0°±2'	xxx ±.01/.3 xxx ±.005/.13 xxxx ±.0020/.050	mm
					dr	S. STONER 9/30/93	scale 1:1
					enr	R. DOUTRICH 9/30/93	FCI
					chr	S. STONER 9/30/93	dwg no
					appd	S. STONER 9/30/93	88917
sheet	revision						type Product Customer Drawing
index	sheet						