


REVISION			
REV	DESCRIPTION	DATE	APPROVED
C1	REVISED PER ECO-14-016154	10/23/14	I. MYONG
D	REVISED PER ECO-15-002339	02/18/15	H. SMITH



STXR40 TINEL-LOCK ADAPTER

NOTES:

1. THIS PRODUCT IS DESIGNED TO TERMINATE A BRAIDED CABLE SHIELD AND A HEAT SHRINKABLE LIPPED BOOT TO A CONNECTOR. SEE NOTE 6 BELOW.
2. SEE SHEET 3 FOR TABLES OF DIMENSIONS, AND REFER TO CH00-0250-008 FOR PART ORDERING INFORMATION.
3. SEE DRAWING TR FOR DETAIL ON TINEL-LOCK RING. RINGS ARE DESIGNATED TO BE HEATED ELECTRICALLY. ALL RINGS ARE MARKED WITH THERMOCHROMIC PAINT WHICH CHANGES COLOR WHEN INSTALLATION TEMPERATURE IS REACHED.
4. ADAPTER TO BE PERMANENTLY MARKED WITH CODE IDENTIFICATION NUMBER AND PART NUMBER LESS RING DESIGNATOR. (e.g. 06090-STXR40AB00-2018). RING SHALL BEAR NO MARKING.
5. TINEL-LOCK RING ENTRY SIZE AND BRAID DESIGNATOR IS TO BE SPECIFIED IN PART NUMBER WHEN ORDERING.
6. ADAPTER MATES TO: MIL-DTL-38999L SERIES III AND IV, CLASS C, F, K, AND W, D38999/20, /24, /26, /40, /46, /47 CONNECTORS, WHEN SO MATED IT SHALL PROVIDE A WATER-TIGHT SEAL MEETING THE REQUIREMENTS OF SAE-AS85049, PARA 3.5.7.
7. FOR MODIFICATIONS, ALTERNATIVE MATERIALS AND FINISHES NOT SHOWN CONTACT TYCO ELECTRONICS.
8. PREFIX "S" DENOTES THAT THE ADAPTER HAS A LARGE ENTRY THAN THE STANDARD TXR BUT IS STILL OF THE TYPE I DESIGN.
9. SEE SHEET 3 FOR TABLE OF ENTRY SIZE APPLICABLE TO THE STXR RANGE. FOR ENTRY SIZES LARGER THAN MAX INDICATED, CONTACT TE.

© 2015 Tyco Electronics Corporation. All rights reserved. Raychem Adapters
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.			TE Connectivity		
DECIMALS: XXX ± .005 XX ± .01 ANGLES: ± 1° X ± .1			TE		
TYCO ELECTRONICS RESERVES THE RIGHT TO AMEND THE DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.			TITLE: TINEL-LOCK ADAPTER "STXR" SERIES CODE 40		
			DOCUMENT NO: STXR40		
DRAWN: T. NGUYEN	CAD FILE: STXR	CAGE CODE: 06090	RPN:	SIZE: A	SCALE: 1/1
			THIRD ANGLE PROJ.		SHEET: 1 OF 3




FIGURE 1
STRAIGHT ADAPTER




FIGURE 2
45° ADAPTER




FIGURE 3
90° ADAPTER

PART NUMBERING

		S	TXR	40	A	B	00	-	20	18	B	I
△- PREFIX	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
- PRODUCT DESIGNATOR	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
- CONNECTOR CODE	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
- MATERIAL:	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
A = ALUMINUM ALLOY B51474 6082-T6, B54300/S 2011 (TD), OR AMS-QQ-A-225. B = NICKEL ALUMINUM BRONZE DGS 1043 OR ASTM C 632000. S = STAINLESS STEEL B5970 303521 OR AMS-QQ-S-763.												
- FINISH (SEE S-CH00-0157-002)	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
- CONFIGURATION:	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
00 = STRAIGHT, 45 = 45°, 90 = 90°												
- ORDER NUMBER	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
- ENTRY SIZE	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
- BRAID DESIGNATOR:	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____
BRAID A: SINGLE LAYER 36 AWG.												
BRAID B: SINGLE LAYER 30 AWG.												
DOUBLE LAYER 36 AWG.												
- RING WITH INSULATING LINING	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____	_____

Raychem Adapters
CUSTOMER DRAWING

DOCUMENT NO:				STXR40			
CAGE CODE:	RPN:	SIZE:	SCALE:	THIRD ANGLE PROJ.	SHEET:		
06090		A	1:1	⌀	2 OF 3		

TABLE I

ORDER NUMBER	SHELL SIZE 		ENTRY SIZE 		ØA THREAD RH METRIC CLASS 6H	ØB MAX	ØC MAX	ØD MAX	ØE MAX	W MAX
	COM	MIL	MIN	(MAX) 						
08	9	A	05	6	M12 x 1.0	.750 (19.1)	.82 (20.8)	1.07 (27.3)	1.10 (27.9)	1.350 (34.3)
10	11	B	08	10	M15 x 1.0	.850 (21.6)	.84 (21.3)	1.10 (28.0)	1.20 (30.5)	1.598 (40.6)
12	13	C	09	12	M18 x 1.0	1.000 (25.4)	.87 (22.1)	1.12 (28.5)	1.26 (32.0)	1.728 (43.9)
14	15	D	12	16	M22 x 1.0	1.140 (29.0)	.89 (22.6)	1.16 (29.5)	1.34 (34.0)	2.000 (50.8)
16	17	E	14	18	M25 x 1.0	1.280 (32.5)	.92 (23.4)	1.19 (30.2)	1.40 (35.6)	2.130 (54.1)
18	19	F	16	20	M28 x 1.0	1.400 (35.6)	.95 (24.1)	1.22 (31.0)	1.45 (36.8)	2.252 (57.2)
20	21	G	18	22	M31 x 1.0	1.500 (38.1)	.97 (24.6)	1.23 (31.4)	1.51 (38.4)	2.252 (57.2)
22	23	H	20	24	M34 x 1.0	1.650 (41.9)	1.00 (25.4)	1.24 (31.6)	1.57 (39.9)	2.252 (57.2)
24	25	J	22	24	M37 x 1.0	1.750 (44.5)	1.02 (25.9)	1.28 (32.6)	1.67 (42.4)	2.252 (57.2)

TABLE II

ENTRY SIZE	ØZ +.010 (0.25) -.020 (0.50)	ØS	ØY +/- .015 (+/- 0.38)
05	.312 (7.92)	.432/.438 (10.97/11.13)	.612 (15.54)
06	.375 (9.52)	.495/.501 (12.57/12.73)	.675 (17.14)
07	.437 (11.09)	.556/.563 (14.12/14.31)	.737 (18.71)
08	.500 (12.70)	.619/.626 (15.72/15.91)	.800 (20.32)
10	.625 (15.87)	.742/.752 (18.84/19.11)	.925 (23.49)
12	.750 (19.05)	.867/.877 (22.02/22.28)	1.050 (26.67)
14	.875 (22.23)	.991/1.002 (25.17/25.46)	1.175 (29.84)
16	1.000 (25.40)	1.116/1.127 (28.34/28.63)	1.300 (32.02)
18	1.125 (28.57)	1.241/1.252 (31.52/31.81)	1.425 (36.19)
20	1.250 (31.75)	1.366/1.377 (34.69/34.98)	1.550 (39.37)
22	1.375 (34.93)	1.488/1.502 (37.79/38.15)	1.675 (42.55)
24	1.500 (38.10)	1.613/1.627 (40.97/41.33)	1.800 (45.72)

Raychem Adapters
CUSTOMER DRAWING

DOCUMENT NO:

STXR40

© 2015 Tyco Electronics Corporation. All rights reserved.

CAGE CODE: 06090	RPN:	SIZE: A	SCALE: 	THIRD ANGLE PROJ. 	SHEET: 3 OF 3
---------------------	------	------------	---	--	------------------