





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		C	REVISED PER ECO-08-010444	17DEC2008	ZMR	SLB




ALTERNATE BRACKET
DESIGN
TYP.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 28JAN2004	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK S. SHUEY 28JAN04				
		APVD M. WALMSLEY 28JAN04	NAME			
DIMENSIONS: mm [INCHES]		PRODUCT SPEC 108-1228	RECEPTACLE ASSEMBLY, SHIELDED, RIGHT ANGLE, RAILED, .050 SERIES, AMPLIMITE			
		APPLICATION SPEC 114-40029				
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-1761028	RESTRICTED TO -
MATERIAL 1		FINISH 2	CUSTOMER DRAWING			
			SCALE 2:1	SHEET 1 of 3	REV C	



4		3		2		1						
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION								
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.				ALL INTERNATIONAL RIGHTS RESERVED.								
LOC		DIST		REVISIONS								
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD			
					-	SEE SHEET 1	-	-	-			
1 CONTACTS: PHOSPHOR BRONZE. HOUSING & PIN-SPACER: UL 94V-0 RATED, THERMOPLASTIC, BLACK. BRACKET: ZINC. SHELL: CARBON STEEL. BOARDLOCKS: COPPER ALLOY. 2 CONTACTS: EITHER 0.00076 [.000030] MIN GOLD PLATE ON MATING END OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, 0.00076 [.000030] MIN TOTAL ON MATING END, 0.00381 [.000150] MIN TIN ON SOLDER END, ALL OVER 0.00127 [.000050] MIN NICKEL ON ENTIRE CONTACT. SHELL: 0.00508 [.000200] MIN NICKEL OVER 0.00127 [.000050] MIN COPPER. BRACKET: 0.00254 [.000100] MIN NICKEL OVER 0.00508 [.000200] COPPER. BOARDLOCKS: 0.00300 [.000118] MIN TIN OVER 0.00127 [.000050] MIN NICKEL.												
TUBE	T	29.87 [1.176]	17.37 [.684]	27.43 [1.080]	0.64 [.025]	23.75 [.935]	31.50 [1.240]	33.40 [1.315]	15.65 [.616]	27.43 [1.080]	20	1761028-6
TUBE	T	80.67 [3.176]	68.17 [2.684]	78.23 [3.080]	0.64 [.025]	74.55 [2.935]	82.30 [3.240]	84.20 [3.315]	66.45 [2.616]	78.23 [3.080]	100	1761028-5
TUBE	T	60.35 [2.376]	47.85 [1.884]	57.91 [2.280]	0.64 [.025]	54.23 [2.135]	61.98 [2.440]	63.88 [2.515]	46.13 [1.816]	57.91 [2.280]	68	1761028-4
TUBE	S	48.92 [1.926]	36.42 [1.434]	46.48 [1.834]	1.27 [.050]	42.80 [1.685]	50.55 [1.990]	52.45 [2.065]	34.70 [1.366]	46.48 [1.830]	50	1761028-3
TUBE	T	42.57 [1.676]	30.07 [1.184]	40.13 [1.580]	0.64 [.025]	36.45 [1.435]	44.20 [1.740]	46.10 [1.815]	28.35 [1.116]	40.13 [1.580]	40	1761028-2
TUBE	S	33.68 [1.326]	21.18 [.834]	31.24 [1.230]	1.27 [.050]	27.56 [1.085]	35.31 [1.390]	37.21 [1.465]	19.46 [.766]	31.24 [1.230]	26	1761028-1
PACKAGING	PC BOARD PATTERN	R	P	L	G	F	E	D	B	A	NO OF POS	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES]  MATERIAL 1 TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH 2				DWN B. MCMASTER28JAN2004		Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608 NAME RECEPTACLE ASSEMBLY, SHIELDED, RIGHT ANGLE, RAILED, .050 SERIES, AMPLIMITE SIZE A3 CAGE CODE 00779 DRAWING NO C-1761028 RESTRICTED TO -						
				CHK S. SHUEY28JAN04								
				APVD M. WALMSLEY28JAN04		PRODUCT SPEC 108-1228						
				APPLICATION SPEC 114-40029		WEIGHT -						
				CUSTOMER DRAWING						SCALE 2:1		SHEET 3 of 3