ANALOG DEVICES

High Voltage Latch-Up Proof, Single SPST Switch

Data Sheet

ADG5401

FEATURES

Latch-up immune under all circumstances
Human body model (HBM) ESD rating: 8 kV
Low on resistance: 6.5 Ω
±9 V to ±22 V dual-supply operation
9 V to 40 V single-supply operation
48 V supply maximum ratings
Fully specified at ±15 V, ±20 V, +12 V, and +36 V
V_{DD} to V_{SS} analog signal range

APPLICATIONS

High voltage signal routing
Automatic test equipment
Analog front-end circuits
Precision data acquisition
Amplifier gain select
Industrial instrumentation
Relay replacement

FUNCTIONAL BLOCK DIAGRAM

SWITCHES SHOWN FOR A LOGIC 1 INPUT

Figure 1.

GENERAL DESCRIPTION

The ADG5401 is a monolithic industrial, complementary metal oxide semiconductor (CMOS) analog switch containing a latch-up immune single-pole/single-throw (SPST) switch. The switch conducts equally well in both directions when on, and has an input signal range that extends to the power supplies. In the off condition, signal levels up to the supplies are blocked.

The ultralow on resistance and on-resistance flatness of these switches make them ideal solutions for data acquisition and gain switching applications, where low distortion is critical. The latch-up immune construction and high ESD rating make these switches more robust in harsh environments.

PRODUCT HIGHLIGHTS

1. Trench isolation guards against latch-up. A dielectric trench separates the P channel and N channel transistors, thereby preventing latch-up even under severe overvoltage conditions.
2. Low R_{ON} of 6.5 Ω.
3. Dual-supply operation. For applications where the analog signal is bipolar, the ADG5401 can operate from dual supplies of up to ±22 V.
4. Single-supply operation. For applications where the analog signal is unipolar, the ADG5401 can operate from a single-rail power supply of up to 40 V.
5. 3 V logic compatible digital inputs: V_{INH} = 2.0 V, V_{INL} = 0.8 V.
6. No V_L logic power supply required.
7. Available in 8-lead MSOP package and 8-lead, 2 mm × 3 mm LFCSP packages.

ADG5401* PRODUCT PAGE QUICK LINKS

Last Content Update: 02/23/2017

COMPARABLE PARTS 🗗

View a parametric search of comparable parts.

EVALUATION KITS 🗗

- Evaluation Board for 8 lead MSOP Devices in the Switch/Mux Portfolio

DOCUMENTATION 🗗

Application Notes

- AN-1313: Configuring the AD5422 to Combine Output Current and Output Voltage to a Single Output Pin

Data Sheet

- ADG5401: High Voltage Latch-Up Proof, Single SPST Switch

User Guides

- UG-893: Evaluating the 8-Lead MSOP Devices in the Switch/Mux Portfolio

REFERENCE MATERIALS 🗗

Press

- Latch-up Immune, High ESD Switches, Expands ADI Offerings in High-Voltage Industrial Applications

DESIGN RESOURCES 🗗

- ADG5401 Material Declaration
- PCN-PDN Information
- Quality And Reliability
- Symbols and Footprints

DISCUSSIONS 🗗

View all ADG5401 EngineerZone Discussions.

SAMPLE AND BUY 🗗

Visit the product page to see pricing options.

TECHNICAL SUPPORT 🗗

Submit a technical question or find your regional support number.

DOCUMENT FEEDBACK 🗗

Submit feedback for this data sheet.

TABLE OF CONTENTS

REVISION HISTORY

SPECIFICATIONS

±15 V DUAL SUPPLY

V_{DD} = +15 V ± 10%, V_{SS} = −15 V ± 10%, GND = 0 V, unless otherwise noted.

Table 1.

Parameter	25°C	−40°C to +85°C	−40°C to +125°C	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range			V_{DD} to V_{SS}	V	
On Resistance, R_{ON}	6.5			Ω typ	V_S = ±10 V, I_S = −10 mA; see Figure 21
	8	10	12	Ω max	V_{DD} = +13.5 V, V_{SS} = −13.5 V
On-Resistance Flatness, $R_{FLAT (ON)}$	1			Ω typ	V_S = ±10 V, I_S = −10 mA
	1.4	1.7	2	Ω max	
LEAKAGE CURRENTS					V_{DD} = +16.5 V, V_{SS} = −16.5 V
Source Off Leakage, I_S (Off)	±0.1			nA typ	V_S = ±10 V, V_D = ∓ 10 V; see Figure 20
	±0.5	±2	±20	nA max	
Drain Off Leakage, I_D (Off)	±0.1			nA typ	V_S = ±10 V, V_D = ∓ 10 V; see Figure 20
	±0.5	±2	±20	nA max	
Channel On Leakage, I_D (On), I_S (On)	±0.2			nA typ	V_S = V_D = ±10 V; see Figure 23
	±1	±8	±40	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{INH}			2.0	V min	
Input Low Voltage, V_{INL}			0.8	V max	
Input Current, I_{INL} or I_{INH}	0.002			µA typ	V_{IN} = V_{GND} or V_{DD}
			±0.1	µA max	
Digital Input Capacitance, C_{IN}	6			pF typ	
DYNAMIC CHARACTERISTICS[1]					
t_{ON}	160			ns typ	R_L = 300 Ω, C_L = 35 pF
	193	230	253	ns max	V_S = 10 V; see Figure 26
t_{OFF}	175			ns typ	R_L = 300 Ω, C_L = 35 pF
	207	230	242	ns max	V_S = 10 V; see Figure 26
Charge Injection, Q_{INJ}	220			pC typ	V_S = 0 V, R_S = 0 Ω, C_L = 1 nF; see Figure 27
Off Isolation	−50			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 22
Total Harmonic Distortion + Noise (THD + N)	0.01			% typ	R_L = 1 kΩ, 15 V p-p, f = 20 Hz to 20 kHz; see Figure 24
−3 dB Bandwidth	170			MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 25
Insertion Loss	−0.4			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 25
C_S (Off)	22			pF typ	V_S = 0 V, f = 1 MHz
C_D (Off)	24			pF typ	V_S = 0 V, f = 1 MHz
C_D (On), C_S (On)	75			pF typ	V_S = 0 V, f = 1 MHz
POWER REQUIREMENTS					V_{DD} = +16.5 V, V_{SS} = −16.5 V
I_{DD}	45			µA typ	Digital inputs = 0 V or V_{DD}
	55		70	µA max	
I_{SS}	0.001			µA typ	Digital inputs = 0 V or V_{DD}
			1	µA max	
V_{DD}/V_{SS}			±9/±22	V min/V max	GND = 0 V

[1] Guaranteed by design; not subject to production test.

±20 V DUAL SUPPLY

V_{DD} = +20 V ± 10%, V_{SS} = −20 V ± 10%, GND = 0 V, unless otherwise noted.

Table 2.

Parameter	25°C	−40°C to +85°C	−40°C to +125°C	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range			V_{DD} to V_{SS}	V	
On Resistance, R_{ON}	6			Ω typ	V_S = ±15 V, I_S = −10 mA; see Figure 21
	7	9	11	Ω max	V_{DD} = +18 V, V_{SS} = −18 V
On-Resistance Flatness, $R_{FLAT (ON)}$	1.2			Ω typ	V_S = ±15 V, I_S = −10 mA
	1.7	2.1	2.5	Ω max	
LEAKAGE CURRENTS					V_{DD} = +22 V, V_{SS} = −22 V
Source Off Leakage, I_S (Off)	±0.1			nA typ	V_S = ±15 V, V_D = ∓ 15 V; see Figure 20
	±0.5	±2	±20	nA max	
Drain Off Leakage, I_D (Off)	±0.1			nA typ	V_S = ±15 V, V_D = ∓ 15 V; see Figure 20
	±0.5	±2	±20	nA max	
Channel On Leakage, I_D (On), I_S (On)	±0.2			nA typ	V_S = V_D = ±15 V; see Figure 23
	±1	±8	±40	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{INH}			2.0	V min	
Input Low Voltage, V_{INL}			0.8	V max	
Input Current, I_{INL} or I_{INH}	0.002			µA typ	V_{IN} = V_{GND} or V_{DD}
			±0.1	µA max	
Digital Input Capacitance, C_{IN}	6			pF typ	
DYNAMIC CHARACTERISTICS[1]					
t_{ON}	150			ns typ	R_L = 300 Ω, C_L = 35 pF
	175	207	219	ns max	V_S = 10 V; see Figure 26
t_{OFF}	170			ns typ	R_L = 300 Ω, C_L = 35 pF
	196	214	223	ns max	V_S = 10 V; see Figure 26
Charge Injection, Q_{INJ}	275			pC typ	V_S = 0 V, R_S = 0 Ω, C_L = 1 nF; see Figure 27
Off Isolation	−50			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 22
Total Harmonic Distortion + Noise (THD + N)	0.01			% typ	R_L = 1 kΩ, 20 V p-p, f = 20 Hz to 20 kHz; see Figure 24
−3 dB Bandwidth	170			MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 25
Insertion Loss	−0.5			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 25
C_S (Off)	21			pF typ	V_S = 0 V, f = 1 MHz
C_D (Off)	23			pF typ	V_S = 0 V, f = 1 MHz
C_D (On), C_S (On)	75			pF typ	V_S = 0 V, f = 1 MHz
POWER REQUIREMENTS					V_{DD} = +22 V, V_{SS} = −22 V
I_{DD}	50			µA typ	Digital inputs = 0 V or V_{DD}
	70		110	µA max	
I_{SS}	0.001			µA typ	Digital inputs = 0 V or V_{DD}
			1	µA max	
V_{DD}/V_{SS}			±9/±22	V min/V max	GND = 0 V

[1] Guaranteed by design; not subject to production test.

12 V SINGLE SUPPLY

V_{DD} = 12 V ± 10%, V_{SS} = 0 V, GND = 0 V, unless otherwise noted.

Table 3.

Parameter	25°C	−40°C to +85°C	−40°C to +125°C	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range			0 V to V_{DD}	V	
On Resistance, R_{ON}	14			Ω typ	V_S = 0 V to 10 V, I_S = −10 mA; see Figure 21
	16	19	22	Ω max	V_{DD} = 10.8 V, V_{SS} = 0 V
On-Resistance Flatness, $R_{FLAT (ON)}$	2.8			Ω typ	V_S = 0 V to 10 V, I_S = −10 mA
	4	5.5	7	Ω max	
LEAKAGE CURRENTS					V_{DD} = +13.2 V, V_{SS} = 0 V
Source Off Leakage, I_S (Off)	±0.1			nA typ	V_S = 1 V to 10 V, V_D = 10 V to 1 V; see Figure 20
	±0.5	±2	±20	nA max	
Drain Off Leakage, I_D (Off)	±0.1			nA typ	V_S = 1 V to 10 V, V_D = 10 V to 1 V; see Figure 20
	±0.5	±2	±20	nA max	
Channel On Leakage, I_D (On), I_S (On)	±0.2			nA typ	V_S = V_D = 1 V to 10 V; see Figure 23
	±1	±8	±40	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{INH}			2.0	V min	
Input Low Voltage, V_{INL}			0.8	V max	
Input Current, I_{INL} or I_{INH}	0.002			µA typ	V_{IN} = V_{GND} or V_{DD}
			±0.1	µA max	
Digital Input Capacitance, C_{IN}	6			pF typ	
DYNAMIC CHARACTERISTICS[1]					
t_{ON}	260			ns typ	R_L = 300 Ω, C_L = 35 pF
	327	406	454	ns max	V_S = 8 V; see Figure 26
t_{OFF}	200			ns typ	R_L = 300 Ω, C_L = 35 pF
	244	280	300	ns max	V_S = 8 V; see Figure 26
Charge Injection, Q_{INJ}	95			pC typ	V_S = 6 V, R_S = 0 Ω, C_L = 1 nF; see Figure 27
Off Isolation	−50			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 22
Total Harmonic Distortion + Noise (THD + N)	0.02			% typ	R_L = 1 kΩ, 6 V p-p, f = 20 Hz to 20 kHz; see Figure 24
−3 dB Bandwidth	190			MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 25
Insertion Loss	−0.9			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 25
C_S (Off)	28			pF typ	V_S = 6 V, f = 1 MHz
C_D (Off)	30			pF typ	V_S = 6 V, f = 1 MHz
C_D (On), C_S (On)	60			pF typ	V_S = 6 V, f = 1 MHz
POWER REQUIREMENTS					V_{DD} = 13.2 V
I_{DD}	40			µA typ	Digital inputs = 0 V or V_{DD}
	50		65	µA max	
V_{DD}			9/40	V min/V max	GND = 0 V, V_{SS} = 0 V

[1] Guaranteed by design; not subject to production test.

36 V SINGLE SUPPLY

V_{DD} = 36 V ± 10%, V_{SS} = 0 V, GND = 0 V, unless otherwise noted.

Table 4.

Parameter	25°C	−40°C to +85°C	−40°C to +125°C	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range			0 V to V_{DD}	V	
On Resistance, R_{ON}	7			Ω typ	V_S = 0 V to 30 V, I_S = −10 mA; see Figure 21
	9	11	13	Ω max	V_{DD} = 32.4 V, V_{SS} = 0 V
On-Resistance Flatness, $R_{FLAT (ON)}$	1.8			Ω typ	V_S = 0 V to 30 V, I_S = −10 mA
	2.6	3	3.5	Ω max	
LEAKAGE CURRENTS					V_{DD} = +39.6 V, V_{SS} = 0 V
Source Off Leakage, I_S (Off)	±0.1			nA typ	V_S = 1 V to 30 V, V_D = 30 V to 1 V; see Figure 20
	±0.5	±2	±20	nA max	
Drain Off Leakage, I_D (Off)	±0.1			nA typ	V_S = 1 V to 30 V, V_D = 30 V to 1 V; see Figure 20
	±0.5	±2	±20	nA max	
Channel On Leakage, I_D (On), I_S (On)	±0.2			nA typ	V_S = V_D = 1 V to 30 V; see Figure 23
	±1	±8	±40	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{INH}			2.0	V min	
Input Low Voltage, V_{INL}			0.8	V max	
Input Current, I_{INL} or I_{INH}	0.002			µA typ	V_{IN} = V_{GND} or V_{DD}
			±0.1	µA max	
Digital Input Capacitance, C_{IN}	6			pF typ	
DYNAMIC CHARACTERISTICS[1]					
t_{ON}	160			ns typ	R_L = 300 Ω, C_L = 35 pF
	187	212	230	ns max	V_S = 18 V; see Figure 26
t_{OFF}	180			ns typ	R_L = 300 Ω, C_L = 35 pF
	213	221	225	ns max	V_S = 18 V; see Figure 26
Charge Injection, Q_{INJ}	255			pC typ	V_S = 18 V, R_S = 0 Ω, C_L = 1 nF; see Figure 27
Off Isolation	−50			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 22
Total Harmonic Distortion + Noise (THD + N)	0.01			% typ	R_L = 1 kΩ, 18 V p-p, f = 20 Hz to 20 kHz; see Figure 24
−3 dB Bandwidth	170			MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 25
Insertion Loss	−0.55			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 25
C_S (Off)	26			pF typ	V_S = 18 V, f = 1 MHz
C_D (Off)	28			pF typ	V_S = 18 V, f = 1 MHz
C_D (On), C_S (On)	65			pF typ	V_S = 18 V, f = 1 MHz
POWER REQUIREMENTS					V_{DD} = 39.6 V
I_{DD}	80			µA typ	Digital inputs = 0 V or V_{DD}
	100		130	µA max	
V_{DD}			9/40	V min/V max	GND = 0 V, V_{SS} = 0 V

[1] Guaranteed by design; not subject to production test.

CONTINUOUS CURRENT PER CHANNEL, S OR D

Table 5.

Parameter	25°C	85°C	125°C	Unit	Test Condition/Comments
8-LEAD MSOP					θ_{JA} = 133.1°C/W
V_{DD} = 15 V, V_{SS} = −15 V	171	116	79	mA maximum	
V_{DD} = 20 V, V_{SS} = −20 V	177	120.5	81	mA maximum	
V_{DD} = 12 V, V_{SS} = 0 V	139	99	70	mA maximum	
V_{DD} = 36 V, V_{SS} = 0 V	174	118	81	mA maximum	
8-LEAD LFCSP					θ_{JA} = 60.88°C/W
V_{DD} = 15 V, V_{SS} = −15 V	234	150	93	mA maximum	
V_{DD} = 20 V, V_{SS} = −20 V	246	155	95	mA maximum	
V_{DD} = 12 V, V_{SS} = 0 V	193	130	85	mA maximum	
V_{DD} = 36 V, V_{SS} = 0 V	241	153	95	mA maximum	

ABSOLUTE MAXIMUM RATINGS

T_A = 25°C, unless otherwise noted.

Table 6.

Parameter	Rating
V_{DD} to V_{SS}	48 V
V_{DD} to GND	−0.3 V to +48 V
V_{SS} to GND	+0.3 V to −48 V
Analog Inputs[1]	V_{SS} − 0.3 V to V_{DD} + 0.3 V or 30 mA, whichever occurs first
Digital Inputs[1]	V_{SS} − 0.3 V to V_{DD} + 0.3 V or 30 mA, whichever occurs first
Peak Current, S or D Pin	630 mA (pulsed at 1 ms, 10% duty cycle maximum)
Continuous Current, S or D[2]	Data + 15%
Temperature Range	
Operating	−40°C to +125°C
Storage	−65°C to +150°C
Junction Temperature	150°C
Thermal Impedance, θ_{JA}	
8-Lead MSOP (4-Layer Board)	133.1°C/W
8-Lead LFCSP	60.88°C/W
Reflow Soldering Peak Temperature, Pb Free	As per JEDEC J-STD-020
Human Body Model (HBM) ESD	8 kV

[1] Overvoltages at the IN, S, and D pins are clamped by internal diodes. Limit current to the maximum ratings given.
[2] See Table 5.

Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

Only one absolute maximum rating can be applied at any one time.

ESD CAUTION

PIN CONFIGURATIONS AND FUNCTION DESCRIPTIONS

NOTES
1. NC = NO CONNECT. NOT INTERNALLY CONNECTED.
2. THE EXPOSED PAD IS TIED TO SUBSTRATE, V_{SS}.

Figure 2. 8-Lead LFCSP Pin Configuration

NOTES
1. NC = NO CONNECT. NOT INTERNALLY CONNECTED.

Figure 3. 8-Lead MSOP Pin Configuration

**Table 7. Pin Function Descriptions**

Pin No.		Mnemonic	Description
8-Lead LFCSP	**8-Lead MSOP**		
1	1	S	Source Terminal. This pin can be an input or output.
2	2	NC	No Connect. Not internally connected.
3	3	GND	Ground (0 V) Reference.
4	4	V_{DD}	Most Positive Power Supply Potential.
5	5	NC	No Connect. Not internally connected.
6	6	IN	Logic Control Input.
7	7	V_{SS}	Most Negative Power Supply Potential.
8	8	D	Drain Terminal. This pin can be an input or output.
	Not applicable	EPAD	The exposed pad is tied to substrate, V_{SS}.

Table 8. Truth Table

IN	Switch Condition
1	On
0	Off

TYPICAL PERFORMANCE CHARACTERISTICS

Figure 4. On Resistance as a Function of V_S, V_D (Dual Supply)

Figure 7. On Resistance as a Function of V_S (V_D) for Different Temperatures, ±20 V Dual Supply

Figure 5. On Resistance as a Function of V_S, V_D (Single Supply)

Figure 8. On Resistance as a Function of V_S (V_D) for Different Temperatures, 12 V Single Supply

Figure 6. On Resistance as a Function of V_S (V_D) for Different Temperatures, ±15 V Dual Supply

Figure 9. On Resistance as a Function of V_S (V_D) for Different Temperatures, 36 V Single Supply

Figure 10. Leakage Currents as a Function of Temperature, ±15 V Dual Supply

Figure 11. Leakage Currents as a Function of Temperature, ±20 V Dual Supply

Figure 12. Leakage Currents as a Function of Temperature, 12 V Single Supply

Figure 13. Leakage Currents as a Function of Temperature, 36 V Single Supply


Figure 14. Off Isolation vs. Frequency

Figure 15. Charge Injection vs. Source Voltage (V_S)

Figure 16. THD + N vs. Frequency

*Figure 18. t*TRANSITION *Times vs. Temperature*

Figure 17. Bandwidth

Figure 19. ACPSRR vs. Frequency

# TEST CIRCUITS

Figure 20. Off Leakage

*Figure 23. On Leakage*

*Figure 21. On Resistance*

Figure 24. THD + N

OFF ISOLATION = 20 log $\frac{V_{OUT}}{V_S}$

Figure 22. Off Isolation

INSERTION LOSS = 20 log $\frac{V_{OUT} \text{ WITH SWITCH}}{V_{OUT} \text{ WITHOUT SWITCH}}$

Figure 25. Bandwidth

*Figure 26. Switching Times, t_{ON} and t_{OFF}*

Figure 27. Charge Injection

TERMINOLOGY

I_{DD}
I_{DD} represents the positive supply current.

I_{SS}
I_{SS} represents the negative supply current.

V_D, V_S
V_D and V_S represent the analog voltage on Terminal D and Terminal S, respectively.

R_{ON}
R_{ON} is the ohmic resistance between Terminal D and Terminal S.

$R_{FLAT\,(ON)}$
$R_{FLAT\,(ON)}$ represents the difference between the maximum and minimum value of on resistance as measured over the specified analog signal range.

I_S (Off)
I_S (Off) is the source leakage current with the switch off.

I_D (Off)
I_D (Off) is the drain leakage current with the switch off.

I_D (On), I_S (On)
I_D (On) and I_S (On) represent the channel leakage currents with the switch on.

V_{INL}
V_{INL} is the maximum input voltage for Logic 0.

V_{INH}
V_{INH} is the minimum input voltage for Logic 1.

I_{INL}, I_{INH}
I_{INL} and I_{INH} represent the low and high input currents of the digital inputs.

C_D (Off)
C_D (Off) represents the off switch drain capacitance, which is measured with reference to ground.

C_S (Off)
C_S (Off) represents the off switch source capacitance, which is measured with reference to ground.

C_D (On), C_S (On)
C_D (On) and C_S (On) represent the on switch capacitances, which are measured with reference to ground.

C_{IN}
C_{IN} represents digital input capacitance.

t_{ON}
t_{ON} represents the delay time between the 50% and 90% points of the digital input and switch on condition.

t_{OFF}
t_{OFF} represents the delay time between the 50% and 90% points of the digital input and switch off condition.

Off Isolation
Off isolation is a measure of unwanted signal coupling through an off channel.

Charge Injection
Charge injection is a measure of the glitch impulse transferred from the digital input to the analog output during switching.

Bandwidth
Bandwidth is the frequency at which the output is attenuated by 3 dB from its dc value.

Total Harmonic Distortion + Noise (THD + N)
The ratio of the harmonic amplitude plus noise of the signal to the fundamental is represented by THD + N.

AC Power Supply Rejection Ratio (ACPSRR)
ACPSRR measures the ability of the device to avoid coupling noise and spurious signals that appear on the supply voltage pin to the output of the switch. The dc voltage on the device is modulated by a sine wave of 0.62 V p-p. The ratio of the amplitude of the signal on the output to the amplitude of the modulation is the ACPSRR (see Figure 19).

APPLICATIONS INFORMATION

The ADG54xx family of switches and multiplexers provide a robust solution for instrumentation, industrial, aerospace, and other harsh environments that are prone to latch-up, which is an undesirable high current state that can lead to device failure and persists until the power supply is turned off. The ADG5401 high voltage switch allows single-supply operation from 9 V to 40 V and dual-supply operation from ±9 V to ±22 V. The ADG5401 (as well as other select devices within this family) achieves an 8 kV human body model ESD rating, which provides a robust solution, eliminating the need for separate protection circuitry designs in some applications.

TRENCH ISOLATION

In the ADG5401, an insulating oxide layer (trench) is placed between the NMOS and the PMOS transistors of each CMOS switch. Parasitic junctions, which occur between the transistors in junction-isolated switches, are eliminated, and the result is a latch-up immune switch.

In junction isolation, the N and P wells of the PMOS and NMOS transistors form a diode that is reverse-biased under normal operation. However, during overvoltage conditions, this diode can become forward-biased. The two transistors form a silicon-controlled rectifier (SCR) type circuit, causing a significant amplification of the current that, in turn, leads to latch-up. With trench isolation, this diode is removed, and the result is a latch-up immune switch.


Figure 28. Trench Isolation

OUTLINE DIMENSIONS

COMPLIANT TO JEDEC STANDARDS MO-187-AA

Figure 29. 8-Lead Mini Small Outline Package [MSOP]
*(RM-8)*
Dimensions shown in millimeters

Figure 30. 8-Lead Lead Frame Chip Scale Package [LFCSP_WD]
2 mm × 3 mm Body, Very Very Thin, Dual Lead
(CP-8-4)
Dimensions shown in millimeters

ORDERING GUIDE

Model[1]	Temperature Range	Package Description	Package Option	Branding
ADG5401BRMZ	−40°C to +125°C	8-Lead Mini Small Outline Package [MSOP]	RM-8	S2M
ADG5401BRMZ-RL7	−40°C to +125°C	8-Lead Mini Small Outline Package [MSOP]	RM-8	S2M
ADG5401BCPZ-RL7	−40°C to +125°C	8-Lead Lead Frame Chip Scale Package [LFCSP_WD]	CP-8-4	BR

[1] Z = RoHS Compliant Part.

www.analog.com