

# MN4017B / MN4017BS

## 5-Stage Johnson Counters

### Description


The MN4017B/S are 5-stage Johnson decade counters constructed with five D-type flip-flops. One of the outputs ( $O_0 \sim O_9$ ) becomes High level according to the number of counter pulses applied to  $CP_0$  or  $\overline{CP}_1$ . The counter is advanced by either a positive going edge of  $CP_0$  while  $\overline{CP}_1$  is Low or a negative going edge of  $\overline{CP}_1$  while  $CP_0$  is High. A High on the reset input (MR) resets the counter to zero ( $O_0 = \overline{O}_{5-9} = \text{High}$ ,  $O_1 \sim O_9 = \text{Low}$ ) independent of the clock inputs ( $CP_0$ ,  $\overline{CP}_1$ ). These are equivalent to MOTOROLA MC14017B and RCA CD4017B.

### Truth Table


| MR | $CP_0$     | $\overline{CP}_1$ | Mode                                                              |
|----|------------|-------------------|-------------------------------------------------------------------|
| H  | X          | X                 | $O_0 = \overline{O}_{5-9} = \text{H}$ , $O_1 \sim O_9 = \text{L}$ |
| L  | H          | $\nearrow$        | Counter Advances                                                  |
| L  | $\nearrow$ | L                 |                                                                   |
| L  | L          | X                 | No Change                                                         |
| L  | X          | H                 |                                                                   |
| L  | H          | $\searrow$        |                                                                   |
| L  | $\searrow$ | L                 |                                                                   |

Note) X : don't care

### Logic Diagram



P- 3




16-Pin • Plastic DIL Package

P- 4



16-Pin • Pinflat Package (SO-16D)

### Pin Configuration



### Pin Explanation

- $CP_0$  : Positive clock input ( $\nearrow$ )
- $\overline{CP}_1$  : Negative clock input ( $\searrow$ )
- MR : Reset input
- $O_0 \sim O_9$  : Output (10 Bits)

# Maximum Ratings (Ta=25°C)

| Item                                    |                                   | Symbol    | Ratings                               | Unit |
|-----------------------------------------|-----------------------------------|-----------|---------------------------------------|------|
| Supply Voltage                          |                                   | $V_{DD}$  | $-0.5 \sim +18$                       | V    |
| Input Voltage                           |                                   | $V_I$     | $-0.5 \sim V_{DD} + 0.5^*$            | V    |
| Output Voltage                          |                                   | $V_O$     | $-0.5 \sim V_{DD} + 0.5^*$            | V    |
| Peak Input · Output Current             |                                   | $\pm I_I$ | max. 10                               | mA   |
| Power Dissipation<br>(per package)      | Ta = $-40 \sim +60^\circ\text{C}$ | $P_D$     | max. 400                              | mW   |
|                                         | Ta = $+60 \sim +85^\circ\text{C}$ |           | Decrease up to 200mW rating at 8mW/°C |      |
| Power Dissipation (per output terminal) |                                   | $P_D$     | max. 100                              | mW   |
| Operating Ambient Temperature           |                                   | Topr      | $-40 \sim +85$                        | °C   |
| Storage Temperature                     |                                   | Tstg      | $-65 \sim +150$                       | °C   |

\*  $V_{DD} + 0.5\text{V}$  should be under 18V


# DC Characteristics (VSS=0V)

| Item                              | $V_{DD}$<br>(V) | Sym-<br>bol | Conditions                                           | Ta = $-40^\circ\text{C}$              |      | Ta = $25^\circ\text{C}$ |      | Ta = $85^\circ\text{C}$ |      | Unit          |
|-----------------------------------|-----------------|-------------|------------------------------------------------------|---------------------------------------|------|-------------------------|------|-------------------------|------|---------------|
|                                   |                 |             |                                                      | min.                                  | max. | min.                    | max. | min.                    | max. |               |
| Quiescent Power<br>Supply Current | 5               | $I_{DD}$    | $V_I = V_{SS}$ or $V_{DD}$                           | —                                     | 20   | —                       | 20   | —                       | 150  | $\mu\text{A}$ |
|                                   | 10              |             |                                                      | —                                     | 40   | —                       | 40   | —                       | 300  |               |
|                                   | 15              |             |                                                      | —                                     | 80   | —                       | 80   | —                       | 600  |               |
| Output Voltage<br>Low Level       | 5               | $V_{OL}$    | $V_I = V_{SS}$ or $V_{DD}$<br>$ I_O  < 1\mu\text{A}$ | —                                     | 0.05 | —                       | 0.05 | —                       | 0.05 | V             |
|                                   | 10              |             |                                                      | —                                     | 0.05 | —                       | 0.05 | —                       | 0.05 |               |
|                                   | 15              |             |                                                      | —                                     | 0.05 | —                       | 0.05 | —                       | 0.05 |               |
| Output Voltage<br>High Level      | 5               | $V_{OH}$    | $V_I = V_{SS}$ or $V_{DD}$<br>$ I_O  < 1\mu\text{A}$ | 4.95                                  | —    | 4.95                    | —    | 4.95                    | —    | V             |
|                                   | 10              |             |                                                      | 9.95                                  | —    | 9.95                    | —    | 9.95                    | —    |               |
|                                   | 15              |             |                                                      | 14.95                                 | —    | 14.95                   | —    | 14.95                   | —    |               |
| Input Voltage<br>Low Level        | 5               | $V_{IL}$    | $ I_O  < 1\mu\text{A}$                               | $V_O = 0.5\text{V}$ or $4.5\text{V}$  |      | —                       | 1.5  | —                       | 1.5  | V             |
|                                   | 10              |             |                                                      | $V_O = 1\text{V}$ or $9\text{V}$      |      | —                       | 3    | —                       | 3    |               |
|                                   | 15              |             |                                                      | $V_O = 1.5\text{V}$ or $13.5\text{V}$ |      | —                       | 4    | —                       | 4    |               |
| Input Voltage<br>High Level       | 5               | $V_{IH}$    | $ I_O  < 1\mu\text{A}$                               | $V_O = 0.5\text{V}$ or $4.5\text{V}$  |      | 3.5                     | —    | 3.5                     | —    | V             |
|                                   | 10              |             |                                                      | $V_O = 1\text{V}$ or $9\text{V}$      |      | 7                       | —    | 7                       | —    |               |
|                                   | 15              |             |                                                      | $V_O = 1.5\text{V}$ or $13.5\text{V}$ |      | 11                      | —    | 11                      | —    |               |
| Output Current<br>Low Level       | 5               | $I_{OL}$    | $V_O = 0.4\text{V}, V_I = 0$ or $5\text{V}$          | 0.52                                  | —    | 0.44                    | —    | 0.36                    | —    | mA            |
|                                   | 10              |             | $V_O = 0.5\text{V}, V_I = 0$ or $10\text{V}$         | 1.3                                   | —    | 1.1                     | —    | 0.9                     | —    |               |
|                                   | 15              |             | $V_O = 1.5\text{V}, V_I = 0$ or $15\text{V}$         | 3.6                                   | —    | 3                       | —    | 2.4                     | —    |               |
| Output Current<br>High Level      | 5               | $-I_{OH}$   | $V_O = 4.6\text{V}, V_I = 0$ or $5\text{V}$          | 0.52                                  | —    | 0.44                    | —    | 0.36                    | —    | mA            |
|                                   | 10              |             | $V_O = 9.5\text{V}, V_I = 0$ or $10\text{V}$         | 1.3                                   | —    | 1.1                     | —    | 0.9                     | —    |               |
|                                   | 15              |             | $V_O = 13.5\text{V}, V_I = 0$ or $15\text{V}$        | 3.6                                   | —    | 3                       | —    | 2.4                     | —    |               |
| Output Current High Level         | 5               | $-I_{OH}$   | $V_O = 2.5\text{V}, V_I = 0$ or $5\text{V}$          | 1.7                                   | —    | 1.4                     | —    | 1.1                     | —    | mA            |
| Input Leakage Current             | 15              | $\pm I_I$   | $V_I = 0$ or $15\text{V}$                            | —                                     | 0.3  | —                       | 0.3  | —                       | 1    | $\mu\text{A}$ |


■ Switching Characteristics (Ta = 25°C, V<sub>SS</sub> = 0V, C<sub>L</sub> = 50pF)

| Item                                                                                                              | V <sub>DD</sub> (V) | Symbol            | min. | typ. | max. | Unit |
|-------------------------------------------------------------------------------------------------------------------|---------------------|-------------------|------|------|------|------|
| Output Rise Time                                                                                                  | 5                   | t <sub>TLH</sub>  | —    | 60   | 180  | ns   |
|                                                                                                                   | 10                  |                   | —    | 30   | 90   |      |
|                                                                                                                   | 15                  |                   | —    | 20   | 60   |      |
| Output Fall Time                                                                                                  | 5                   | t <sub>THL</sub>  | —    | 60   | 180  | ns   |
|                                                                                                                   | 10                  |                   | —    | 30   | 90   |      |
|                                                                                                                   | 15                  |                   | —    | 20   | 60   |      |
| Propagation Delay Time<br>CP <sub>0</sub> , $\overline{\text{CP}}_1 \rightarrow \text{O}_0$ to $\text{O}_9$ (H→L) | 5                   | t <sub>PHL</sub>  | —    | 195  | 585  | ns   |
|                                                                                                                   | 10                  |                   | —    | 75   | 225  |      |
|                                                                                                                   | 15                  |                   | —    | 50   | 150  |      |
| Propagation Delay Time<br>CP <sub>0</sub> , $\overline{\text{CP}}_1 \rightarrow \text{O}_0$ to $\text{O}_9$ (L→H) | 5                   | t <sub>PLH</sub>  | —    | 245  | 735  | ns   |
|                                                                                                                   | 10                  |                   | —    | 95   | 285  |      |
|                                                                                                                   | 15                  |                   | —    | 60   | 180  |      |
| Propagation Delay Time<br>CP <sub>0</sub> , $\overline{\text{CP}}_1 \rightarrow \overline{\text{O}}_{5-9}$ (H→L)  | 5                   | t <sub>PHL</sub>  | —    | 245  | 735  | ns   |
|                                                                                                                   | 10                  |                   | —    | 90   | 270  |      |
|                                                                                                                   | 15                  |                   | —    | 60   | 180  |      |
| Propagation Delay Time<br>CP <sub>0</sub> , $\overline{\text{CP}}_1 \rightarrow \overline{\text{O}}_{5-9}$ (L→H)  | 5                   | t <sub>PLH</sub>  | —    | 190  | 570  | ns   |
|                                                                                                                   | 10                  |                   | —    | 75   | 225  |      |
|                                                                                                                   | 15                  |                   | —    | 50   | 150  |      |
| Propagation Delay Time<br>MR→O <sub>1</sub> to O <sub>9</sub> (H→L)                                               | 5                   | t <sub>PHL</sub>  | —    | 130  | 390  | ns   |
|                                                                                                                   | 10                  |                   | —    | 55   | 165  |      |
|                                                                                                                   | 15                  |                   | —    | 40   | 120  |      |
| Propagation Delay Time<br>MR→ $\overline{\text{O}}_{5-9}$ (L→H)                                                   | 5                   | t <sub>PLH</sub>  | —    | 110  | 330  | ns   |
|                                                                                                                   | 10                  |                   | —    | 45   | 135  |      |
|                                                                                                                   | 15                  |                   | —    | 35   | 105  |      |
| Propagation Delay Time<br>MR→O <sub>0</sub> (L→H)                                                                 | 5                   | t <sub>PLH</sub>  | —    | 130  | 390  | ns   |
|                                                                                                                   | 10                  |                   | —    | 55   | 165  |      |
|                                                                                                                   | 15                  |                   | —    | 40   | 120  |      |
| Hold Time<br>CP <sub>0</sub> → $\overline{\text{CP}}_1$                                                           | 5                   | t <sub>hold</sub> | —    | 70   | 210  | ns   |
|                                                                                                                   | 10                  |                   | —    | 25   | 75   |      |
|                                                                                                                   | 15                  |                   | —    | 15   | 45   |      |
| Hold Time<br>$\overline{\text{CP}}_1$ →CP <sub>0</sub>                                                            | 5                   | t <sub>hold</sub> | —    | 85   | 255  | ns   |
|                                                                                                                   | 10                  |                   | —    | 30   | 90   |      |
|                                                                                                                   | 15                  |                   | —    | 20   | 60   |      |
| Minimum Clock Pulse Width                                                                                         | 5                   | t <sub>WCP</sub>  | —    | 35   | 105  | ns   |
|                                                                                                                   | 10                  |                   | —    | 15   | 45   |      |
|                                                                                                                   | 15                  |                   | —    | 10   | 30   |      |
| Minimum Reset Pulse Width                                                                                         | 5                   | t <sub>WMRH</sub> | —    | 35   | 105  | ns   |
|                                                                                                                   | 10                  |                   | —    | 15   | 45   |      |
|                                                                                                                   | 15                  |                   | —    | 10   | 30   |      |
| Reset Recovery Time                                                                                               | 5                   | t <sub>RMR</sub>  | —    | 25   | 75   | ns   |
|                                                                                                                   | 10                  |                   | —    | 10   | 40   |      |
|                                                                                                                   | 15                  |                   | —    | 10   | 30   |      |
| Maximum Clock Frequency                                                                                           | 5                   | f <sub>max</sub>  | 3    | 6    | —    | ns   |
|                                                                                                                   | 10                  |                   | 8    | 16   | —    |      |
|                                                                                                                   | 15                  |                   | 12   | 24   | —    |      |
| Input Capacitance                                                                                                 |                     | C <sub>i</sub>    | —    | —    | 7.5  | pF   |


## 1. Switching Time Test Circuit



## 2. Waveforms



Waveforms showing hold times for  $CP_0$  to  $\overline{CP}_1$  and  $\overline{CP}_1$  to  $CP_0$ .  
Hold times are shown as positive values, but may be specified as negative values.



Waveforms showing recovery time for MR; minimum  $CP_0$  and MR pulse widths  
Conditions:  $\overline{CP}_1$  = LOW while  $CP_0$  is triggered on a LOW to HIGH transition;  
 $t_{wCP1}$  and  $t_{RMR}$  also apply when  $CP_0$  = HIGH and  $\overline{CP}_1$  is triggered on a HIGH to LOW transition.

# Timing Diagram

