


Array Type Multilayer Ceramic Capacitors

T2K110BJ104MB-T



■ Features

- Item Summary
25V, X5R, 0.1 μ F, $\pm$ 20%, 0504
- Lifecycle Stage
Non-preferred
- Standard packaging quantity (minimum)
Taping paper 4000pcs

■ Products characteristics table

CaseSize (EIA/JIS)	0504/1410
Rated Voltage (max)	25V
Capacitance	0.1 μ F
Capacitance Tolerance	$\pm$ 20%
Resistance	10,000 M Ω min.
Dielectric Loss Tangent	5%MAX
Temperature Characteristics (EIA/JIS)	X5R/B
Temperature Range (EIA/JIS)	-55 to +85 $^{\circ}$ C/-25 to +85 $^{\circ}$ C
Capacitance Change (EIA/JIS)	$\pm$ 15/ $\pm$ 10%
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

■ External Dimensions

L	1.37mm $\pm$ 0.07
W	1.0mm $\pm$ 0.08
T	0.6mm $\pm$ 0.06
e	0.36mm $\pm$ 0.10

2014.06.06

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.