

**CONNECTOR
DESIGNATOR
A-F-L-H-S
ROTATABLE
COUPLING**

Product Series — **620** A S 003 M 16


Connector Designator —

Angle and Profile — S = Straight

Basic Part No. —

Shell Size —

Finish (Table II) —


TABLE III: CABLE ENTRY

Shell Size Conn. Desig.		E		F		H Cable Entry			
A,F,L	H	Max		Nom		Closed		Open	
08	09	.625	(15.9)	.750	(19.1)	.055	(1.4)	.125	(3.2)
10	11	.656	(16.7)	.750	(19.1)	.055	(1.4)	.188	(4.8)
12	13	.718	(18.2)	.937	(23.8)	.095	(2.4)	.250	(6.4)
14	15	.968	(24.6)	1.015	(25.8)	.219	(5.6)	.375	(9.5)
16	17	1.105	(28.1)	1.125	(28.6)	.219	(5.6)	.500	(12.7)
18	19	1.105	(28.1)	1.188	(30.2)	.345	(8.8)	.625	(15.9)
20	21	1.105	(28.1)	1.312	(33.3)	.469	(11.9)	.750	(19.1)
22	23	1.105	(28.1)	1.437	(36.5)	.594	(15.1)	.875	(22.2)
24	25	1.105	(28.1)	1.562	(39.7)	.594	(15.1)	1.000	(25.4)
28		1.105	(28.1)	1.812	(46.0)	.859	(21.8)	1.250	(31.8)

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[620AS003C16](#) [620AS003M10](#) [620AS003M14-56](#) [620AS003M16](#) [620AS003NF20](#) [620HS003B11](#) [620HS003B23](#)
[620HS003M09](#) [620HS003M13](#) [620HS003M17](#) [620HS003M19](#) [620HS003M21](#) [620HS003M23](#) [620HS003N09](#)
[620HS003N11](#) [620HS003N13](#) [620HS003N15](#) [620HS003N17](#) [620HS003N19](#) [620HS003N21](#) [620HS003N23](#)
[620HS003N25](#) [620HS003NF09](#) [620HS003NF11](#) [620HS003NF13](#) [620HS003NF19](#) [620HS003NF21](#) [620HS003NF23](#)
[620HS003NF25](#) [620LS003N10](#) [620LS003N12](#) [620LS003N18](#) [620AS003NF12](#) [620AS003NF16](#) [620AS003M12](#)
[620AS003NF14](#) [620AS003NF18](#) [620HS003M09-98A](#) [620HS003NF15](#)