



 Active

 [Add to Part List](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Radial Application
- Family Name = RGEF
- Radial Construction, Through Hole Construction
- IH (Room Temperature) = 10 Amps.
- IT (Room Temperature) = 17.00 Amps.

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- [RGEF1000](#) (PDF, English)

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

[List all Documents](#)

- UL Recognized = File No. E74889
- CSA File No. = 78165C

- IH (Room Temperature) (Amps.) = 10
- IT (Room Temperature) (Amps.) = 17.00
- Vmax Operating (V) = 16
- Rmin (Ω) = 0.004
- Rmax (Ω) = 0.0071
- R1 Max [Post Trip] (Ω) = 0.0102
- UL Rated Current (Amps.) = 100
- Tripped Power Dissipation (Typical) (W) = 3.60

- Construction = Radial, Through Hole

- Lead Type = Straight

- Family Name = RGEF

- Coating = Coated

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041433

- Operating Temperature (Max.) (°C) = 85

- Application = Radial

- Packaging Method = Tape & Reel

- Brand = Raychem