

Data Sheet

ST072xxHGNN

Page 1/4


P/N

AST072xx

xx=number of poles

2013/09/06

Illustration



see enlarged drawing at the end of the document

Product specification

- spring clamp terminal block, solderable, double solder pins
- centerline 2.54 mm, direction of connection 90°
- color green
- push-button
- Connection data

CRIUS V / A / AWG 150 / 6 / 26 - 20

SEV 0.5 mm² 130 V / 6 A / T60

Data Sheet

ST072xxHGNN

Page 2/4

P/N

AST072xx

xx=number of poles

2013/09/06

Technical Data

General Data

Solder pin length	3.2 mm		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 600		
clearance/creepage dist.	2 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	400 V	400 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV
Min. insul. strip length	10 mm		

Connection data

 V / A / AWG	150 / 6 / 26 - 20
 0.5 mm ²	130 V / 6 A / T60

Material

insulating material	PA66
flammability class	V0

Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

solderability	For THR products acc. to IPC/JEDEC J-STD-020D-MSL 1 For THT products max. 260 °C / 10 s
Tolerance	ISO 2768 -mH

Data Sheet

ST072xxHGNN

Page 3/4

P/N





AST072xx

xx=number of poles

2013/09/06

Illustration

Drawing



$$L = (\text{pole size} - 1) \times \text{centerline} + 4.74 [0.187]$$

Data Sheet

ST072xxHGNN

Page 4/4

P/N

AST072xx

xx=number of poles

2013/09/06

PCB Layout

