




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0	W		REVISED PER ECO-07-010240	5/3/07	SS
		W1		REVISED PER ECO-09-020935	09SEP09	KK

- $\triangle 1$ 2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL.
- $\triangle 2$ 0.76um[.000030] MIN GOLD, INTERNALLY, FOR A DISTANCE OF 5.08[.200] MIN FROM MATING END, GOLD FLASH ON THE REMAINDER, ALL OVER 0.76um[.000030] MIN NICKEL.
- $\triangle 3$ POSTS ARE SEMI AUTOMATICALLY WIREABLE AND WILL ACCOMODATE 3 TERMINATIONS.
- $\triangle 4$ AMP, PART NUMBER, AND DATE CODE MARKED IN THIS AREA.
5. #24 AWG MAX WIRE TO BE USED WITH THIS CONNECTOR.
- $\triangle 6$ 2.54um[.000100] MIN TIN OVER 1.27um[.000050] MIN NICKEL.
- $\triangle 7$ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

$\triangle 7$ OBSOLETE	$\triangle 6$	6-205511-2
	$\triangle 1$	1-205511-3
	POST PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. REIFSNYDER CHK R. STONE APVD M. MCALONIS	13 FEB 96 22 FEB 96 22 FEB 96	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC	± -	PRODUCT SPEC	
		1 PLC	± -	APPLICATION SPEC	
MATERIAL SEE CALLOUTS		2 PLC	± 0.13 [.005]	SIZE	
		3 PLC	± -	CAGE CODE	
FINISH SEE CALLOUTS		4 PLC	± -	DRAWING NO	
		ANGLES	± -	RESTRICTED TO	
		WEIGHT	-	A1 00779 C=205511	
		CUSTOMER DRAWING		SCALE	4:1
				SHEET	1 OF 1
				REV	W1