




PRODUCT NUMBER
SEE TABLE



mat'l. code				surface		tolerance		projection		product family													
				ISO 1302 ✓		ISO 406 ISO 1101				LATCH-N-LOK													
ltr ecn nodr date				tolerances unless otherwise specified						title													
H		ELX-N-008453		ZK		11/28/11		angles		linear		Xxxx.01/0.Xxx0.3 Xxxx.005/0.Xxx0.13 Xxxx0.0020/0.Xxx0.001		INCH/MM		2X6 LNL VERTICAL PANEL HEADER ASSEMBLY							
C		V01703		TFG		7/21/00		0°±2°				Xxxx0.0020/0.Xxx0.001		scale 1:1									
D		V10987		TFG		2/15/01		dr		M. CORMAN		6/25/90				dwg no				sheet 1 of 2		size	
E		M05-0050		MHT		3/16/05		engr		D. HORCHLER		6/25/90				78098				A3			
F		M06-0282		AGS		7/28/06		chr		D. HORCHLER		6/25/90											
G		M06-0365		AGS		9/20/06		appd		D. HORCHLER		6/25/90											
sheet		revision		H		H										type Product Customer Drawing							
index		sheet		1		2																	


78098-XXXXLF

LEAD FREE OPTION (6)(8)

	COLOR (4)	
1	70343 LT GRAY	OBS
2	80166 OFF WHITE	
3	70634 DK GRAY	OBS
4	701 BLACK	
5	70511 SLATE GRAY	OBS
7	70455 SILVER GRAY	
8	80189 PEARL WHITE	OBS
9	70419 PEBBLE GRAY	

	PLATING (3)
0	30u" MIN OVER 50u"MIN Ni
3	30u" MIN OVER 50u"MIN Ni
5	50u" MIN OVER 50u"MIN Ni

	PIN LENGTH
	DIM L
0	.200/5.08
1	.130/3.30



RECOMMENDED P.C.B. LAYOUT

NOTES:

- HEADER SHROUD
MAT'L: HIGH TEMPERATURE THERMOPLASTIC.
UL-94V-0 RATED.
- GROUND CONTACT
MAT'L: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06u" TIN
- SIGNAL CONTACT
MAT'L: COPPER ALLOY
PLATING OPTION: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT
ON CONTACT AREA OR TAIL, OPTIONALLY (78-295u") TIN ON TAIL.
- NUMBERS SHOWN ARE FOR G.E. LEXAN AND
ARE FOR REFERENCE ONLY.
- THIS ASSEMBLY U.L. APPROVED PER FILE E66906 VOL. 1, SEC. 84
AND CSA APPROVED PER MASTER FILE LR46923.
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PRODUCT SPEC: GS-12-003

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family LATCH-N-LOK	
ltr ecn nodr date		tolerances unless otherwise specified		title		dwg no		sheet 2 of 2 size	
H		angles 0°±2'		line XXX±.01/0.03 XXX±.005/0.03 XXX±.0020/0.005		scale 1:1		78098	
dr M. CORMAN 6/25/90		engr D. HORCHLER 6/25/90		chr D. HORCHLER 6/25/90		app D. HORCHLER 6/25/90		A3	
sheet index		revision sheet		type Product Customer Drawing					