



Circuit Diagram



Dimensions: (In.)

## ■ Specifications:

- Primary voltage: 117VAC 60Hz
- Primary exciting current: 25mA (max.)
- 41AC106 secondary voltage (no load): 8.47VDC  $\pm$  5%  
(full load): 6VDC  $\pm$  5%
- 41AC109 secondary voltage (no load): 12.23VDC  $\pm$  5%  
(full load): 9VDC  $\pm$  5%
- Rated secondary current: 100mA
- Breakdown voltage (hipot): 1500VAC 50Hz for 1 minute
- Coil~coil insulation: 100M $\Omega$  (min.) @ 500VDC
- Core size: EI-35
- Core material: hilite core H-23 .5mm
- Inner & outer insulation: polyester tape
- Bobbin: nylon 66 EI-35; 10 x 10mm double deck
- Impregnation: varnish
- Lead wire: 22AWG
- Cabinet: ABS black
- Capacitor: 470mfd 16V x 1pc.
- Rectifier: 1N4001 x 2 pc.
- AC plug: flat pins
- DC plug: 3.5mm male
- Cable: 6 ft.
- Insulation plate: 1 pc.
- Tip: positive

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[41AC109](#) [41AC106](#)