



# EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DIS-033-046

ECN : \_\_\_\_\_

REV : 1.1

PAGE : 1/8

## 5mm Infrared LED ,T-1 3/4

MODEL NO : SIR333/L9

### ■ Features :

- High radiant intensity
- Peak wavelength  $\lambda_p=875\text{nm}$
- View angle  $20^\circ$
- High reliability
- Low forward voltage
- Standard T-1 $^{3/4}$ (  $\phi 5\text{mm}$ ) package

### ■ Description :

- EVERLIGHT's Infrared Emitting Diode (SIR333/L9) is a high intensity diode, molded in a blue transparent plastic package.

The device is spectrally matched with phototransistor, photodiode and infrared receiver module.


### ■ Applications :

- Free air transmission system
- Optoelectronic switch
- Infrared remote control units with high power requirement
- Floppy disk drive
- Infrared source for optical counter and card reader

PART NO.	CHIP	LENS COLOR
	MATERIAL	
SIR	GaAlAs	Blue

DEVICE NUMBER : DIS-033-046REV : 1.1

ECN : \_\_\_\_\_

PAGE : 2/8**5mm Infrared LED ,T-1 3/4**MODEL NO : SIR333/L9**■ Package Dimensions :****■ Notes :**

1. All dimensions are in millimeter.
2. Protruded resin under flange 1.5 mm Max.
3. Lead spacing is measured where the lead emerge from the package.
4. Lens color : . Blue transparent.
5. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
6. These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.
7. When using this product , please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

DEVICE NUMBER : DIS-033-046

ECN : \_\_\_\_\_

REV : 1.1

PAGE : 3/8

**5mm Infrared LED ,T-1 3/4**

MODEL NO : SIR333/L9

**■ Absolute Maximum Ratings at  $T_A = 25^\circ\text{C}$** 

Parameter	Symbol	Rating	Unit	Notice
Continuous Forward Current	$I_F$	100	mA	
Peak Forward Current Pulse width=100 $\mu\text{s}$ , Duty cycle=1%	$I_{FP}$	1.0	A	
Reverse Voltage	$V_R$	5	V	
Operating Temperature	$T_{opr}$	-25 ~ +85	$^\circ\text{C}$	
Storage Temperature	$T_{stg}$	-40 ~ +85	$^\circ\text{C}$	
Soldering Temperature	$T_{sol}$	260	$^\circ\text{C}$	4mm from mold body less than 5 seconds
Power Dissipation at(or below) $25^\circ\text{C}$ Free Air Temperature	$P_d$	150	mW	

**■ Electronic Optical Characteristics :**

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Radiant Intensity	Ee	7.8	20	----	mW/sr	$I_F=20\text{mA}$
		----	95	----		$I_F=100\text{mA}, t_p=100 \mu\text{s}, t_p/T=0.01$
		----	920	----		$I_F=1\text{A}, t_p=100 \mu\text{s}, t_p/T=0.01$
Peak Wavelength	$\lambda_p$	----	875	----	nm	$I_F=20\text{mA}$
Spectral Bandwidth	$\Delta \lambda$	----	80	----	nm	$I_F=20\text{mA}$
Forward Voltage	$V_F$	----	1.3	1.6	V	$I_F=20\text{mA}$
		----	1.4	1.8		$I_F=100\text{mA}, t_p=100 \mu\text{s}, t_p/T=0.01$
		----	2.6	4.0		$I_F=1\text{A}, t_p=100 \mu\text{s}, t_p/T=0.01$
Reverse Current	$I_R$	----	----	10	$\mu\text{A}$	$V_R=5\text{V}$
View Angle	$2\Theta 1/2$	----	20	----	deg	$I_F=20\text{mA}$









DEVICE NUMBER : DIS-033-046 REV : 1.1  
ECN : \_\_\_\_\_ PAGE : 4/8**5mm Infrared LED ,T-1 3/4**MODEL NO : SIR333/L9**■ Typical Electrical/Optical/Characteristics Curves**Fig. 1 Forward Current vs.  
Ambient Temperature

Fig. 2 Spectral Distribution

Fig. 3 Peak Emission Wavelength vs.  
Ambient TemperatureFig. 4 Forward Current vs.  
Forward Voltage

DEVICE NUMBER : DIS-033-046

ECN : \_\_\_\_\_

REV : 1.1PAGE : 5/8**5mm Infrared LED ,T-1 3/4**MODEL NO : SIR333/L9**■ Typical Electrical/Optical/Characteristics Curves**Fig. 5 Relative Intensity vs.  
Forward CurrentFig. 6 Relative Radiant Intensity vs.  
Angular DisplacementFig. 7 Relative Intensity vs.  
Ambient Temperature (°C)Fig. 8 Forward Current vs.  
Ambient Temperature (°C)



# EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DIS-033-046

ECN : \_\_\_\_\_

REV : 1.1PAGE : 6/8

## 5mm Infrared LED ,T-1 3/4

MODEL NO : SIR333/L9

### ■ Reliability Test Item And Condition

The reliability of products shall be satisfied with items listed below.

Confidence level:90%

LTPD:10%

NO.	Item	Test Conditions	Test Hours/Cycles	Sample Sizes	Failure Judgement Criteria	Ac/Re
1	<b>Solder Heat</b>	TEMP : 260°C ± 5 °C	5 secs	22 pcs		0/1
2	<b>Temperature Cycle</b>	H : +85°C      30 mins 5 mins L : -55°C      30 mins	50 cycles	22 pcs	$I_R \geq U_x$ 2 $E_e \leq L_x$ 0.8 $V_F \geq U_x$ 1.2	0/1
3	<b>Thermal Shock</b>	H : +100°C      5 mins 10 secs L : -10°C      5 mins	50 cycles	22 pcs	U :Upper specification limit L :Lower specification limit	0/1
4	<b>High Temperature Storage</b>	TEMP. : +100°C	1000 hrs	22pcs		0/1
5	<b>Low Temperature Storage</b>	TEMP. : -55°C	1000 hrs	22 pcs		0/1
6	<b>DC Operating Life</b>	$I_F=20mA$	1000 hrs	22 pcs		0/1
7	<b>High Temperature / High Humidity</b>	85°C / 85% R.H.	1000 hrs	22 pcs		0/1

DEVICE NUMBER : DIS-033-046 REV : 1.1  
ECN : \_\_\_\_\_ PAGE : 7/8

## 5mm Infrared LED ,T-1 3/4


MODEL NO : SIR333/L9

### ■ Test Method For Power :

Condition :  $I_F=20$  mA

Test Item : Radiant Intensity

Unit : mW/sr



### ■ To Distinguish Intensity

( $T_a=25^\circ C$ )


Condition :  $I_F=20$  mA

Unit : mW/sr


Bin Number	M	N	P	Q
Min	7.8	11.0	15.0	21.0
Max	12.5	17.6	24.0	34.0

DEVICE NUMBER : DIS-033-046 REV : 1.1  
ECN : \_\_\_\_\_ PAGE : 8/8**5mm Infrared LED ,T-1 3/4**MODEL NO : SIR333/L9**■ Packing Specifications**


1. Bag



2. Box



3. Carton

**EVERLIGHT**

CPN:

P/N:



SIR333/L9

QTY:



CAT:

HUE:

REF:

LOT NO:

MADE IN TAIWAN

CPN : Customer's Production Number

P/N : Production Number

QTY : Packing Quantity

CAT : Ranks

HUE : Peak Wavelength

REF : Reference

LOT NO : Lot Number

MADE IN TAIWAN : Production place

**■ Packing Quantity Specification**

1. 500Pcs/1Bag , 6 Bags/1Box
2. 10 Boxes/1Carton