

WWS450H

2D CORDLESS SCANNER



Productivity Solutions for Small Businesses

The Wasp WWS450H 2D healthcare barcode scanner offers fast, efficient barcode scanning. Accurately read 1D and 2D barcodes with the WWS450H aggressive digital imager scan engine.

Simply plug the USB adapter (or optional PS2, RS232) into a PC to rapidly scan barcodes up to 160 feet away from the communication stand using wireless connectivity. Pair the WWS450H with an Android™ or iOS® device, including iPhone®, iPad®, or iPod®, to monitor operations in the field from up to 30' away from the smartphone or tablet device. Barcode data is instantly added to a spreadsheet, document, or database, without time-consuming manual data entries or inaccuracies.

With built-in antimicrobial technology, the WWS450H is ideal for use in pharmaceutical or hospital facilities, where protection against odor-and-stain causing bacteria is needed. The disinfectant-friendly housing safeguards the WWS450H from alcohol cleaning – preventing discoloration, corruptions, and hardware malfunction.

■ WASP WWS450H FEATURES

- ▶ Read 1D barcodes up to 20" away and 2D barcodes up to 12" away
- ▶ Ideal for use in healthcare, pharmacies, and medical packaging use
- ▶ Withstands multiple 4' drops to concrete
- ▶ Compatible with Android and iOS devices
- ▶ Connect wirelessly up to 160' (light of sight) from a PC and 30' from a mobile device
- ▶ Holds up to 256 scans in buffer memory should scanner be out of range
- ▶ Antimicrobial protection against odor-and-stain causing bacteria
- ▶ Support up to 7 scanners per base station

■ BENEFITS

- ▶ High speed, low power consumption eliminates the need to rescan
- ▶ Ergonomic design ensures comfortable use
- ▶ Durable construction eliminates down-time due to breakage
- ▶ Eliminate time-consuming manual data entry

■ WASP WWS450 SERIES COMMON USES

- ▶ Healthcare
- ▶ Pharmacies
- ▶ Medical packaging

WWS450H

2D CORDLESS SCANNER



Productivity Solutions for Small Businesses

SPECIFICATIONS

OPTICAL FEATURES	Light source: 625 nm
	Optical sensor: 752 x 480 pixels
	Resolution: 1D 3mil, 2D 5mil
	Depth of field: 0.8" to 22.4"
	Scan rate: 1D 100 scans/sec, 2D 60 frames/sec
ELECTRICAL CHARACTERISTICS	Operating voltage: +5 V $\pm 10\%$
	Current consumption: Idle 35 mA, Operating 230 mA
	Working hours: 16 hours (based on 1 scan/5 sec)
MECHANICAL CHARACTERISTICS	Dimensions: 6.0" H x 2.4" L x 3.7" W (15.3 cm H x 6.1 cm L x 9.3 cm W)
	Net weight: 6.5 oz
ENVIRONMENT CHARACTERISTICS	Operating temperature: 32°F to 122°F (0°C to 50°C)
	Storage temperature: -4°F to 140°F (-20°C to 60°C)
	Relative humidity: 5% to 95% (non-condensing)
	Mechanical shock: Withstands repeated 4 ft. (1.2 m) drops to concrete
	Ingress protection: IP30
	Electrostatic discharge: ± 8 kV contact ± 15 kV air
1D (LINEAR) SYMBOLOGIES READ	EMC regulation: BSMI, CE, C-trick, FCC, IC, NCC, KC, SRMC, TELEC
	Codabar, Code 39, Code 93, Code 128, GS1 DataBar (RSS), Industrial 2 of 5, Interleave 2 of 5, ISBT-128, Italian, Matrix 2 of 5, MSI, UPC-A, UPC-E, EAN-8, EAN-13, GS1-128 (EAN-128)
2D SYMBOLOGIES READ	PDF417, MicroPDF417, Composite, RSS, TLC-39, Datamatrix, QR code, Micro QR code, Aztec, MaxiCode
POSTAL CODES READ	US PostNet, US Planet, UK Postal, Australian Postal, Japan Postal, Dutch Postal (KIX)
PART NUMBERS	Wasp WWS450H 2D Healthcare Barcode Scanner with USB Base: 633808121549
	WaspProtect 2-Year Extended Warranty for WWS450/WWS450H Barcode Scanner: 633808391294