

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

FT

0

D2

REVISED PER ECO-11-005027

14MAR2011

RK

HMR

0.9±0.1

5.00±0.05

2.5 REF

TEST FACILITY

CLAMPING SCREW

0.60±0.05

284093-3 AS SHOWN

10.15±0.10

0.50±0.05

3.5±0.3

8.2

WIRE ENTRY

INTERLOCKING FEATURE

RECOMMENDED PC BOARD LAYOUT

5.0

1.1

0.1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.3

1 PLC ±.3

2 PLC ±.25

3 PLC ±.

4 PLC ±.

ANGLES ±2

MATERIAL

FINISH

DWN

E. ZANOLINI

10SEP2001

CHK

D. BIEVENOUR

10SEP2001

APVD

D. BIEVENOUR

10SEP2001

PRODUCT SPEC

10820166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING

NAME

TERMINAL BLOCK, PCB MOUNT

TOP ENTRY WIRE, STACKING

W/INTERLOCK, 5.00mm PITCH

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-284093

RESTRICTED TO

-

SCALE

4:1

SHEET

1

OF

2

REV

D2

125

25

2-284093-5

120

24

2-284093-4

115

23

2-284093-3

110

22

2-284093-2

105

21

2-284093-1

100

20

2-284093-0

95

19

1-284093-9

90

18

1-284093-8

85

17

1-284093-7

80

16

1-284093-6

75

15

1-282093-5

70

14

1-284093-4

65

13

1-284093-3

60

12

1-284093-2

55

11

1-284093-1

50

10

1-284093-0

45

9

284093-9

40

8

284093-8

35

7

284093-7

30

6

284093-6

25

5

284093-5

20

4

284093-4

15

3

284093-3

10

2

284093-2

DIM. A

N° OF POS.

PART NUMBER

1470-19 (3/11)

Pro/ENGINEER DRAWING

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.


3 END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

4 WIRE SIZE RANGE
SOLID WIRE: 0,03-1,5mm² (15AWG).
STRANDED WIRE: 0,03-1mm² (17AWG).



NOT CUMULATIVE TOLERANCE.

6 PART COMPLIES WITH EN 60335-1.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 10SEP2001	TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±2	CHK D. BIEVENOUR 10SEP2001				
		APVD D. BIEVENOUR 10SEP2001				
		PRODUCT SPEC -				
	MATERIAL -	APPLICATION SPEC -	NAME TERMINAL BLOCK, PCB MOUNT TOP ENTRY WIRE, STACKING W/INTERLOCK, 5.00mm PITCH			
		WEIGHT -				
		SIZE A3		CAGE CODE 00779	DRAWING NO C-284093	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 4:1	SHEET 2 OF 2	REV D2