

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					C	ECR-13-014508	13OCT2015	UKo	Ak
					C1	ECR-14-007162	21SET2017	AP	AK
					C2	ECR-18-017686 (Add prod. site; PN list update)	07MAY2019	HC	LS
					C3	ECR-24-204093 (Add prod. site CZ)	27MAR2024	Stei	Ried

Order Number - ABCCCC

made in Austria:

A : Line (1...Line1)

B : Day (1-7, Mon=1, Tue=2.)

C : Time(hhmm)

made in Czech Rep.:

A : Packing day (1-7, Sun=1)

B : Shift (1=day, 2=night)


C : Lot number (sequential)

made in Portugal:

A : Packing day (1-7, Sat=1)

B : Shift (1=day, 2=night)

C : Lot number (sequential)



Mark 2)

Mark 1)

AT : made in Austria

CZ : made in Czech Rep.

historic:

H : made in Switzerland (until 2013)

PT : made in Portugal (until 2023)

Q : made in China (until 2016)

C : made in China (until 2012)

Date code (YYWW)

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM00..	00	1.5	3-1462037-7		3-1462037-5	
IM00NS	00N	1.5				1-1462038-0*
IM01..	01	3	1462037-1	4-1462037-0	1462037-4	
IM01B..	01B	3	4-1462039-5			
IM01C..	01C	3	1462038-4			
IM01NS	01N	3				1-1462038-1
IM01N..L	01N	3				4-1462039-3
IM01P	01P	3	9-1462037-3			
IM02..	02	4.5	1462037-9	1-1462037-1	1-1462037-3	6-1462039-4
IM02..	02	4.5	8-1462039-1			
IM02..L	02	4.5	2-1462039-3			
IM02C..	02C	4.5	1462038-1			
IM02D..	02D	4.5	9-1462038-8			
IM02H..	02H	4.5	1-1462039-1			
IM02I..	02I	4.5	1462047-9	1462047-8		
IM02NS	02N	4.5				1-1462038-2

*obsolete

DRAWING ALIAS: IM0C-DOK17

DIMENSIONS:		DWN	21FEB2003	MATERIAL	FINISH
mm		HD 9121	21FEB2003	-	-
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK HD 9121	21FEB2003	 TE Connectivity	
0 PLC ±-		APVD HD 9121	21FEB2003		
1 PLC ±-		PRODUCT SPEC			
2 PLC ±-		APPLICATION SPEC			
3 PLC ±-				NAME IM-Relay Marking	
4 PLC ±-				SIZE	CAGE CODE
ANGLES ±-				A 4	00779
		WEIGHT	-	DRAWING NO	
				C- 1462037-1	
		CUSTOMER DRAWING		SCALE	10:1
				SHEET	1 OF 6
				REV	C3

2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2000



0 PLC ±-


1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-



REV 03

LOC HJ	DIST -	REVISIONS																																																																																																																																																																																										
		P	LTR	DESCRIPTION	DATE	DWN	APVD																																																																																																																																																																																					
			-	SEE SHEET 1	-	-	-																																																																																																																																																																																					
<table border="1"> <thead> <tr> <th>Relay-Typ</th> <th>Mark 1)</th> <th>Mark 2)</th> <th>PN (GR)</th> <th>PN (JR)</th> <th>PN (TS)</th> <th>PN (KS/NS)</th> </tr> </thead> <tbody> <tr> <td>IM07C ..</td> <td>07C</td> <td>24</td> <td>1462039-2</td> <td></td> <td>1462039-1</td> <td></td> </tr> <tr> <td>IM07D ..</td> <td>07D</td> <td>24</td> <td></td> <td>7-1462039-4</td> <td>7-1462039-2</td> <td></td> </tr> <tr> <td>IM07NS</td> <td>07N</td> <td>24</td> <td></td> <td></td> <td></td> <td>1-1462038-7</td> </tr> <tr> <td>IM08I ..</td> <td>08I</td> <td>2.4</td> <td></td> <td></td> <td>1462047-3</td> <td></td> </tr> <tr> <td>IM11..</td> <td>11</td> <td>3</td> <td>9-1462038-5</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM12..</td> <td>12</td> <td>4.5</td> <td>1462039-3</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM13..</td> <td>13</td> <td>5</td> <td>1462039-4</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM15..</td> <td>15</td> <td>9</td> <td>8-1462039-5</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM16..</td> <td>16</td> <td>12</td> <td>1462039-5</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM17..</td> <td>17</td> <td>24</td> <td>1462039-6</td> <td></td> <td>4-1462039-6</td> <td></td> </tr> <tr> <td>IM21..</td> <td>21</td> <td>3</td> <td>2-1462039-6</td> <td></td> <td>1-1462039-5</td> <td></td> </tr> <tr> <td>IM22..</td> <td>22</td> <td>4.5</td> <td>2-1462039-7</td> <td></td> <td>2-1462039-8</td> <td>8-1462039-9</td> </tr> <tr> <td>IM23..</td> <td>23</td> <td>5</td> <td>2-1462039-9</td> <td></td> <td>3-1462039-0</td> <td>6-1462039-7</td> </tr> <tr> <td>IM25..</td> <td>25</td> <td>9</td> <td>3-1462039-5</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM26..</td> <td>26</td> <td>12</td> <td>3-1462039-1</td> <td></td> <td>3-1462039-2</td> <td></td> </tr> <tr> <td>IM40..</td> <td>40</td> <td>1.5</td> <td>5-1462037-1</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM40D ..</td> <td>40D</td> <td>1.5</td> <td>8-1462039-4</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM40NS</td> <td>40N</td> <td>1.5</td> <td></td> <td></td> <td></td> <td>1-1462038-8</td> </tr> <tr> <td>IM41..</td> <td>41</td> <td>3</td> <td>5-1462037-4</td> <td>5-1462037-5</td> <td>5-1462037-3</td> <td></td> </tr> <tr> <td>IM41C ..</td> <td>41C</td> <td>3</td> <td>4-1462039-2</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM41D ..</td> <td>41D</td> <td>3</td> <td>6-1462039-8</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM41NS</td> <td>41N</td> <td>3</td> <td></td> <td></td> <td></td> <td>1-1462038-9</td> </tr> <tr> <td>IM42..</td> <td>42</td> <td>4.5</td> <td>3-1462037-1</td> <td>5-1462037-7</td> <td>5-1462037-6</td> <td></td> </tr> <tr> <td>IM42C ..</td> <td>42C</td> <td>4.5</td> <td>4-1462039-1</td> <td></td> <td></td> <td></td> </tr> <tr> <td>IM42D ..</td> <td>42D</td> <td>4.5</td> <td>1-1462039-9</td> <td></td> <td></td> <td></td> </tr> </tbody> </table>							Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)	IM07C ..	07C	24	1462039-2		1462039-1		IM07D ..	07D	24		7-1462039-4	7-1462039-2		IM07NS	07N	24				1-1462038-7	IM08I ..	08I	2.4			1462047-3		IM11..	11	3	9-1462038-5				IM12..	12	4.5	1462039-3				IM13..	13	5	1462039-4				IM15..	15	9	8-1462039-5				IM16..	16	12	1462039-5				IM17..	17	24	1462039-6		4-1462039-6		IM21..	21	3	2-1462039-6		1-1462039-5		IM22..	22	4.5	2-1462039-7		2-1462039-8	8-1462039-9	IM23..	23	5	2-1462039-9		3-1462039-0	6-1462039-7	IM25..	25	9	3-1462039-5				IM26..	26	12	3-1462039-1		3-1462039-2		IM40..	40	1.5	5-1462037-1				IM40D ..	40D	1.5	8-1462039-4				IM40NS	40N	1.5				1-1462038-8	IM41..	41	3	5-1462037-4	5-1462037-5	5-1462037-3		IM41C ..	41C	3	4-1462039-2				IM41D ..	41D	3	6-1462039-8				IM41NS	41N	3				1-1462038-9	IM42..	42	4.5	3-1462037-1	5-1462037-7	5-1462037-6		IM42C ..	42C	4.5	4-1462039-1				IM42D ..	42D	4.5	1-1462039-9			
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)																																																																																																																																																																																						
IM07C ..	07C	24	1462039-2		1462039-1																																																																																																																																																																																							
IM07D ..	07D	24		7-1462039-4	7-1462039-2																																																																																																																																																																																							
IM07NS	07N	24				1-1462038-7																																																																																																																																																																																						
IM08I ..	08I	2.4			1462047-3																																																																																																																																																																																							
IM11..	11	3	9-1462038-5																																																																																																																																																																																									
IM12..	12	4.5	1462039-3																																																																																																																																																																																									
IM13..	13	5	1462039-4																																																																																																																																																																																									
IM15..	15	9	8-1462039-5																																																																																																																																																																																									
IM16..	16	12	1462039-5																																																																																																																																																																																									
IM17..	17	24	1462039-6		4-1462039-6																																																																																																																																																																																							
IM21..	21	3	2-1462039-6		1-1462039-5																																																																																																																																																																																							
IM22..	22	4.5	2-1462039-7		2-1462039-8	8-1462039-9																																																																																																																																																																																						
IM23..	23	5	2-1462039-9		3-1462039-0	6-1462039-7																																																																																																																																																																																						
IM25..	25	9	3-1462039-5																																																																																																																																																																																									
IM26..	26	12	3-1462039-1		3-1462039-2																																																																																																																																																																																							
IM40..	40	1.5	5-1462037-1																																																																																																																																																																																									
IM40D ..	40D	1.5	8-1462039-4																																																																																																																																																																																									
IM40NS	40N	1.5				1-1462038-8																																																																																																																																																																																						
IM41..	41	3	5-1462037-4	5-1462037-5	5-1462037-3																																																																																																																																																																																							
IM41C ..	41C	3	4-1462039-2																																																																																																																																																																																									
IM41D ..	41D	3	6-1462039-8																																																																																																																																																																																									
IM41NS	41N	3				1-1462038-9																																																																																																																																																																																						
IM42..	42	4.5	3-1462037-1	5-1462037-7	5-1462037-6																																																																																																																																																																																							
IM42C ..	42C	4.5	4-1462039-1																																																																																																																																																																																									
IM42D ..	42D	4.5	1-1462039-9																																																																																																																																																																																									
*obsolete																																																																																																																																																																																												
DIMENSIONS: mm		DWN HD 9121 21FEB2003	MATERIAL -		DRAWING ALIAS: IM0C-DOK17																																																																																																																																																																																							
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK HD 9121 21FEB2003	 TE Connectivity																																																																																																																																																																																									
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		APVD HD 9121 21FEB2003																																																																																																																																																																																										
PRODUCT SPEC -																																																																																																																																																																																												
APPLICATION SPEC -		NAME IM-Relay Marking		SIZE A 4																																																																																																																																																																																								
WEIGHT -		CAGE CODE 00779		DRAWING NO C- 1462037-1		RESTRICTED TO -																																																																																																																																																																																						
CUSTOMER DRAWING		SCALE 10:1		SHEET 3 OF 6		REV C3																																																																																																																																																																																						


2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2000



LOC	DIST	REVISIONS					
HJ	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM42DNS	42D	4.5				1-1462039-6
IM42NS	42N	4.5				2-1462038-0
IM42P..	42P	4.5	5-1462039-7			
IM42PNS	42P	4.5				7-1462039-8
IM43..	43	5	5-1462037-9	6-1462037-0	5-1462037-8	
IM43C..	43C	5	9-1462038-7			
IM43NS	43N	5				2-1462038-1
IM44..	44	6	6-1462037-2	6-1462037-3	6-1462037-1	
IM44NS	44N	6				2-1462038-2
IM45..	45	9	6-1462037-4	6-1462037-5	3-1462037-2	
IM45I..	45I	9	1462047-5			
IM45NS	45	9				2-1462038-3
IM46..	46	12	6-1462037-7	6-1462037-8	6-1462037-6	
IM46C..	46C	12	8-1462039-0			
IM46NS	46N	12				2-1462038-4
IM46PNS	46P	12				6-1462039-1
IM47..	47	24	7-1462037-0		6-1462037-9	
IM47D..	47D	24		7-1462039-5		
IM47NS	47N	24				2-1462038-5
IM48..	48	2.4	1462039-8			
IM48D..	48D	2.4	1462039-9			
IM48C..	48C	2,4	9-1462039-0			
IM48I..	48I	2.4	1462047-1			
IM49I..	49I	2	1462047-4			

*obsolete

DRAWING ALIAS: IMOC-DOK17

DIMENSIONS:

11

DWN	21FEB2003
-----	-----------

MATERIAL

FINISH

CHK	21FFB2003
-----	-----------

AD 9121	
1512	21FEB2003

HD 9121

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT	
--------	--


CUSTOMER DRAWING:

TE TE Connectivity

NAME	IM-Relay Marking
------	---------------------

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A 4	00779	C- 1462037-1	-

SCALE		10:1	SHEET		4	OF	6	REV	C3
-------	--	------	-------	--	---	----	---	-----	----



LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IM61..	61	3	7-1462039-7						
IM68..	68	2.4	8-1462039-2						
IMB01C ..	B01C	3	1462041-1		1462041-4				
IMB02C ..	B02C	4.5	1462041-2						
IMB03C ..	B03C	5	1462041-7						
IMB03C ..E	B03C	5	1-1462041-8						
IMB04C ..	B04C	6	1462041-9		1-1462041-1				
IMB05C ..	B05C	9	1-1462041-0		1-1462041-2				
IMB06C ..	B06C	12	1462041-3		1462041-6				
IMB07C ..	B07C	24	1-1462041-3		1-1462041-4				
IMB32B..	B32B	4.5	2-1462041-0						
IMB33B..	B33B	5	1-1462041-9						
IMB41C ..	B41C	3	1-1462041-7						
IMB42C ..	B42C	4.5	1-1462041-6		1-1462041-5				
*obsolete									
DIMENSIONS:			DWN	21FEB2003	MATERIAL		DRAWING ALIAS:		
mm			HD 9121		-		IM0C-DOK17		
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m			CHK	21FEB2003			FINISH		
			HD 9121				-		
			APVD	21FEB2003					
			HD 9121						
			PRODUCT SPEC						
			APPLICATION SPEC						
			WEIGHT						
			CUSTOMER DRAWING		SCALE		SHEET		REV
					10:1		5 OF 6		C3

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

TE

TE Connectivity

IM-Relay Marking

SIZE: A 4
CAGE CODE: 00779
DRAWING NO: C-1462037-1
RESTRICTED TO: -


2000

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 2000

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IMC01..	C01	3	1462042-1		1462042-4				
IMC02..	C02	4.5	1462042-2		1462042-5				
IMC03..	C03	5	1462042-8		1462042-7				
IMC06..	C06	12	1462042-3		1462042-6				
IMC07..	C07	24	1-1462042-1		1-1462042-2				
IMC02C..	C02C	4.5	1-1462042-0						
IMC03C..	C03C	5	1-1462042-5						
IMC06C..	C06C	12	1462042-9		1-1462042-4				
IMC41C..	C41C	3			1-1462042-3				
IME01..	E01	3	1462043-1		1462043-5				
IME02..	E02	4.5	1462043-2		1462043-6				
IME03..	E03	5	1462043-3		1462043-7				
IME06..	E06	12	1462043-4		1462043-8				
IMF61..	F61	3	1462048-3						
IMF68..	F68	2.4	1-1462048-0						
*obsolete									
DIMENSIONS:		DWN		21FEB2003		MATERIAL		DRAWING ALIAS:	
mm		HD 9121				-		IM0C-DOK17	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK		21FEB2003		 TE Connectivity			
		HD 9121							
		APVD		21FEB2003					
		HD 9121							
0 PLC ±-		PRODUCT SPEC		NAME		IM-Relay			
1 PLC ±-		-				Marking			
2 PLC ±-		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO	
3 PLC ±-		-		A 4		00779		C- 1462037-1	
4 PLC ±-		WEIGHT		-				RESTRICTED TO	
ANGLES ±-		-						-	
		CUSTOMER DRAWING		SCALE		10:1		SHEET 6 OF 6	
								REV C3	

2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2000

THIS DRAWING IS UNPUBLISHED.