

DESCRIPTION

The SG1536 series of monolithic amplifiers is designed specifically for use in high voltage applications up to $\pm 40V$ and where high common-mode input ranges, high output voltage swings, and low input

currents are required. These devices are internally compensated and are pin compatible with industry standard operational amplifiers.


IMPORTANT: For the most current data, consult MICROSEMI's website: <http://www.microsemi.com>

KEY FEATURES

- High Supply Voltage Capability
- High Output Voltage Swing
- High Common-Mode Voltage Range
- Internal Frequency Compensation
- Input Current 35nA Maximum Over Temperature

HIGH RELIABILITY FEATURES


- Available to MIL-STD-883D and DESC SMD
- Microsemi LEVEL "S" Processing Available

PRODUCT HIGHLIGHT


M & Y PACKAGE

(Top View)

M Package: RoHS / Pb-free 100% Matte Tin Lead Finish†



T PACKAGE

(Top View)

PACKAGE ORDER INFO

T_A (°C)	M Plastic DIP 8-Pin	Y Plastic DIP 8-Pin	T TO-99 Metal Can 8-Pin
	RoHS Compliant / Pb-free Transition DC: 0503*		
0 to 70	SG1436M	SG1436Y	SG1436T
-55 to 125	-	SG1536Y	SG1536T
MIL-STD-883	-	SG1536Y/883B	SG1536T/883B
DESC	-	SG1536Y/DESC	SG1536T/DESC

Note: Available in Tape & Reel. Append the letters "TR" to the part number. (i.e. SG1536Y-TR)

†Peak Package Solder Reflow Temperature (40 seconds maximum exposure) 260°C (+0, -5)

HIGH-VOLTAGE OPERATIONAL AMPLIFIER

DESCRIPTION

The SG1536 series of monolithic amplifiers is designed specifically for use in high voltage applications up to $\pm 40V$ and where high common-mode input ranges, high output voltage swings, and low input currents are required. These devices are internally compensated and are pin compatible with industry standard operational amplifiers.


FEATURES

- High supply voltage capability
- High output voltage swing
- High common-mode voltage range
- Internal frequency compensation
- Input current 35nA maximum over temperature

HIGH RELIABILITY FEATURES -SG1536

- ♦ Available to MIL-STD-883 and DESC SMD
- ♦ SG level "S" processing available


CIRCUIT SCHEMATIC




ABSOLUTE MAXIMUM RATINGS (Note 1)

Supply Voltage	
SG1536	$\pm 40V$
SG1436	$\pm 34V$
Differential Input Signal	$\pm(V^+ + V^- - 3)V$
Common-Mode Input Swing	$\pm V^+, -(V^- - 3)V$

Note 1. Exceeding these ratings could cause damage to the device.

THERMAL DERATING CURVES

Output Short Circuit Duration	5.0sec
($V^+ = V^- = 28V, V_O = 0V$)	
Operating Junction Temperature	
Hermetic (T, Y-Package)	150°C
Storage Temperature Range	-65°C to 150°C
Lead Temperature (Soldering, 10 Seconds)	300°C

**RECOMMENDED OPERATING CONDITIONS** (Note 2)

Supply Voltage	
SG1536	$\pm 28V$
SG1436	$\pm 15V$

Operating Ambient Temperature Range (T_A)

SG1536	-55°C to 125°C
SG1436	0°C to 70°C

Note 2. Range over which the device is functional.

ELECTRICAL SPECIFICATIONS






(Unless otherwise specified, these specifications apply for the operating ambient temperature of $T_A = 25^\circ\text{C}$, and $V_S = \pm 28V$. Low duty cycle pulse testing techniques are used which maintains junction and case temperatures equal to the ambient temperature.)

Parameter	Test Conditions	SG1536			SG1436			Units
		Min.	Typ.	Max.	Min.	Typ.	Max.	
Input Offset Voltage	$T_A = T_{\text{MIN}}$ to T_{MAX}	2.0		5.0	5.0		10	mV
Input Offset Current	$T_A = T_{\text{MIN}}$	1.0		7.0			14	mV
	$T_A = T_{\text{MAX}}$			3.0	5.0		10	nA
Input Bias Current	$T_A = T_{\text{MIN}}$			7.0			14	nA
	$T_A = T_{\text{MAX}}$			4.5			14	nA
Differential Input Impedance	$T_A = T_{\text{MIN}}$ to T_{MAX}	8.0		20	15		40	nA
Common-Mode Input Impedance	Open loop, $\leq 5.0\text{Hz}$			35			55	nA
Common-Mode Input Voltage	$f \leq 5.0\text{Hz}$	10			10			MΩ
Range (Peak)		250			250			MΩ
Common-Mode Rejection Ratio		± 24	± 25		± 22	± 25		V
Large Signal Voltage Gain	$R_L = 10K\Omega, V_O = \pm 10V$	80	110		70	100		dB
	$R_L = 100K\Omega, V_O = \pm 10V$		200K			200K		V/V
Power Supply Rejection Ratio	$T_A = T_{\text{MIN}}$ to T_{MAX}	100K	500K		70K	500K		V/V
	V^+ constant, $R_S \leq 10K\Omega$	50K			50K			V/V
	V^- constant, $R_S \leq 10K\Omega$		15	100		35	200	$\mu\text{V/V}$
Output Impedance	$f \leq 5.0\text{Hz}$		15	100		35	200	$\mu\text{V/V}$
Short Circuit Output Current			1.0			1.0		KΩ
Output Voltage Swing (Peak)	$R_L = 5.0K\Omega, V_S = \pm 28V$	± 22			± 22			V
	$R_L = 5.0K\Omega, V_S = \pm 36V$	± 30			± 30			V

ELECTRICAL SPECIFICATIONS (continued)

Parameter	Test Conditions	SG1536			SG1436			Units
		Min.	Typ.	Max.	Min.	Typ.	Max.	
Power Bandwidth	$A_v = +1$, $R_L = 5.0\text{K}\Omega$, $\text{THD} \leq 5\%$, $V_O = 40\text{V p-p}$		23		23			KHz
Unity Gain Crossover Frequency	Open loop	1.0			1.0			MHz
Slew Rate	Unity gain	2.0			2.0			V/ μs
Phase Margin	Open loop, unity gain	50			50			deg
Gain Margin		18			18			dB
Equivalent Input Noise	$A_v = 100$, $R_s = 10\text{K}\Omega$, $f = 1.0\text{KHz}$, $\text{BW} = 1.0\text{ Hz}$	50			50			nV/ $\sqrt{\text{Hz}}$
Power Supply Current		2.2	4.0		2.6	5.0		mA
Power Consumption	$V_O = 0$	124	224		146	280		mW

CHARACTERISTIC CURVES

FIGURE 1.
POWER BANDWIDTHFIGURE 2.
PEAK OUTPUT VOLTAGE SWING VS.
POWER SUPPLY VOLTAGEFIGURE 3.
OPEN-LOOP FREQUENCY RESPONSEFIGURE 4.
OUTPUT SHORT-CIRCUIT CURRENT VS.
TEMPERATUREFIGURE 5.
INPUT BIAS CURRENT VS.
TEMPERATURE

TYPICAL APPLICATIONS




FIGURE 6 - VOLTAGE OFFSET NULL CIRCUIT




FIGURE 7 - DIFFERENTIAL AMPLIFIER WITH $\pm 20V$ COMMON-MODE INPUT VOLTAGE RANGE




FIGURE 8 - LOW-DRIFT SAMPLE AND HOLD




FIGURE 9 - TYPICAL NON-INVERTING X10 VOLTAGE AMPLIFIER




FIGURE 10 - VOLTAGE CONTROLLED CURRENT SOURCE OR TRANSCONDUCTANCE AMPLIFIER WITH 0 TO 40V COMPLIANCE

CONNECTION DIAGRAMS & ORDERING INFORMATION (See Notes Below)

Package	Part No.	Ambient Temperature Range	Connection Diagram
8-PIN METAL CAN T - PACKAGE	SG1536T/883B SG1536T SG1436T	-55°C to 125°C -55°C to 125°C 0°C to 70°C	
8-PIN CERAMIC DIP Y - PACKAGE	SG1536Y/883B SG1536Y SG1436Y	-55°C to 125°C -55°C to 125°C 0°C to 70°C	

Note 1. Contact factory for JAN and DESC product availability.
2. All packages are viewed from the top.