

Distributed by:




JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 739024

LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
	35				F	REV PER EC 0410-43-97	02 JUN 97	JGH
					G	OBSOLETE -6	29 JUL 97	JGH
					H	PER EC 0410-202-96		
						REV PER EC 0410-56-97	06 OCT 97	JGH
					J	REACTIVATE -6	10 APR 00	SLB
						PER EC 051A-0114-00		



- 1 DOUBLE BAR POLARIZATION
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4 CENTER POLARIZATION SLOT
- 5 FOR 10 POSN ASSEMBLY, SLOT OMITTED WHERE INDICATED
- 6 CENTER STANDOFF RIB(S) ARE OPTIONAL.
- 7 NUMBER 1 POSITION.
- 8 THE RETENTIVE FEATURE ON THIS CONNECTOR WAS DESIGNED TO BE USED FULLY SEATED IN A CIRCUIT BOARD HAVING A THICKNESS OF .062 $\pm$.007 FOR CONNECTORS HAVING RETENTIVE FEATURES DESIGNED FOR USE IN CIRCUIT BOARDS OF OTHER THICKNESSES CONTACT AMP INCORPORATED.
- 9 LOCATION OF HOLD-DOWN POSTS (4 PLACES).
- 10 OPTIONAL AMP IDENTIFICATION NUMBER (DATE CODE). LOCATION APPROXIMATELY WHERE SHOWN.

3.300	2.900	29	60	1-104338-0
2.800	2.400	24	50	104338-9
2.300	1.900	19	40	104338-8
2.000	1.600	16	34	104338-7
1.600	1.200	12	26	104338-6
1.500	1.100	11	24	104338-5
1.300	.900	9	20	104338-4
1.100	.700	7	16	104338-3
1.000	.600	6	14	104338-2
.800	.400	4	10	104338-1
C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON :		DR 1-28-88 H MOLL	AMP INCORPORATED Harrisburg, Pa. 17105	
2 PL DEC $\pm$.005 3 PL DEC $\pm$.005 ANGLES $\pm$.		CHK 2-2-88 T.C. CLARK		
MATERIAL: HOUSING: POLYESTER OR NYLON		APPD 2-2-88 R. ELICKER	NAME	
POSTS: PH05 BRONZE		PRODUCT SPEC 108-40018	HEADER ASSY, LOW PROFILE, HIGH TEMP, AMP-LATCH™	
FINISH: POSTS: .000015 GOLD IN CONTACT AREA, .000100-.000200 TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL		APPLICATION SPEC -	SIZE D	FSCM NO 00779
		WEIGHT -	SCALE 4:1	DRAWING NO 104338
				SHEET 1 OF 1