










www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2006/11/14	ANGULAR	LINEAR	0.X ±0.3		size A2	Scale 2:1		
Eng	P LEGARE	2006/11/14			0.XX ±0.1					
Chr	P LEGARE	2006/11/14			0.XXX ±0.05					
Appr	P LEGARE	2006/11/14	0° ±2°		ECN		F10-0072			
Product family					-		Spec ref			
			title SUB MALE DMW full power without contact			dwg no C01-8637-1732			Rev. C	
catalog no			-			CUSTOMER			sheet 2 of 4	




2V2




3V3



3W3



SIDE VIEW FOR
LAYOUTS: E A B C



Copyright FCI.

REV E - 2006-03-28


www.fciconnect.com			Surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	M PESSON	2006/11/14	ANGULAR	LINEAR	0.X	±0.3	size	A2			
Eng	P LEGARE	2006/11/14			0.XX	±0.1					
Chr	P LEGARE	2006/11/14			0° ±2°	0.XXX	±0.05	ECN F10-0072			
Appr	P LEGARE	2006/11/14	Product family				-	Spec ref			
			title SUB MALE DMW			dwg no C01-8637-1732			Rev. C		
			full power without contact								
			catalog no			-			CUSTOMER		sheet 3 of 4

PDS: Rev :C

PDM: Rev:0

STATUS:Released

ReleasedPrinted: Jun 18, 2015



Copyright FCI.

www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 				
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	M PESSON	2006/11/14	ANGULAR 0° ±2°	LINEAR	0.X ±0.3		size A2	Scale 2:1			
Eng	P LEGARE	2006/11/14			0.XX ±0.1						
Chr	P LEGARE	2006/11/14			0.XXX ±0.05						
Appr	P LEGARE	2006/11/14	Product family				ECN F10-0072				
							-		Spec ref		
			title SUB MALE DMW				dwg no C01-8637-1732			Rev.	
			full power without contact							C	
			catalog no -				CUSTOMER		sheet 4 of 4		