





PRODUCT NUMBER
88903-XYX
88903-XYXLF



NOTES:

- FOR DIM A, AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL POLYMER 30 % GLASS, FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL: PHOSPHOR BRONZE
- PLATING ON PRESS-FIT TAIL:
88903-XYX IS SnPb
88903-XYXLF IS Sn (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
PART NUMBER DESIGNATION J8 BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES. IF TRAY PACKAGING IS REQUIRED, SUFFIX "P" WILL BE ADDED TO THE END OF THE PART NUMBER. EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF
- PRODUCT SPECIFICATION: GS-12-180
APPLICATION SPECIFICATION: BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH QUALIFIED TOOL.
- Ayy PLATING HAS Au FLASH IN PRESS-FIT AREA (LEAD FREE)
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN 'LF' MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- FOR LEAD FREE PART NUMBERS, ADD AN 'LF' SUFFIX. EXAMPLE: 88903-X01LF.
- ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING (DRAWING NO.)-N1--- OR (DRAWING NO.)-N5--- WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1--- AND (DRAWING NO.)-N5--- WILL NOT WITHSTAND REFLOW AND Au CONTACT SURFACES OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM OF 140°C FOR NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING IN CONTACT AREA

DASH NUMBER	PERFORMANCE LEVEL	NOTES
-PYY	0.25 um GOLD MIN.	SEE NOTE 9
-NIYY	TELCORDIA CO (NXT)	-
-N5YY	TELCORDIA UE (NXT)	-
-IYY	TELCORDIA CO	-
-2YY	TELECOM CLASS	-
-3YY	IEC CLASS I	-
-5YY	TELCORDIA UE	-
-NIYYLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 10
-N5YYLF	TELCORDIA UE (NXT)	SEE NOTE 10
-IYYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 10
-2YYLF	TELECOM CLASS	SEE NOTE 10
-5YYLF	TELCORDIA UE	SEE NOTE 10

mat'l code				tolerances unless otherwise specified		CUSTOMER	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY	
S	V06-0305	LP	04/10/06		0.XX ±0.13	projection	
T	V06-0433	DAI	2006-05-09		.XXX ±.051		
U	V06-0984	DCH	2006-09-29	angles	0° ±2°		
V	DG09-0256	TER	2009-08-19	dr	T.BRUNGARD 11/19/99	MM	
W	DG10-0243	TER	2010-06-28	enrg	M.STRAWSEY 11/19/99	scale	
-	-	-	-	chr	M.STRAWSEY 11/19/99		
R	V06-0211	LP	3/8/06	appd	M.STRAWSEY 02/29/00		
sheet	revision	W	W	W	W		
index	sheet	1	2	3	4		



www.fciconnect.com

title
METRAL SIGNAL HEADER
2 MOD, 5 ROW PRESS-FIT

product family METRAL

size dwg no

88903

code 213

sheet 1 of 4

code code 22526

Pro/E


PDM: Rev:W

STATUS Released

Printed: Jul 01 2010



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
12	7.25	17.00
19	8.00	4.30
23	8.00	17.70
25	5.75	15.60
42	7.25	15.60



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCi www.fciconnect.com				
lfr	ecn no.	dr	date	linear	0.X ±0.3		COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT			
W					0.XX ±0.13		projection					
					.XXX ±.051							
				angles	0° ±2°				product family METRAL code 213 sheet 2			
				dr	T.BRUNGARD	11/19/99	MM scale 1:1					
				enrg	M.STRAWSER	11/19/99						
				chr	M.STRAWSER	11/19/99						
				appd	M.STRAWSER	02/29/00						
sheet index	revision sheet											

Pro/E

PDM: Rev:W

STATUS **Released**

Printed: Jul 01 2010



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X01 SEE NOTE 11 FOR LEAD FREE	E	2	2	2	2	4	19	19	2	19	19
	D	2	2	2	2	2	19	19	2	19	19
	C	2	2	2	2	2	19	19	2	19	19
	B	2	2	2	2	2	19	19	2	19	19
	A	2	2	1	2	2	19	19	2	19	19
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X02 SEE NOTE 11 FOR LEAD FREE	E	12	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25
	C	25	25	23	25	25	23	25	25	25	25
	B	25	25	25	25	12	25	25	25	25	25
	A	12	25	25	25	25	25	25	25	25	25
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X03 SEE NOTE 11 FOR LEAD FREE	E	2	2	1	1	1	1	1	1	1	2
	D	2	2	1	1	1	1	1	1	1	2
	C	2	2	1	1	1	1	1	1	1	2
	B	2	2	1	1	1	1	1	1	1	2
	A	2	2	1	1	1	1	1	1	1	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X04 SEE NOTE 11 FOR LEAD FREE	E	7	6	6	6	6	6	6	6	6	6
	D	7	6	6	6	6	6	6	6	6	6
	C	7	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6
	A	7	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X05 SEE NOTE 11 FOR LEAD FREE	E	3	2	2	2	2	2	2	2	2	2
	D	3	2	2	2	2	2	2	2	2	2
	C	3	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2
	A	3	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X06 SEE NOTE 11 FOR LEAD FREE	E	3	2	2	2	2	2	1	2	2	2
	D	3	2	2	2	2	2	3	2	2	2
	C	3	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	1
	A	3	2	2	2	2	2	2	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X07 SEE NOTE 11 FOR LEAD FREE	E	2	2	2	2	2	2	2	2	4	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	4	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X08 SEE NOTE 11 FOR LEAD FREE	E	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25
	C	25	42	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25
	A	25	25	25	25	25	25	25	25	25	25
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X09 SEE NOTE 11 FOR LEAD FREE	E	2	2	3	2	2	3	2	2	4	2
	D	2	2	3	2	2	3	2	2	4	2
	C	2	2	3	2	2	3	2	2	4	2
	B	2	2	3	2	2	3	2	2	4	2
	A	2	2	3	2	2	3	2	2	4	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X10 SEE NOTE 11 FOR LEAD FREE	E	2	2	3	2	2	3	2	3	2	3
	D	2	2	3	2	2	3	2	3	2	3
	C	2	2	3	2	2	3	3	3	3	3
	B	2	2	3	2	2	3	1	3	2	3
	A	2	2	3	2	2	3	1	3	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X11 SEE NOTE 11 FOR LEAD FREE	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X12 SEE NOTE 11 FOR LEAD FREE	E	2	2	3	2	2	2	2	2	2	2
	D	2	2	3	2	2	2	2	2	2	2
	C	2	2	3	2	2	2	2	2	2	2
	B	2	2	3	2	2	2	2	2	2	2
	A	2	2	3	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X13 SEE NOTE 11 FOR LEAD FREE	E	1	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88903-X14 ----- 88903-X14LF	E	4	-	4	-	4	-	2	-	2	-
	D	-	3	-	3	-	2	-	2	-	19
	C	4	-	4	-	4	-	2	-	2	-
	B	-	3	-	3	-	2	-	2	-	19
	A	1	-	1	-	4	-	2	-	2	-

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com		
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		projection		title		
W					0.XX ±0.13					METRAL SIGNAL HEADER		
					.XXX ±.051					2 MOD, 5 ROW PRESS-FIT		
				angles	0° ±2°					product family		
				dr	T.BRUNGARD 11/19/99					METRAL		
				enrg	M.STRAWSER 11/19/99					code		
				chr	M.STRAWSER 11/19/99					213		
				appd	M.STRAWSER 02/29/00					sheet		
										3		
sheet index	revision											
	sheet											

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
88903-X20	E	4	2	2	2	2	2	4	2	2	2	2	2
	D	4	2	2	2	2	2	4	2	2	2	2	2
-----	C	4	2	2	2	2	2	4	2	2	2	2	2
88903-X20LF	B	4	2	2	2	2	2	4	2	2	2	2	2
	A	4	2	2	2	1	4	4	2	2	2	1	4

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
88903-X22	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
-----	C	2	2	2	2	2	2	2	2	2	2	2	2
88903-X22LF	B	2	2	2	2	2	2	3	2	2	2	2	2
	A	2	2	2	2	2	2	3	2	2	2	2	2

