

3M

Scotch-Weld™

Polyurethane Sealant

DP-5001, Black

Technical Data

July, 2006

Product Description

3M™ Scotch-Weld™ Polyurethane Sealant DP-5001 is a black, fast-setting, two-component polyurethane. It is packaged as 1:1 ratio liquids in duo-pak cartridges. With the squeeze of the trigger, the components are automatically mixed through a mixing tip and easily dispensed.

Suggested Applications

- Repairing tears and worn spots
- Protection of belt fasteners to prevent wear of splices
- Repair of conveyor belts in mines

Features

- Fast-setting to reduce downtime
- Abrasion resistant
- Remains flexible at low temperature
- Automatic one-step mixing and dispensing decreases waste
- Balanced, low-viscosity, liquid components form an easy-to-use paste
- Withstands a wide range of temperatures
- 100% urethane
- Odorless application

3M

Scotch-Weld™

Polyurethane Sealant

DP-5001, Black

Typical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Test	Conditions	Test Method	Properties
Viscosity Mixture	68°F (20°C)	Brookfield HBDVI* CP	100,000 cps
Work Life	10 g, 1/6" thick @ 77°F (25°C)	PEC	60 seconds
Tack-Free Time	10 g, 1/6" thick @ 77°F (25°C)	PEC	15 minutes
Full Cure Time	10 g, 1/6" thick @ 77°F (25°C)	PEC	12 hours
Hardness	24 hours @ 77°F (25°C)	ASTM D2240-91	72 Shore A
Lapshear	24 hours @ 77°F (25°C)	ASTM D1002-72	600 psi
Temperature Range	Continuous	PEC	-60°F (-51°C) to 250°F (121°C)

Conveyor Belt Repair

Section 1: Preparation

General Preparation of the Dual Cartridge/Dispenser/Mixer Tip Assembly:

1. Select the desired dispenser (manual or pneumatic) and the mix tip.
2. Cut the blind-end off of the cartridge orifice, or remove the cap.
3. Place the cartridge in the dispenser.
4. Dispense just enough material so that both components dispense equally.
5. Assemble the mix tip onto the cartridge.

Preparation of Repair Area

Note: 3M™ Scotch-Weld™ Polyurethane Sealant DP-5001 is a primerless system which cures at room temperature. For optimum results, it is recommended that cure be accelerated with heat.

Preparation of Repair Area For Splicing

1. Clean repair area thoroughly with acetone* at least 6 inches beyond the repair area to remove any contaminants from the area to be repaired. Allow to dry.
2. After cutting the belt for the splice, use normal skiving procedures to skive the belt 5-6 inches on both sides of the cut.
3. Use a template to mark holes for the clips.
4. Punch the holes out manually or use an impact wrench.
5. Bevel both sides of the splice.
6. Use a coarse sanding disk to grind 2-3 inches beyond the repair.
7. Remove all grinding debris with compressed air. Make sure air lines are dry.
8. Clean thoroughly about 2 inches beyond the ground area with acetone*. Allow to dry 20-30 minutes at room temperature.
9. Attach clips to all holes.
10. Use duct tape to keep Scotch-Weld sealant DP-5001 off of the clip hinges.
11. Use duct tape to dam both sides of the belt area to be filled.

***Note: When using solvents, be sure to extinguish all ignition sources and follow the manufacturer's precautions and directions for use.**

3M

Scotch-Weld™

Polyurethane Sealant

DP-5001, Black

Conveyor Belt Repair (continued)

Section 2: Application

1. Fill the cut out section and be sure to apply material to ground sections on the surface. Use a spreader to spread 3M™ Scotch-Weld™ Polyurethane Sealant DP-5001 into ground areas. Do not apply or spread beyond the scuffed areas. Use masking tape to keep Scotch-Weld sealant DP-5001 off of the non-scuffed areas. **Note:** When applying Scotch-Weld sealant DP-5001 on a tilted or non-horizontal surface, use a spreader to keep working the Scotch-Weld sealant DP-5001 into the void.
2. Allow to cure at room temperature for 2 hours or use heat cure to accelerate the cure.

Heat Cure

1. Apply heat (heat gun or preferably a heat tunnel) to the area of belt that was repaired, including the 2-3 inches ground on both sides. In a heat tunnel, temperature should be 170°F (76°C) for 20 minutes or 250°F (121°C) for 5 minutes. (A heat tunnel can be easily made with air conditioning duct.) If a heat gun is used, heat on HIGH for 20 minutes. Hold the gun 6-8 inches above the belt and use a constant back-and-forth motion to distribute the heat evenly.
2. Let the repair cool to room temperature and remove all damming duct tape.

Preparation of Repair Area For Gouges And Holes

Note: Repairing gouges and holes are done in the same manner with the exception that repairing holes requires the extra step of damming the bottom of the belt as stated in Step 4 below. When repairing gouges, skip the following Step 4.

1. Clean with acetone* to remove any contaminants from the area to be repaired. Thoroughly dry the surface.
2. Bevel all around the gouge or hole. Use a coarse grinding disk to grind 2-3 inches beyond the edges of the gouge or hole. Use compressed air to remove all grinding debris. Make sure air lines are completely free of moisture.
3. Clean thoroughly about 2 inches beyond the ground area with acetone* to remove any contaminants from the area to be repaired. Allow to dry 20-30 minutes at room temperature.
4. When Scotch-Weld sealant DP-5001 is to be used on a hole in a belt, bevel both the top and bottom of the hole and use duct tape to dam the bottom of the belt.

***Note: When using solvents, be sure to extinguish all ignition sources and follow the manufacturer's precautions and directions for use.**

Application To Gouge/Hole Repair Area

1. Fill the gouge or hole with Scotch-Weld sealant DP-5001 and also apply Scotch-Weld sealant DP-5001 to the ground edges.
2. Use a spreader to spread the Scotch-Weld sealant DP-5001 into the ground edges. Use masking tape to keep Scotch-Weld sealant DP-5001 off of the non-ground areas of the belt.
3. Allow to cure at room temperature for two hours or use the heat-cure method previously described to accelerate the cure.
4. Let the repair cool to room temperature and remove all damming duct tape.

3M

Scotch-Weld™

Polyurethane Sealant

DP-5001, Black

Storage	This product has a shelf life of 6 months when properly stored in unopened packages at temperatures of 65°F to 85°F (18°C to 30°C). Do not expose to excessive cold or moisture.
----------------	--

Maintenance	No maintenance is required; however, if the product repair becomes damaged, simply reapply 3M™ Scotch-Weld™ Polyurethane Sealant DP-5001.
--------------------	---

Precautionary Information	Refer to Product Label and Material Safety Data Sheet (MSDS) for health and safety information before using this product. For environmental information, refer to MSDS. Always wear gloves, eye protection, appropriate respiratory protection, and work in a well-ventilated area. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.
----------------------------------	--

Product Use	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.
--------------------	---

Warranty and Limited Remedy	Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.
------------------------------------	--

Limitation of Liability	Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.
--------------------------------	---

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Business
Industrial Adhesives and Tapes Division
3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M and Scotch-Weld are trademarks of 3M.
Printed in U.S.A.
©3M 2006 78-9236-7085-1 (7/06)