





1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
CONTACT: COPPER ALLOY
5. FINISH: 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD
OVER 0.00127 [.000050] NICKEL ENTIRE POST.
6. FINISH: 0.00254-0.00508 [.000100-.000200] MATTE TIN
OVER 0.00127 [.000050] NICKEL ENTIRE POST.

5	98.65 [3.884]	96.52 [3.800]	39	40	4-146461-0
5	101.19 [3.984]	99.06 [3.900]	38	39	3-146461-9
5	96.11 [3.784]	93.98 [3.700]	37	38	3-146461-8
5	93.57 [3.684]	91.44 [3.600]	36	37	3-146461-7
5	91.03 [3.584]	88.90 [3.500]	35	36	3-146461-6
5	88.49 [3.484]	86.36 [3.400]	34	35	3-146461-5
5	85.95 [3.384]	83.82 [3.300]	33	34	3-146461-4
5	83.41 [3.284]	81.28 [3.200]	32	33	3-146461-3
5	80.87 [3.184]	78.74 [3.100]	31	32	3-146461-2
5	78.33 [3.084]	76.20 [3.000]	30	31	3-146461-1
5	75.79 [2.984]	73.66 [2.900]	29	30	3-146461-0
5	73.25 [2.884]	71.12 [2.800]	28	29	2-146461-9
5	70.71 [2.784]	68.58 [2.700]	27	28	2-146461-8
5	68.17 [2.684]	66.04 [2.600]	26	27	2-146461-7
5	65.63 [2.584]	63.50 [2.500]	25	26	2-146461-6
5	63.09 [2.484]	60.96 [2.400]	24	25	2-146461-5
5	60.55 [2.384]	58.42 [2.300]	23	24	2-146461-4
5	58.01 [2.284]	55.88 [2.200]	22	23	2-146461-3
5	55.47 [2.184]	53.34 [2.100]	21	22	2-146461-2
5	52.93 [2.084]	50.80 [2.000]	20	21	2-146461-1
5	50.39 [1.984]	48.26 [1.900]	19	20	2-146461-0
5	47.85 [1.884]	45.72 [1.800]	18	19	1-146461-9
5	45.31 [1.784]	43.18 [1.700]	17	18	1-146461-8
5	42.77 [1.684]	40.64 [1.600]	16	17	1-146461-7
5	40.23 [1.584]	38.10 [1.500]	15	16	1-146461-6
5	37.69 [1.484]	35.56 [1.400]	14	15	1-146461-5
5	35.15 [1.384]	33.02 [1.300]	13	14	1-146461-4
5	32.61 [1.284]	30.48 [1.200]	12	13	1-146461-3
5	30.07 [1.184]	27.94 [1.100]	11	12	1-146461-2
5	27.53 [1.084]	25.40 [1.000]	10	11	1-146461-1
5	24.99 [.984]	22.86 [.900]	9	10	1-146461-0
5	22.45 [.884]	20.32 [.800]	8	9	146461-9
5	19.91 [.784]	17.78 [.700]	7	8	146461-8
5	17.37 [.684]	15.24 [.600]	6	7	146461-7
5	14.83 [.584]	12.70 [.500]	5	6	146461-6
5	12.29 [.484]	10.16 [.400]	4	5	146461-5
5	9.75 [.384]	7.62 [.300]	3	4	146461-4
5	7.21 [.284]	5.08 [.200]	2	3	146461-3
5	4.67 [.184]	2.54 [.100]	1	2	146461-2
5	2.13 [.084]	-	-	1	146461-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG 1/17/96 CHK 3/18/96 G. DUBNICZKI G. DUBNICZKI		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		PRODUCT SPEC		HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SUB.POST, UNSHROUDED	
MATERIAL		APPLICATION SPEC		SIZE	CAGE CODE
		FINISH		DRAWING NO	RESTRICTED TO
SEE TABLE		WEIGHT		A1	00779
CUSTOMER DRAWING		SCALE		4:1	SHEET 1 OF 1
		REV		B	