





features

- Surface-mountable chip type test terminal
- Automatic machine insertable
- Suitable for reflow and wave soldering
- Available in three standard sizes: 0603, 0805 or 1206
- Products with lead-free terminations meet RoHS requirements

dimensions and construction



Type (Inch Size Code)	Dimensions inches (mm)				
	L	W	t	a	b
RCU (0603)	.063 (1.6)	.031 (0.8)	.045 (1.15)	.009 (0.23)	.009 (0.23)
RCT (0805)	.079 (2.0)	.049 (1.25)	.057 (1.45)	.009 (0.23)	.018 (0.45)
RCS (1206)				.049 (1.25)	.008 (0.2)
RCW (1206)	.126 (3.2)	.063 (1.6)		.079 (2.0)	.009 (0.23)
					.018 (0.45)

Note: Top surfaces of RCT and RCW are not solderable.

ordering information

New Part #	RCU	C	TE
	Type	Termination Material	Packaging
	U	C: SnCu	TE: 7" embossed plastic (2,000 pieces/reel)
	T	(Other termination styles available, contact factory for options)	TED: 10" embossed plastic (5,000 pieces/reel)
	S		RCW not available in TED
	W		

For further information on packaging,
please refer to Appendix A.

applications and ratings

Part Designation	Rated Current	Standard Resistance	Rated Ambient Temperature	Operating Temperature Range
RCU	2 Amps	Less than 50mΩ	+70°C	-55°C to +125°C
RCT				
RCS				
RCW				

environmental applications

Performance Characteristics

Parameter	Requirement ΔR	Test Method
Parameter	Limit	Typical
Resistance	50mΩ Max. after the test	25°C
Overload		Rated voltage x 2.5 or max. overload voltage for 5 seconds, whichever is less
Resistance to Solder Heat		260°C ± 5°C, 10 seconds ± 1 second
Rapid Change of Temperature		-55°C (30 minutes), +125°C (30 minutes), 100 cycles
Moisture Resistance	100mΩ Max. after the test	40°C ± 2°C, 90 - 95% RH, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Endurance at 70°C		70°C ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Low Temperature Operation	50mΩ Max. after the test	-55°C, 1 hour
High Temperature Exposure		+125°C, 100 hours