


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs (g) 100 pcs
	MIN. in (mm)	MAX. in (mm)									
SG100M	.03 (.8)	.9 (23)	.038 (.97)	.118 (3.0)	.173 (4.4)	.154 (3.9)	.209 (5.3)	4.2 (105.9)	18 (80)	MINIATURE	.066 (30)
SG150I	.03 (.8)	1.5 (38)	.040 (1.0)	.168 (4.3)	.220 (5.6)	.179 (4.5)	.306 (7.8)	6.2 (157.0)	40 (178)	INTERMEDIATE	.145 (66)

NOTE:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS	
										PANDUIT CORP. TINLEY PARK, ILLINOIS SUPER-GRIP CABLE TIES UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .020(.5) (.XX) ±.02(.5) ANGLES ± UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY JABO MAT'L: DATE 4/28/05 CHK'D BOB K	
										SCALE NONE DRAWING NO. SS-27441 SHEET 1 OF 3	
1	7/5/07	ERW		CORRECTED SG100M MAX. BUNDLE DIAMETER FROM 1.0 (25mm) TO .9 (23mm).		27441	1			NYLON 6.6 DWG A SIZE	
REV	DATE	BY	CHK	DESCRIPTION		ECN	R	CUST	SUP		