


HONEYWELL PART NUMBER
-

REV	DOCUMENT	CHANGED BY	CHECK
2	0041228	VS 03JUL08	BLR



NOTES
1 - SWITCH MATERIALS WILL WITHSTAND 150°C

RELEASE NO PR-23788	CATALOG LISTING V7-1C33D855-002
REPLACES X111449-V7	CW-B5611

CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: ☒ US (inch) CUSTOMARY ☐ SI (mm) METRIC NO PLACE X ± - ± - ONE PLACE .X ± .030 ± - TWO PLACE .XX ± .015 ± - THREE PLACE .XXX ± .005 ± - ANGLES ± - ± - RAW MATERIAL-COMMERCIAL STANDARD		DRAWN	PPF	18DEC98		Honeywell			
OPERATING FORCE----- 160 GRAMS MAX		CONTACT ARRANGEMENT S P N C				CHECK	JAF	18DEC98					
RELEASE FORCE ----- 15 GRAMS MIN		15.1A 1/2 HP 125, <u>250</u> , 277 VAC 1/2A 125VDC 1/4A 250VDC; 5A 125VAC "L" L215 T 		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		TITLE SWITCH, BASIC							
DIFFERENTIAL TRAVEL ----- .015 MAX													
OVERTRAVEL ----- .035 MIN													
RELEASE TRAVEL ----- .010 MIN				THIRD ANGLE PROJECTION		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED		SIZE	DWG TYPE	DRAWING NAME		REV	
				RASTER		ANSI Y14.5M-1982	B	I	V7-1C33D855-002		2		
						SCALE	NTS	WEIGHT		SHEET I OF I			