



GFG-8215A



GFG-8216A



GFG-8217A



GFG-8219A



GFG-8250A



GFG-8255A



GFG-8200A Series

FEATURES

- Frequency Range: 0.3Hz ~ 3MHz
 - Waveforms: Sine, Triangle, Square, Ramp, TTL and CMOS Output
 - External Voltage Controlled Frequency (VCF) Function
 - Duty Cycle Control with Signal Inversion Capability
 - Variable DC Offset Control
 - Two-Step (-20dBx2) and Variable attenuator
-
- Frequency Range: 0.3Hz ~ 3MHz
 - Waveforms: Sine, Triangle, Square, Ramp, TTL and CMOS Output
 - External Voltage Controlled Frequency (VCF) Function
 - Duty Cycle Control with Signal Inversion Capability
 - Variable DC Offset Control
 - Two-Step (-20dBx2) and Variable attenuator
 - Built-in 6 Digit Counter with INT/EXT Function up to 150MHz
-
- Frequency Range: 0.3Hz ~ 3MHz
 - Waveforms: Sine, Triangle, Square, Ramp, TTL and CMOS Output
 - External Voltage Controlled Frequency (VCF) Function
 - Duty Cycle Control with Signal Inversion Capability
 - Variable DC Offset Control
 - Two-Step (-20dBx2) and Variable attenuator
 - Built-in 6 Digit Counter with INT/EXT Function up to 150MHz
 - LIN/LOG Sweep Mode
-
- Frequency Range: 0.3Hz ~ 3MHz
 - Waveforms: Sine, Triangle, Square, Ramp, TTL and CMOS Output
 - External Voltage Controlled Frequency (VCF) Function
 - Duty Cycle Control with Signal Inversion Capability
 - Variable DC Offset Control
 - Two-Step (-20dBx2) and Variable attenuator
 - Built-in 6 Digit Counter with INT/EXT Function up to 150MHz
 - INT/EXT AM/FM Modulation
 - LIN/LOG Sweep Mode
 - GCV Output for Synchronization
-
- Frequency Range: 0.5Hz ~ 5MHz
 - Waveforms: Sine, Triangle, Square, Ramp, TTL and CMOS Output
 - External Voltage Controlled Frequency (VCF) Function
 - Duty Cycle Control with Signal Inversion Capability
 - Variable DC Offset Control
 - Two-Step (-20dBx2) and Variable attenuator
 - Built-in 6 Digit Counter with INT/EXT Function up to 150MHz
-
- Frequency Range: 0.5Hz ~ 5MHz
 - Waveforms: Sine, Triangle, Square, Ramp, TTL and CMOS Output
 - External Voltage Controlled Frequency (VCF) Function
 - Duty Cycle Control with Signal Inversion Capability
 - Variable DC Offset Control
 - Two-Step (-20dBx2) and Variable attenuator
 - Built-in 6 Digit Counter with INT/EXT Function up to 150MHz
 - INT/EXT AM/FM Modulation
 - LIN/LOG Sweep Mode
 - GCV Output for Synchronization

SPECIFICATIONS

MODEL		GFG-8215A/8216A/8217A/8219A	GFG-8250A / 8255A
MAIN	Frequency Range Amplitude Impedance Attenuator DC Offset Duty Control Display Range Accuracy	0.3Hz ~ 3MHz (7 Range) > 10Vpp (into 50 load) 50 $\pm$ 10% -20dB $\pm$ 1dBx2 <-5V ~ >5V (into 50 load) 80% : 20% : 80% to 1MHz Continue variable 6 digit LED display *GFG-8215A does not have display. $\pm$ 5%+1Hz (at 3 position) *only for GFG-8215A	0.5Hz ~ 5MHz (7 Range) > 10Vpp (into 50 load) 50 $\pm$ 10% -20dB $\pm$ 1dBx2 <-5V ~ >5V (into 50 load) 80% : 20% : 80% to 1MHz Continue variable 6 digit LED display
SINE WAVE	Distortion Flatness	$\leq$ 1%, 0.3Hz ~ 200kHz THD $\leq$ 35dB below fundamental in all range (Specification applied from MAX. to 1/10 level) < 0.3dB, 0.3Hz ~ 300kHz < 0.5dB, 300kHz ~ 3MHz	$\leq$ 1%, 0.5Hz ~ 100kHz THD $\leq$ 30dB below fundamental in all range (Specification applied from MAX. to 1/10 level) $\leq$ 0.3dB, below 500kHz $\leq$ 1dB, below 5MHz
TRIANGLE WAVE	Linear	$\geq$ 98%, 0.3Hz ~ 100kHz $\geq$ 95%, 100kHz ~ 3MHz	$\geq$ 98%, 0.5Hz ~ 100kHz $\geq$ 95%, 100kHz ~ 5MHz
SQUARE WAVE	Symmetry Rise or Fall Time	$\pm$ 2%, 0.3Hz ~ 100kHz $\leq$ 100nS at maximum output (into 50 load)	$\pm$ 2%, 1Hz ~ 100kHz $\leq$ 50nS at maximum output (into 50 load)
CMOS OUTPUT	Level Rise or Fall Time	4Vpp $\pm$ 1Vpp ~ 14.5Vpp $\pm$ 0.5Vpp adjustable $\leq$ 120nS	4Vpp $\pm$ 1Vpp ~ 14.5Vpp $\pm$ 0.5Vpp adjustable $\leq$ 120nS
TTL OUTPUT	Level Fan Out Rise or Fall Time	$\geq$ 3Vpp 20 TTL load $\leq$ 25nS	$\geq$ 3Vpp 20 TTL load $\leq$ 25nS
VCF	Input Voltage Input Impedance	0V ~ 10V $\pm$ 1V (100 : 1) 10k $\pm$ 10%	0V ~ 10V $\pm$ 1V (100 : 1) 10k $\pm$ 10%
GCV (for GFG-8219A/8255A only)	Output Voltage	To set the voltage between 0V ~ 2V as per different frequency	To set the voltage between 0V ~ 2V as per different frequency
SWEEP OPERATION (for GFG-8217A/8219A/8255A only)	Sweep/Manual Sweep/Rate Sweep/Time Sweep/Mode	Switch selector 100 : 1 ratio max. and adjustable 0.5sec. ~ 30sec. adjustable Lin./Log. switch selector	Switch selector 100 : 1 ratio max. and adjustable 0.5sec. ~ 30sec. adjustable Lin./Log. switch selector
AMPLITUDE MODULATION (for GFG-8219A/8255A only)	Depth MOD. Frequency Carrier BW EXT Sensitivity	0 ~ 100% 400Hz (INT), DC ~ 1MHz (EXT.) 100Hz ~ 3MHz (-3dB) $\leq$ 10Vpp for 100% modulation	0 ~ 100% 400Hz (INT), DC ~ 1MHz (EXT.) 100Hz ~ 5MHz (-3dB) $\leq$ 10Vpp for 100% modulation
FREQUENCY MODULATION (for GFG-8219A/8255A only)	Deviation MOD. Frequency EXT. Sensitivity	0 ~ $\pm$ 5% 400Hz (INT), DC ~ 20kHz (EXT.) $\leq$ 10Vpp for 10% modulation	0 ~ $\pm$ 5% 400Hz (INT), DC ~ 20kHz (EXT.) $\leq$ 10Vpp for 10% modulation
FREQUENCY COUNTER (except GFG-8215A)	Int./Ext. Range Accuracy Time Base Resolution Input Impedance Sensitivity	Switch selector 0.3Hz ~ 3MHz (5Hz ~ 150MHz EXT.) Time base accuracy $\pm$ 1 count $\pm$ 10ppm (23 $^{\circ}$ C $\pm$ 5 $^{\circ}$ C) after 30 minutes warm up The maximum resolution is 100nHz for 1Hz and 1Hz for 100MHz 1M // 150pF $\leq$ 35mVrms (5Hz ~ 100MHz) $\leq$ 45mVrms (100MHz ~ 150MHz)	Switch selector 0.5Hz ~ 5MHz (5Hz ~ 150MHz EXT.) Time base accuracy $\pm$ 1 count $\pm$ 10ppm (23 $^{\circ}$ C $\pm$ 5 $^{\circ}$ C) after 30 minutes warm up The maximum resolution is 100nHz for 1Hz and 1Hz for 100MHz 1M // 150pF $\leq$ 35mVrms (5Hz ~ 100MHz) $\leq$ 45mVrms (100MHz ~ 150MHz)
GENERAL INFORMATION	Power Source Accessories Dimension Weight	AC115V, 230V $\pm$ 15%, 50 / 60Hz GTL-101 x 2 (GTL-101 x 1 for GFG-8215A) User manual x 1 251 (W) x 91 (H) x 291 (D) Approx. 2.0 kgs (GFG-8215A) Approx. 2.15kgs (GFG-8217A) Approx. 2.1 kgs (GFG-8216A) Approx. 2.2 kgs (GFG-8219A)	AC115V, 230V $\pm$ 15%, 50 / 60Hz GTL-101 x 2 User manual x 1 251 (W) x 91 (H) x 291 (D) Approx. 2.3 kgs (GFG-8250A) Approx. 2.4 kgs (GFG-8255A)

Specifications subject to change without notice. FG-820AGD0DH

Ordering Information

GFG-8215A	3MHz Function Generator	GFG-8219A	3MHz Function Generator With Counter, Sweep Mode & AM/FM Modulation
GFG-8216A	3MHz Function Generator With Counter	GFG-8250A	5MHz Function Generator With Counter
GFG-8217A	3MHz Function Generator With Counter x Sweep Mode	GFG-8255A	5MHz Function Generator With Counter, Sweep Mode & AM/FM Modulation

Global Headquarters
GOOD WILL INSTRUMENT CO., LTD.
 No. 7-1, Jhongsing Road, Tucheng City, Taipei County 236, Taiwan
 T +886-2-2268-0389 F +886-2-2268-0639
 E-mail: marketing@goodwill.com.tw

China Subsidiary
GOOD WILL Instrument (Shanghai) Co., Ltd.
 8F, of NO.2 Building, No.889 Yishan Road, Shanghai China
 T +86-21-6485-3399 F +86-21-5450-0789
 E-mail: marketing@instek.com.cn

U.S.A. Subsidiary
INSTEK AMERICA CORP., U.S.A.
 3661 Walnut Avenue Chino, CA 91710, U.S.A.
 T +1-909-5918358 F +1-909-5912280
 E-mail: sales@instek.com

Malaysia Subsidiary
GOOD WILL Southeast Asia Sdn. Bhd., MALAYSIA
 27, Persiaran Mahsuri 1/1, Sunway Tunas,
 11900 Bayan Lepas, Penang, Malaysia.
 T +604-6309985 F +604-6309989
 E-mail: ettan@goodwill.com.my

GW INSTEK

www.gwinstek.com.tw