

10 9 8 7 6 5 4 3 2 1

注記
NOTE

- ① 適合ターミナル: 50097-8*00
APPLICABLE: 50097-8*00

- ② トレードマーク: MXJにて表示.

キャビティ番号: 1桁から2桁の数字にて表示. 金型番号: アルファベット1文字にて表示.






TRADE MARK IS FORMED BY MXJ.

AND BY 1-2 DIGIT NUMBER (TO CAVITY NO.)


AND BY 1 LETTER OF ALPHABET (TO MOLD NO.)

3. ELV及びRoHS適合品

ELV AND RoHS COMPLIANT.



(公差非累積)
(NON-ACCUMULATIVE)



基板取付穴推奨寸法基板厚: 1.6mm)

RECOMMENDED PC BOARD
HOLE DIMENSION
(THICKNESS: 1.6mm)

56	60	51036-1500	15
52	56	1400	14
48	52	1300	13
44	48	1200	12
40	44	1100	11
36	40	1000	10
32	36	0900	9
28	32	0800	8
24	28	0700	7
20	24	0600	6
16	20	0500	5
12	16	0400	4
8	12	0300	3
4	8	51036-0200	2
B	A	ENG.NO.	REV. CRT.

材料 MATERIAL	NYLON66,UL94V-0
適用電線範囲 WIRE RANGE	AWG#22~18,AV0.5~0.85 AVS0.3~0.85
被覆外径 INS. RANGE	φ1.8~2.6

REVISED EC NO.: J2011-1484 DRAWN: HORI CHKD: KASAKAWA APPR: NUKITA 2011/05/13 2011/05/13 2011/05/16	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		10 UNDER	± 0.2	DRAWN BY KSANO	DATE 1996/06/30	TITLE 4.0 BOARD IN CONNECTOR HOUSING		
		10 OVER 30 UNDER	± 0.25	CHECKED BY MSAKANO	DATE 1996/06/30			
		30 OVER	± 0.3	APPROVED BY MENOMOTO	DATE 1996/06/30			
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.	SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-51036-001		
	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						