



Features

- Carbon element
- Plain or knurled shaft option
- Metal bushing/metal shaft
- Center detent standard
- Rear solder lugs or PC pins
- 250K and 500K standard resistance values
- Standard M and N taper

■ RoHS compliant*



PDB182-GTRB - 17 mm Blend-Balance Guitar Potentiometer

Electrical Characteristics

Taper..... Linear, audio
Standard Resistance Range..... 250K to 500K ohms
Standard Resistance Tolerance..... $\pm 20\%$
Residual Resistance..... 1 % max.

Environmental Characteristics

Operating Temperature.... -10°C to $+50^{\circ}\text{C}$
Power Rating..... 0.06 watt
Dual Section..... 0.06 watt
Maximum Operating Voltage..... 150 V
Sliding Noise..... 47 mV max.

Mechanical Characteristics

Mechanical Angle..... $300^{\circ} \pm 5^{\circ}$
Rotational Torque..... 10 to 150 gf-cm
Detent Torque..... 50 to 300 gf-cm
Stop Strength..... 5 kg-cm min.
Rotational Life..... 15,000 cycles
Soldering Condition
Manual/Wave..... 260°C max. for 3 seconds max.
Wash..... Not recommended
Hardware..... One flat washer and mounting nut supplied per potentiometer with bushing

Standard Resistance Table

Resistance (Ohms)	Resistance Code
250,000	254
500,000	504


How to Order

PDB18 2 - GTR B1 - 254 MN





Model _____
Number of Sections _____
2 = Dual Section
Guitar Pot Designator _____
Configuration _____
B1 = Knurled Shaft/Solder Lugs/
Center Detent
B2 = Plain Shaft/Solder Lugs/
Center Detent
B3 = Knurled Shaft/PC Pins/
Center Detent
B4 = Plain Shaft/PC Pins/
Center Detent
Resistance Code (See Table) _____
Resistance Taper (See Taper Chart) _____

Product Dimensions

**PDB182-GTRB1,
PDB182-GTRB2**



**PDB182-GTRB3,
PDB182-GTRB4**



TOLERANCES:
UNDER 10.0 = ± 0.3 (± 0.012) 10.0 ~ 100 = ± 0.5 (± 0.020)

*RoHS Directive 2002/95/EC Jan 27, 2003 including Annex.


Specifications are subject to change without notice.

Customers should verify actual device performance in their specific applications.


PDB182-GTRB - 17 mm Blend-Balance Guitar Potentiometer

BOURNS®

Taper Chart




Derating Curve



Circuit

Dual Gang



BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116
Europe: Tel: +41-41 768 5555 • Fax: +41-41 768 5510
The Americas: Tel: +1-951 781-5500 • Fax: +1-951 781-5700
www.bourns.com

REV. 08/11

Specifications are subject to change without notice.
 Customers should verify actual device performance in their specific applications.