


SOT223 P-CHANNEL ENHANCEMENT MODE VERTICAL DMOS FET

ZVP0545G

ISSUE 1 – MARCH 98

FEATURES

- * 450 Volt V_{DS}
- * $R_{DS(on)}=150\Omega$



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Drain-Source Voltage	V_{DS}	-450	V
Continuous Drain Current at $T_{amb}=25^{\circ}\text{C}$	I_D	-75	mA
Pulsed Drain Current	I_{DM}	-400	mA
Gate Source Voltage	V_{GS}	± 20	V
Power Dissipation at $T_{amb}=25^{\circ}\text{C}$	P_{tot}	2	W
Operating and Storage Temperature Range	$T_j:T_{stg}$	-55 to +150	$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated).

PARAMETER	SYMBOL	MIN.	MAX.	UNIT	CONDITIONS.
Drain-Source Breakdown Voltage	BV_{DSS}	-450		V	$I_D=-1\text{mA}$, $V_{GS}=0\text{V}$
Gate-Source Threshold Voltage	$V_{GS(th)}$	-1.5	-4.5	V	$I_D=-1\text{mA}$, $V_{DS}=V_{GS}$
Gate-Body Leakage	I_{GSS}		20	nA	$V_{GS}=\pm 20\text{V}$, $V_{DS}=0\text{V}$
Zero Gate Voltage Drain Current	I_{DSS}		-20 -2	μA mA	$V_{DS}=-450\text{V}$, $V_{GS}=0$ $V_{DS}=-360\text{V}$, $V_{GS}=0\text{V}$, $T=125^{\circ}\text{C}$ (2)
On-State Drain Current(1)	$I_{D(on)}$	-100		mA	$V_{DS}=-25\text{V}$, $V_{GS}=-10\text{V}$
Static Drain-Source On-State Resistance (1)	$R_{DS(on)}$		150	Ω	$V_{GS}=-10\text{V}$, $I_D=-50\text{mA}$
Forward Transconductance (1)(2)	g_{fs}	40		mS	$V_{DS}=-25\text{V}$, $I_D=-50\text{mA}$
Input Capacitance (2)	C_{iss}		120	pF	$V_{DS}=-25\text{V}$, $V_{GS}=0\text{V}$, $f=1\text{MHz}$
Common Source Output Capacitance (2)	C_{oss}		20	pF	
Reverse Transfer Capacitance (2)	C_{rss}		5	pF	
Turn-On Delay Time (2)(3)	$t_{d(on)}$		10	ns	$V_{DD}=-25\text{V}$, $I_D=-50\text{mA}$
Rise Time (2)(3)	t_r		15	ns	
Turn-Off Delay Time (2)(3)	$t_{d(off)}$		15	ns	
Fall Time (2)(3)	t_f		20	ns	

(1) Measured under pulsed conditions. Width=300 μs . Duty cycle $\leq 2\%$

(2) Sample test.

(3) Switching times measured with 50 Ω source impedance and $< 5\text{ns}$ rise time on a pulse generator