



Industrial



Test



Broadcast




Comms



Renewable

300W and 400W, High Density AC-DC, digital power solution



Features	Benefits
• High peak power rating	Reduces size of power supply needed
• Full Digital Control	Improves Product Performance
• High Efficiency	Minimises heat in system
• Temperature controlled fan option	Reduces noise in system
• 5 Year Warranty	Low cost of ownership

Input			
Input Voltage	90-264Vac	Input Frequency	45 - 63Hz (440Hz with reduced PFC - consult sales office)
Input Harmonics	EN61000-3-2 compliant	Inrush Current	<20A at 25°C and 230Vac (cold start) (meets EN61000-3-3). <30A for EFE400
Input Fuse	Dual fuses (Live + Neutral) Fast acting (not user accessible)		
Earth Leakage Current	410µA at 120Vac (60Hz), 858µA max at 240Vac (60Hz) Worst case leakage current is less than 1.0mA at 264Vac, 63Hz (normal condition, 1.8mA Single Fault Condition)		

Quick Selector (Standard models). Additional variants available - see below							
Output Voltage	Current	Units without fan				Units with end fan	
		Open Frame		Cover + Chassis		Cover + Chassis	
		Description	Order Code	Description	Order Code	Description	Order Code
12V	25A	EFE300-12-CNMDs	U2Y002G	EFE300-12-CCMDS	U2Y001F	EFE300-12-ECMDS	U2Y003H
	33.3A	EFE400-12-CNMDs	U4Y002H	EFE400-12-CCMDS	U4Y001G	EFE400-12-ECMDS	U4Y003J
24V	12.5A	EFE300-24-CNMDs	U2Y005K	EFE300-24-CCMDS	U2Y004J	EFE300-24-ECMDS	U2Y006L
	16.7A	EFE400-24-CNMDs	U4Y005L	EFE400-24-CCMDS	U4Y004K	EFE400-24-ECMDS	U4Y006M

How To Create A Product Description							
Output	Factory Setting Range		Case / Fan Option				
	EFE300	EFE400					
12	11.4 - 13.2V	11.4 - 13.2V	CN	Open frame, no fan, with 12V / 0.25A fan supply			
24	22.8 - 26.4V	22.8 - 26.4V	CU	U chassis, no fan, with 12V / 0.25A fan supply			
Required output voltage must be specified at time of ordering			CC	Cover+chassis, no fan, with 12V / 0.25A fan supply			
			EC	Cover+chassis, end fan (temp controlled)			
			EFE300- or EFE400-	Vout	Case/Fan Option	Input Connector	D - Dual Fused
							Earth Leakage
							Output Connector
							blank = right angled -V = vertical
							M = Molex (see connection drawings for details)
							S = Standard (see above for details)
Confirm availability of created product with the sales office							

Isolation

Input to Output	Reinforced	3kVac, 4.3kVdc		
Input to Earth	Basic	1.5kVac, 2.3kVdc	Output to Earth	200Vdc

Output Specification

	EFE300	EFE400	
Output Power	300W	400W	Continuous or RMS (including Peak power)
Peak Power	400W	530W	EFE300 - for 10 seconds EFE400 - for 10 seconds
Total Regulation	better than 4%		Including Line (for 90-264Vac input change), Load (for 0-100% load change) and temperature (0-50°C)
Ripple & Noise	1.5%		pk-pk, using EIAJ test method & 20MHz bandwidth
Voltage Setting Accuracy	±1%		at 50% load
Turn on Time	1.5s max		at 90 Vac & 100% rated output power. EFE400 2s max.
Efficiency	up to 90%		
Hold up	>16ms		at 90 Vac, 75% load
Min Load	None		
Transient Response	<5%		of set voltage for 50% load change (in 50µs within the range 25 - 100% load)
Recovery	<1ms		for recovery to 2% of set voltage
Short circuit protection	Yes		Auto recovery after removal of short circuit
Over Temperature protection	Yes		Primary - auto recovers, secondary - cycle power to restart
Over Voltage Protection	Yes		Latching, need to cycle ac to restart unit.
Fan supply	12V / 0.25A		Available if 'no fan' is specified, otherwise used by PSU fan. No access to connector with -CC (cover + chassis) variant.

Environment

Temperature	0°C to 50°C operational, -40°C to 70°C storage (max 12 months). Full load, with 2m/s air blown from input to output (approximately 10CFM)
Derating	50°C to 70°C derate each output by 2.5% per °C
Low Temp Startup	-20°C
Humidity	5 - 95% RH non condensing
Shock	±3 x 30g shocks in each plane, total 18 shocks 30g shock = 11ms (+/-0.5msec), half sine Conforms to EN60068-2-27, EN60068-2-47, IEC68-2-27, IEC68-2-47, JIS C0041-1987. Conforms to MIL-STD-810E/F, Method 516.5, Pro IV, VI
Vibration	Single axis 10 - 500 Hz at 2g (sweep and endurance at resonance) in all 3 planes Conforms to EN60068-2-6, IEC68-2-6 Conforms to MIL-STD-810E, Method 514.4, Pro I, Cat 1,9
Altitude	-200 to 3000 metres operational (-200 to 5000m storage/transportation)
Pollution	Degree 2, Material group IIIb

Emissions EN61000-6-3:2007

Radiated Electric Field	EN55011, EN55032	(as per CISPR.11/22) Class B, FCC47 part 15 subpart B see application note for details
Conducted Emissions	EN55011, EN55032	(as per CISPR.11/22) Class B, FCC47 part 15 subpart B
Conducted Harmonics	EN61000-3-2	Class A Class C - EFE300 at 100W and above, EFE400 at 200W and above
Flicker	EN61000-3-3	Compliant - d _{max} only

Safety Approvals	
	Notes
IEC/EN 60950-1, UL60950-1 / CSA 22.2 No 60950-1	File E135494
IEC/EN 61010-1	File E331788
CE Mark (EN60950-1)	LV Directive 2006/95/EC
CB certificate and Report available on request	<i>Please check with technical sales for status of approvals</i>

[illegible]

1 off input connector and 3 crimps are available as part number is 94910.
1 off output connector and 10 crimps are available as part number 94750. (EFE300)
1 off output connector and 14 crimps are available as part number 94751 (EFE400)



TDK-Lambda France SAS

3 Avenue du Canada
Parc Technopolis
Bâtiment Sigma
91940 les Ulis
France
Tel: +33 1 60 12 71 65
Fax: +33 1 60 12 71 66
france@fr.tdk-lambda.com
www.fr.tdk-lambda.com



Italy Sales Office

Via Giacomo Matteotti 62
20092 Cinisello Balsamo (MI)
Italy
Tel: +39 02 61 29 38 63
Fax: +39 02 61 29 09 00
info.italia@it.tdk-lambda.com
www.it.tdk-lambda.com



Netherlands

info@nl.tdk-lambda.com
www.nl.tdk-lambda.com



TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40
77855 Achern
Germany
Tel: +49 7841 666 0
Fax: +49 7841 5000
info.germany@de.tdk-lambda.com
www.de.tdk-lambda.com



Austria Sales Office

Aredstrasse 22
2544 Leobersdorf
Austria
Tel: +43 2256 655 84
Fax: +43 2256 645 12
info@at.tdk-lambda.com
www.de.tdk-lambda.com




Switzerland Sales Office

Eichtalstrasse 55
8634 Hombrechtikon
Switzerland
Tel: +41 44 850 53 53
Fax: +41 44 850 53 50
info@ch.tdk-lambda.com
www.de.tdk-lambda.com



Nordic Sales Office

Haderslevvej 36B
DK-6000 Kolding
Denmark
Tel: +45 8853 8086
info@dk.tdk-lambda.com



TDK-Lambda UK Ltd.

Kingsley Avenue
Ilfracombe
Devon EX34 8ES
United Kingdom
Tel: +44 (0) 12 71 85 66 66
Fax: +44 (0) 12 71 86 48 94
powersolutions@uk.tdk-lambda.com
www.uk.tdk-lambda.com



TDK-Lambda Ltd.

1 Alexander Yanai
Segula
Petah-Tikva
Israel
Tel: +9 723 902 4333
Fax: +9 723 902 4777
info@tdk-lambda.co.il
www.tdk-lambda.co.il



C.I.S.

Commercial Support:

Tel: +7 (495) 665 2627

Technical Support:

Tel: +7 (812) 658 0463
info@tdk-lambda.ru
www.tdk-lambda.ru

Local Distribution