

SERIES 84BL


Standard Backlit




FEATURES

- Backlit for Low Light Applications
- Waterproof Silicone Rubber
- Audible, Tactile Contacts
- Low Contact Resistance
- Optional RFI/EMI Shielding
- 3,000,000 Operations per Button

DIMENSIONS In inches (and millimeters)




SCHEMATIC AND TRUTH TABLE



LED Color	Forward Voltage			Resistor (OHMS)	Typ. Current Consumption (With 5V Pwr. Supply)	
	Min.	Typ.	Max.		3 x 4	4 x 4
Red	-	1.95	2.40	43	155mA	205mA
Yellow	-	1.95	2.40	43	155mA	205mA
Green	1.50	-	2.40	43	155mA	205mA
Orange	-	1.95	2.40	43	155mA	205mA

STANDARD LEGENDS

Available through Grayhill Distributors To order one of the configurations below, use the dash number shown here; select the keypad size and order the part number with the appropriate legend dash number. Contact Grayhill for Customs.



SPECIFICATIONS

Rating Criteria

Rating at 24 Vdc: - 10 milliamps resistive
Contact Bounce: 4 milliseconds maximum at make; 10 milliseconds, at break
Contact Resistance: 10 ohms maximum

Life Expectancy: 3 million operations/button
Insulation Resistance: •1,000 megohms

Operating Features

Pre-Travel: .030 inches minimum
Operating Force: 20 ± 4 ounces
Humidity: 0 to 98% (no condensation)

Materials and Finishes

Terminal Pins: Copper alloy CDA 725
PC Board: FR-4 glass cloth epoxy
Dome Retainer/Rear Seal Sheet: Polyester
Mounting Studs: Phosphor bronze
Optional Hex Nut: Stainless steel, passivated
Optional EMI Shield: Aluminum foil
Keypad: Silicone rubber

ORDERING INFORMATION

